


4-bit I/O CONNECTION REAL TIME CLOCK MODULE

RTC-58321/58323

- Builtin crystal unit allows adjustment-free efficient operation.
- Incorporating time counter (hour, minute, sec.) and calender counter (year, month, day of week).
- Either 12H or 24H selectable and leap year automatically adjustable.
- Standard signal output selectable among a choice of 1024 Hz, 1 sec., 60 sec., and 1 hour.
- Provided with counter start, stop and reset functions.
- Data transmission is by 4-bit bidirectional bus line and memory read and write method.
- Low current consumption and backup function provided.



■ Specifications (characteristics)

■ Absolute Max. rating

Item	Symbol	Condition	Specifications	Unit
Power source voltage	V_{DD}	$T_a=25^\circ\text{C}$	-0.3 to 6.5	V
Input and output voltage	V_{IO}		-0.3 to $V_{DD}+0.3$	
storage temperature	T_{STG}	—	-55 to +85	$^\circ\text{C}$
Soldering condition	T_{SOL}	RTC-58321	Under 260°C within 10 sec. (lead part) (package should be less than 150°C)	
		RTC-58323	Twice at under 260°C within 10 sec. or under 230°C within 3 min.	

■ Operating range

Item	Symbol	Condition	Specifications	Unit
Operating voltage	V_{DD}	—	4.5 to 5.5	V
Operating temperature	T_{OPR}	RTC-58321	-10 to +70	$^\circ\text{C}$
		RTC-58323	-30 to +85	
Data holding voltage	V_{DH}	—	2.2 to 5.5	V
CSI data holding time	t_{CDR}	Refer to the data holding timing	0 min.	μs
Operation restoring time	t_r			

■ Frequency characteristics and current consumption characteristics


Item	Symbol	Condition		Specifications	Unit
Frequency tolerance	$\Delta f/f_0$	$T_a=25^{\circ}\text{C}$ $V_{DD}=5\text{V}$	58321 A	± 10	ppm
			58321 B	± 50	
			58323	5 ± 20	
Frequency temperature characteristics	—	-10 to +70°C (25°C reference temperature)		+10/-120	
Aging	f_a	$V_{DD}=5\text{V}$, $T_a=25^{\circ}\text{C}$, first year		± 5 max.	ppm/Y
Shock resistance	S.R.	Three drops on a hard board from 75 cm or 3000G x 0.3ms x 1/2 sine wave x 3 directions		± 10 max.	ppm
Current consumption	$I_{DD\ 1}$	$V_{DD}=5\text{V}$, $CS_1=0\text{V}$		40 max.	μA
	$I_{DD\ 2}$	$V_{DD}=3\text{V}$, $CS_1=0\text{V}$		20 max.	

■ Electrical characteristics

Item	Symbol	Condition	Min.	Typ.	Max.	Unit	Applicable terminal
"H" input voltage	V_{IH1}	—	3.6	—	—	V	Input other than CS_1
"H" input voltage	V_{IH2}		$V_{DD}-0.5$	—	—		
"L" input voltage	V_{IL}	—	—	—	0.8	—	—
"L" output voltage	V_{OL}	$I_{OL}=1.6\text{mA}$	—	—	0.4		
"L" output current	I_{OL}	$V_O=0.4\text{V}$	1.6	—	—	mA	—
"H" input current	I_{IH}	$V_I=5\text{V}$	10	30	80	μA	Input other than D_0 to D_3
"L" input current	I_{IL}	$V_I=0\text{V}$	—	—	-1		
Input leak current	I_{LIH}	$V_I=5\text{V}$	—	—	1	μA	D_0 to D_3
Input off leak current	I_{LIL}	$V_I=0\text{V}$	—	—	-1		
Input capacity	C_1	Input frequency 1 MHz	—	5	—	pF	—
Oscillation start-up time	t_{OSC}	$V_{DD}=5\text{V}$ $T_a=25^\circ\text{C}$	—	1.5	3.0	s	Busy output


■ Terminal connection

● RTC-58321



No.	58321	No.	58323
1	CS_2	1 to 4	N.C
2	WRITE	5	CS_2
3	READ	6	WRITE
4	D_0	7	READ
5	D_1	8	D_0
6	D_2	9	D_1
7	D_3	10	D_2
8	GND	11	D_3
9	ADDRESS WRITE	12	GND
10	BUSY	13	ADDRESS WRITE
11	STOP	14	BUSY
12	TEST	15	STOP
13	CS_1	16	TEST
14 to 15	N.C	17	CS_1
16	V_{DD}	18 to 24	V_{DD}

● RTC-58323




● NC is not connected internally.


■ External dimensions

(Unit: mm)

● RTC-58321



● RTC-58323



■ Supplement

0= "L" level 1= "H" level

Item	Description																							
* mark	Writable. Recognized as 0 while in read mode																							
24/12	"1" =24 H mode,"0" =12H mode																							
PM/AM	"1" =PM, "0" =AM. In 24 H mode, this will be "0"																							
D ₃ and D ₂ of 10 days digit	Used to select leap year. Calculated according to the surplus after dividing 10 year digit by 4 <table><tr><th>Calendar</th><th>D₃</th><th>D₂</th><th>Surplus after dividing 10 year digit by 4</th><th>Example of leap year</th></tr><tr><td>Gregorian calendar</td><td>0</td><td>0</td><td>0</td><td>96, 00</td></tr><tr><td rowspan="3">Spare</td><td>1</td><td>0</td><td>3</td><td></td></tr><tr><td>0</td><td>0</td><td>2</td><td></td></tr><tr><td>1</td><td>1</td><td>1</td><td></td></tr></table>	Calendar	D ₃	D ₂	Surplus after dividing 10 year digit by 4	Example of leap year	Gregorian calendar	0	0	0	96, 00	Spare	1	0	3		0	0	2		1	1	1	
Calendar	D ₃	D ₂	Surplus after dividing 10 year digit by 4	Example of leap year																				
Gregorian calendar	0	0	0	96, 00																				
Spare	1	0	3																					
	0	0	2																					
	1	1	1																					
Reset register	These selections are for resetting 5-stage and the busy circuit after 1/2 ¹⁵ frequency stage. Resetting is activated by latching this code on to the address latch and setting WRITE=H																							
Standard signal register	By latching this code to the address latch and setting READ to H, the standard signals will be output at D ₀ to D ₃																							

Note:

- Do not enter erroneous data for clock.
- This may result in time keeping error.
- Do not change STOP more than once while in BUSY mode.

■ Switching characteristics

● Write & read mode

(V_{DD}=5V±0.5V)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit.
CS setup time	t _{CS}	—	0	—	—	μs
Address setup time	t _{AS}		0.5			
Address write pulse width	t _{AW}		0.1			
Address hold time	t _{AM}		0			
Data setup time	t _{DS}		2			
Write pulse width	t _{WW}		0			
Data hold time	t _{DH}		—			
Read inhibit time	t _{RI}		—			
Read access time	t _{RA}		—		*1	
Read delay time	t _{DD}		—		1	
CS hold time	t _{CH}		0		—	

*1 t_{RA}=1μs+C x R x ln [V_{DD}/(V_{DD}-V_H)]


C: Data line capacity

R: Pull-up resistance

V_H: "H" input voltage connected to the data line

ln: Natural logarithm


● Date holding timing



■ Register table

Address	D ₃	D ₂	D ₁	D ₀	Name of register	D ₃	D ₂	D ₁	D ₀	Count	Note
0	0	0	0	0	S ₁	S ₈	S ₄	S ₂	S ₁	0 to 9	1 - sec. digit register
1	0	0	0	1	S ₁₀	*	S ₄₀	S ₂₀	S ₁₀	0 to 5	10 - sec. digit register
2	0	0	1	0	MI ₁	mi ₈	mi ₄	mi ₂	mi ₁	0 to 9	1 - min. digit register
3	0	0	1	1	MI ₁₀	*	mi ₄₀	mi ₂₀	mi ₁₀	0 to 5	10 - min. digit register
4	0	1	0	0	H ₁	h ₈	h ₄	h ₂	h ₁	0 to 9	1 - hour digit register
5	0	1	0	1	H ₁₀	24/12	PM/AM	h ₂₀	h ₁₀	0 to 2 or 0 to 1	10 - hour digit register
6	0	1	1	0	W	*	W ₄	W ₂	W ₁	0 to 6	Week register
7	0	1	1	1	D ₁	d ₈	d ₄	d ₂	d ₁	0 to 9	1 - day digit register
8	1	0	0	0	D ₁₀	Leap year selection	d ₂₀	d ₁₀		0 to 3	10 - day digit register
9	1	0	0	1	MO ₁	mo ₈	mo ₄	mo ₂	mo ₁	0 to 9	1 - month digit register
A	1	0	1	0	MO ₁₀	*		mo ₁₀		0 to 1	10 - month digit register
B	1	0	1	1	Y ₁	y ₈	y ₄	y ₂	y ₁	0 to 9	1 - year digit register
C	1	1	0	0	Y ₁₀	y ₈₀	y ₄₀	y ₂₀	y ₁₀		10 - year digit register
D	1	1	0	1	—	*					Reset register
E	1	1	1	0	—	1 hour	1 min.	1 sec.	1024 Hz		Standard signal register
F	1	1	1	1	—						

● Write and read timing

(V_{DD}=5V±0.5V T_a=25°C)

■ Block diagram

