




FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC				
ltr	ecn no	dr	date	tolerances unless otherwise specified					title					
A	V12795	RDS	10/24/91	angles	linear	.XX ±.01/.3			INCH/MM	VERTICAL SHROUD 3 ROW W/O GUIDE PIN				
B	V20224	MRC	2/28/92			.XXX ±.005/.13								
C	V23049	SAR	7/24/92			0°±2°	.XXXX ±.0020/.051							
D	V41077	GAH	7/06/94	dr	D. SHEAFFER	8/07/91		scale 1:1	FCI 				dwg no 50434	sheet 1 of 2 A3
E	V94441	JWS	12/30/99	enr	S. CLARK	10/24/91								
F	V05-0967	DAI	10/20/05	chr	S. CLARK	10/24/91								
G	M06-0255	AEA	7/07/06	appd	S. CLARK	10/24/91								
sheet index		revision	G	G						type Product Customer Drawing				
		sheet	1	2										

form: A3

PDM: Rev:G


STATUS: Released

Printed: May 13, 2011


1 2 3 4 5 6

PRODUCT NUMBER

SEE NOTE 1



SECTION U-U



SECTION X-X

NOTES:

- PRODUCT NUMBERING CODE:
50434-X YYY X LF
LEAD FREE (OPTIONAL)
ALWAYS "X"
NO. OF POSITIONS SEE NOTE 2
ALWAYS "X"
BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6, 7, 8, 9,.....79, 80.
- MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC.
FLAME RETARDANT PER UL94 V-0. COLOR: BLACK
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.
- LENGTH FORMULAS
DIM A= $.100/2.54 \times \text{NO. OF COLUMNS} + .75/19.1$
DIM B= $.100/2.54 \times \text{NO. OF COLUMNS} + .450/11.43$
DIM C= $.100/2.54 \times \text{NO. OF COLUMNS} - .100/2.54$
- THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE OVEN.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ec	no	dr	date	tolerances unless otherwise specified	scale 1:1 FCJ	title VERTICAL SHROUD 3 ROW W/O GUIDE PIN
G					angles linear .XX ±.01/.3 .XXX ±.005/.13 0°±2° .XXXX ±.0020/.051		dwg no 50434
					dr D. SHEAFFER 8/07/91		sheet 2 of 2 size A3
					enr S. CLARK 10/24/91		
					chr S. CLARK 10/24/91		
					appd S. CLARK 10/24/91		
sheet index	revision sheet						type Product Customer Drawing

form: A3

1 2 3 4 5 6