


**Part Number: 79107-0068**

2.00mm Pitch Milli-Grid™ Receptacle, Through Hole, Dual Row, Vertical, 0.80µm Gold (Au) Selective, 38 Circuits



Series image - Reference only

Status: **OBsolete**
Replacement: [791077068](#)
Series: [79107](#)
Category: PCB Receptacles

Mates With Part(s):
[87759](#), 87762, 87758, 87760**Product Environmental Compliance**EU RoHS: Not RoHS CompliantChina RoHS: REACH SVHC: Contains SVHC: NoLow-Halogen Status: Not Reviewed**Part Detail****General**

Status	Obsolete
Category	PCB Receptacles
Series	79107
Application	Board-to-Board, Signal
Obsolete Date	2005/06/01
Product Name	Milli-Grid™

Physical

Circuits (Loaded)	38
Circuits (maximum)	38
Durability (mating cycles max)	50
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Through Hole

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Solder Process Data

Replacement RoHS Compliant Part Number	0791077068
--	------------

Material Info

UPC	800754347846
-----	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling

Specification document.

Previously Available Application

Tooling

[Check our list of old tooling that used to be available for this part](#)