




PANDUIT PART NUMBER *	WEIGHT lbs/100 pcs (g)/100 pcs	MAXIMUM BUNDLE CAPACITY	PANEL DIMENSIONS	
			THICKNESS	HOLE SIZE
VWS106----	0.397 (180)	1.06 (26.9)	UP TO 0.090 (UP TO 2.29)	0.187 (4.76)



NOTES;
* 1. SEE CURRENT PRICE SHEET FOR
PART NUMBER SUFFIX DESIGNATION
FOR PACKAGE SIZE.
2. -20 MATERIAL DESIGNATION IS
PIGMENTED BLACK



CAD FILENAME/LAYERS

G01332BB_PB_VWS106_03

PANDUIT

CORP. TINLEY PARK, ILLINOIS

VWS106-
VERTICAL WIRE SADDLE

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	JAD
----------	-----

BY JAD

MAT'L:

DATE	7-24-97
------	---------

NYLON 6/6

SCALE	NONE
-------	------

DRAWING NO.

GB 1332BB

DWG
A
SIZE

3	7-03-01	LGG		UPDATED AND ADDED REF	G01332BB	3			
2	4-21-98	MLD		DIM 0.34 (8.6) WAS 0.36 (9.1)	G01332BB	2			
1	7-29-97	JAD		MAX PANEL THICKNESS CHANGED FROM .105 TO .090. ADDED 1.18 DIM. ADDED 'INSTALLED' TO 1.3 DIM.	G01332BB	1			
R	7-24-97	JAD		INITIAL RELEASE	G01332BB	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		