


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REDRAWN PER ECO-17-007400	12DEC2017	RS	DR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



1 FOR $\phi 3.810[\phi .150]$ TO $\phi 5.842[\phi .230]$ WIRE INSULATION.

2 BODY MATERIAL THICKNESS: $1.219 \pm 0.051[.048 \pm .002]$


3 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

4 STAMP AMP 16-14* APPROX AS SHOWN.

5 MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B152
INSULATION: NYLON PER ASTM D4066, TYPE I.

6 FINISH:
BODY & SLEEVE: TIN PLATE PER ASTM B545
INSULATION: COLOR-YELLOW.

2500	ON TAPE	1-320627-0
500	LOOSE PIECE	320627
QTY.	PACKAGE TYPE	PART NO.

DIMENSIONS: mm [INCHES]		DWN RAVI S	12DEC2017	MATERIAL 5	FINISH 6		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		CHK ROHDE DANIEL F	12DEC2017	 TE Connectivity			
		APVD ROHDE DANIEL F	12DEC2017				
		PRODUCT SPEC UL 486 A-B		NAME WIRE TERMINAL, P.I.D.G-RING TONGUE, WIRE SIZE: 16-14 AWG HD			
		APPLICATION SPEC 114-2157					
		WEIGHT —		SIZE A4	CAGE CODE 00779	DRAWING NO C-320627	RESTRICTED TO —
		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1