


REV	DESCRIPTION	DATE
AA	RELEASE, FORMERLY EBBERT# 15541-H300-358A	9/18/01
B	REVISED WAS DRAWN WRONG	01/31/03
C	REVISED AND REDRAWN	10/13/03
D	OBSOLETE SUPERSEDED BY PH2F1LH	12/05/03



FILE OBSOLETE

OBSOLESCENT DATE: XX/XX/XX

OBSOLETE DATE: 12/05/03

SUPERSEDED BY: PH2F1LH

FORM KE104 REV C		By accepting this proprietary Huck drawing, recipient agrees not to reproduce or disclose any part thereof to any others without the written permission of Huck International, Inc.							
MATERIAL:	-	SPEC:	TOLERANCES UNLESS OTHERWISE SPECIFIED: (ALL DIMENSIONS ARE IN INCHES)		HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DRIVE, P.O. BOX 2270 KINGSTON, NEW YORK 12401				
HARDNESS:	-	RAW OR STOCKED STATE							
HEAT TREAT TO:	-	SPEC:	.XX, .XXX ±	.01, .005	PULLING HEAD ASSEMBLY				
SURFACE TREAT:	-	SPEC:	INT. COR. RADII	.005-.015					
SURFACE FINISH NOT TO EXCEED: 125 Ra			BREAK EDGES		.005-.015	DET: CHR	CK:	DATE: 9/18/01	SCALE: 2/1
IDENTIFICATION PER SPEC 42-31: ★ PERMANENT			ANGLES ±		3°	FOC.	B	PH2F1HL	
SURFACES TO BE ○, //, ◆, ⊥, & ▽ WITHIN .005 T.I.R.			FINAL ASSY:		FAC.				