


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	THE OFFICIAL VERSION RELEASED	27-Feb-15	E.F.	C.W.

- NOTES:
- 1. HOUSING MATERIAL: THERMO PLASTIC RESIN.
 - 2. CONTACT MATERIAL: COPPER ALLOY.
 - 2. FINISH :
50u" MIN. NICKEL UNDERPLATING ALL OVER,
GOLD PLATING 2u" MIN. ON CONTACT AREA
12u" MIN. PD/Ni ON CONTACT AREA
GOLD PLATING 1u" MIN. ON SOLDER AREA
 - 3. COPLANARITY: 0.08MAX. (BEFORE IR)
 - 4. DATE CODE:
YWWDSL (YEAR, WEEK, DAY, SHIFT, LINE)



CARD INSERTION DIRECTION

2287217-1	2	CONTACT	2
	1	HOUSING	1
P/N	ITEM	COMPONENT	MATERIAL / FINISH






ANTI-BUCKLING BLOCK SIM CONNECTOR
SIDE ENTRY TYPE


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2287217	-

DWN	E.F.	27-Feb-15
CHK	S.L.	27-Feb-15
APVD	C.W.	27-Feb-15
PRODUCT SPEC		
108-115090		
APPLICATION SPEC		
-		
WEIGHT	0.026g	
CUSTOMER DRAWING		



THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		
	0 PLC	±-
	1 PLC	±0.1
	2 PLC	±0.05
	3 PLC	±0.02
	4 PLC	±-
MATERIAL	FINISH	-




SEE DETAIL A




DETAIL A
SCALE 50:1



SOLDER AREA




COPPER FOIL REMOVE & SOLDER MASK KEEP OUT (DEPTH:0.05~0.10MM)



CONNECTOR BOUNDARY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.05
3 PLC ±0.02
4 PLC ±
ANGLES ±

MATERIAL

-

FINISH

-

DWN E.F. 27-Feb-15

CHK S.L. 27-Feb-15

APVD C.W. 27-Feb-15

PRODUCT SPEC

108-115090

APPLICATION SPEC

-

WEIGHT

0.026g

CUSTOMER DRAWING



TE Connectivity

NAME
ANTI-BUCKLING BLOCK SIM CONNECTOR
SIDE ENTRY TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2287217

-

SCALE 10:1

SHEET

2

OF

2

REV

A