

Rev. V5

TO-8-1

-

Dimensions in () are in mm
Unless Otherwise Noted, .XXX = ± 0.10 (.XX = ± 0.25)
XX = ± 0.02 (X = ± 0.5)
WEIGHT (APPROX) 0.20 OUNCES 2.8 GRAMS

SF-1




Figure 1: Mechanical drawing of the test specimen. The drawing shows a top view and a side view. The top view is a rectangle with four pins labeled 1, 2, 3, and 4. Pin 1 is at the top left, pin 2 at the top right, pin 3 at the bottom left, and pin 4 at the bottom right. Dimensions are given in inches and millimeters. The top view dimensions are: width .016 W ± 0.001 (0.41 ± 0.03) X 0.10 (2.54 ± 0.31), height .060 (1.52), distance from top edge to pin 1 center .385 ± 0.020 (9.8 ± 0.51), distance from top edge to pin 2 center .385 ± 0.020 (9.8 ± 0.51), distance from bottom edge to pin 3 center .510 ± 0.020 (12.95 ± 0.51), distance from bottom edge to pin 4 center .510 ± 0.020 (12.95 ± 0.51), distance from left edge to pin 1 center .205 (5.21), distance from left edge to pin 3 center .305 (7.75), distance from left edge to pin 4 center .430 (10.92), and distance from right edge to pin 2 center .060 (2.0). The side view shows a thickness of .070 (4.32) MAX. and a ground tab on the left side.

Dimensions in Ø are in mm
Unless Otherwise Noted: XXX = +0.010
XX = +0.02
WEIGHT (APPROX), 0.07 OUNCES 2 GRAMS

Absolute Maximum Ratings ¹

Parameter	Absolute Maximum
Max. Input Power	+10 dBm
V _{bias}	+15.75 V
Operating Temperature	-55°C to +85°C
Storage Temperature	-65°C to +125°C

North America Tel: 800.366.2266 • **Europe** Tel: +353.21.244.6400
India Tel: +91.80.4155721 • **China** Tel: +86.21.2407.1588
 Visit www.macomtech.com for additional data sheets and product information.

M/A-COM Technology Solutions Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Electrical Specifications: ² T_A = -55°C to +85°C Case Temperature

Parameter	Test Conditions	Frequency	Units	Min.	Typ.	Max.
Gain	@+25°C	50 MHz	dB	12.0	12.5	13.0
Frequency Response	—	10 - 100 MHz	dB	—	—	±0.6
Gain Variation with Temperature	—	10 - 100 MHz	dB	—	—	±0.6
1 dB Compression	Output Power	10 - 100 MHz	dBm	+13	—	—
Noise Figure	—	10 - 100 MHz	dB	—	—	1.6
Reverse Transmission	—	10 - 100 MHz	dB	—	-15	-14
VSWR	—	10 - 100 MHz	Ratio	—	—	2.0:1
Output IP ₂	Two-Tone inputs up to 0 dBm	10 - 100 MHz	dBm	+40	—	—
Output IP ₃	Two-Tone inputs up to 0 dBm	10 - 100 MHz	dBm	+26	—	—
V _{bias}	—	—	VDC	+14.5	+15.0	+15.5
I _{bias}	V _{bias} = +15.0 VDC	—	mA	—	11	15
Power Dissipation	@ +15 V Bias	—	mW	—	165	—


2. All specifications apply when operated at +15 VDC, with 50 ohms source and load impedance.

S-Parameter Data


Frequency (MHz)	S11 MAG/ANG	S21 MAG/ANG	S12 MAG/ANG	S22 MAG/ANG
10	0.07/165	4.06/66	0.18	0.09/169.1
20	0.09/-166.8	4.13/-6.5	0.17	0.09/-159.2
30	0.08/-151.5	4.18/-15.8	0.17	0.09/-129.5
40	0.10/-146.9	4.20/-24.0	0.17	0.11/-120.3
50	0.11/-147.9	4.23/-32.2	0.17 1	0.12/-117.7
60	0.11/-152.0	4.19/-39.8	0.17	0.13/-118.5
70	0.12/-159.7	4.20/-47.7	0.17	0.14/-120.3
85	0.12/-171.2	4.17/-59.5	0.16	0.14/-122.6
100	0.12/174.1	4.15/-72.1	0.16	0.15/-123.6

Typical Performance Curves


Gain vs. Frequency




VSWR vs. Frequency




Noise Figure



1 dB Compression



Intermodulation Intercept



Ordering Information

Part Number	Package
AM-162 PIN	TO-8-1
AMC-162 SMA **	Connectorized
AMS-162 PIN	SF-1

** The connectorized version is not RoHS compliant.