

ES52E9C1N-10.000M TR

[Click part number to visit Part Number Details page](#)

REGULATORY COMPLIANCE (Data Sheet downloaded on Apr 30, 2016)


[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.



ITEM DESCRIPTION

Temperature Compensated Quartz Crystal Clock Oscillators TCXO (TCVCXO) Clipped Sinewave Stratum 3 3.3Vdc 10 Pad 5.0mm x 7.0mm Ceramic Surface Mount (SMD) 10.000MHz ± 0.28 ppm Maximum -20°C to +70°C

ELECTRICAL SPECIFICATIONS

Nominal Frequency	10.000MHz
Total Frequency Tolerance	± 4.6 ppm Maximum (Inclusive of Frequency Tolerance, Frequency Stability, Vdd ($\pm 1\%$), Load ($\pm 5\%$), solder reflow, and 20 year aging)
Frequency Tolerance	± 1.0 ppm Maximum (at 25°C $\pm 2^\circ\text{C}$, at Vdd=3.3Vdc (Pre-Reflow))
Frequency Stability	± 0.28 ppm Maximum (Inclusive of Operating Temperature Range, at Vdd=3.3Vdc; $(F_{\text{max}} - F_{\text{min}})/(2 \cdot F_0)$)
Frequency Stability vs. Aging	± 3.0 ppm over 20 Years Maximum (at 25°C)
Operating Temperature Range	-20°C to +70°C
Supply Voltage	3.3Vdc $\pm 5\%$
Total Holdover Stability	± 0.37 ppm Maximum (Inclusive of Frequency Stability and 24 hours aging)
Input Current	2.0mA Maximum
Output Voltage	0.8Vp-p Clipped Sinewave Minimum (External DC-Cut capacitor required, 1000pF recommended)
Load Drive Capability	10kOhms // 10pF
Output Logic Type	Clipped Sinewave
Control Voltage	None (No Connect Pad 10)
Phase Noise	All Values are Typical -80dBc/Hz at 10Hz Offset -115dBc/Hz at 100Hz Offset -135dBc/Hz at 1kHz Offset -145dBc/Hz at ≥ 10 kHz Offset
RMS Phase Jitter	1pSec Maximum ($F_j = 12$ kHz to 20MHz)
Start Up Time	10mSec Maximum
Storage Temperature Range	-40°C to +125°C


ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

Fine Leak Test	MIL-STD-883, Method 1014 Condition A
Gross Leak Test	MIL-STD-883, Method 1014 Condition C
Mechanical Shock	MIL-STD-202, Method 213 Condition C
Resistance to Soldering Heat	MIL-STD-202, Method 210
Resistance to Solvents	MIL-STD-202, Method 215
Solderability	MIL-STD-883, Method 2003
Temperature Cycling	MIL-STD-883, Method 1010
Vibration	MIL-STD-883, Method 2007 Condition A

ES52E9C1N-10.000M TR

[Click part number to visit Part Number Details page](#)


MECHANICAL DIMENSIONS (all dimensions in millimeters)



LINE	MARKING
1	EXX.XXX <i>E=Ecliptek Designator XX.XXX=Nominal Frequency in MHz</i>
2	XXXXXX <i>XXXXXX=Ecliptek Manufacturing Identifier</i>

Suggested Solder Pad Layout

All Dimensions in Millimeters




All Tolerances are ±0.1

ES52E9C1N-10.000M TR [Click part number to visit Part Number Details page](#)




OUTPUT WAVEFORM



ES52E9C1N-10.000M TR

[Click part number to visit Part Number Details page](#)

Test Circuit for No Connect Option



Note 1: An external $0.01\mu\text{F}$ bypass capacitor in parallel with a $0.1\mu\text{F}$ high frequency ceramic bypass capacitor close (less than 2mm) to the package ground and supply voltage pin is required.

Note 2: A low input capacitance ($<12\text{pF}$), 10X attenuation factor, high impedance ($>10\text{Mohms}$), and high bandwidth ($>300\text{MHz}$) passive probe is recommended.

Note 3: Capacitance value C_L includes sum of all probe and fixture capacitance.

ES52E9C1N-10.000M TR

Tape & Reel Dimensions

Quantity Per Reel: 1,000 units

All Dimensions in Millimeters

Compliant to EIA-481



ES52E9C1N-10.000M TR
[Click part number to visit Part Number Details page](#)
Recommended Solder Reflow Methods**Low Temperature Infrared/Convection 230°C**

T _S MAX to T _L (Ramp-up Rate)	5°C/Second Maximum
---	--------------------

Preheat

- Temperature Minimum (T _S MIN)	N/A
- Temperature Typical (T _S TYP)	150°C
- Temperature Maximum (T _S MAX)	N/A
- Time (t _s MIN)	30 - 60 Seconds

Ramp-up Rate (T _L to T _P)	5°C/Second Maximum
--	--------------------

Time Maintained Above:

- Temperature (T _L)	150°C
- Time (t _L)	200 Seconds Maximum

Peak Temperature (T _P)	230°C Maximum
------------------------------------	---------------

Target Peak Temperature (T _P Target)	230°C Maximum 2 Times
---	-----------------------

Time within 5°C of actual peak (t _P)	10 Seconds Maximum 2 Times
--	----------------------------

Ramp-down Rate	5°C/Second Maximum
----------------	--------------------

Time 25°C to Peak Temperature (t)	N/A
-----------------------------------	-----

Moisture Sensitivity Level	Level 1
----------------------------	---------

Additional Notes	Temperatures shown are applied to body of device.
------------------	---

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to body of device.)

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to body of device.)