



Flex-Twist Hanger Assembly for WR42

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide
Cables per Hanger 1
Color Silver
Hanger Type Flex-Twist hanger
Mounting 4.5 in OD pipe

Dimensions

Height 7.62 mm | 0.3 in
Width 151.892 mm | 5.98 in
Length 381 mm | 15 in
Waveguide Size WR42 | WG20 | R220

Material Specifications

Material Type Stainless steel

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Test Method MIL-F-14072C | MIL-STD-889B

Packaging and Weights

Included Clamp | Rubber grommet | Threaded rod
Packaging quantity 1

244106A-220

Weight, gross 0.64 kg | 1.411 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

