
samtec

(2,00 mm) .0787"

TLSD SERIES



COST EFFECTIVE IDC SOCKET CABLES

Mates with:
TMM, TMMH (Except –SR), TW, MTMM, TLMM

FEATURES

- Low cost alternative to TCSD
- 1 point of contact phosphor bronze
- Strain Relief for Rugged Applications

SPECIFICATIONS

For complete specifications see www.samtec.com?TLSD

Insulator Material:
Black Glass Filled Polyester
Contact:
Phosphor Bronze
Plating:
Au or Sn over
50µ" (1,27 µm) Ni
Wire:
28 AWG 7/36 Stranded, Tinned, Copper with Gray PVC Insulator
Current Rating:
1A per contact
Operating Temp Range:
-40°C to +105°C
Lead Size Accepted:
(0,48 mm) .019" to (0,53 mm) .021"
Contact Resistance:
15 mΩ maximum delta from initial
Insertion Depth:
(3,56 mm) .140" to (4,27 mm) .168"
Insertion Force:
(Single contact only)
2 oz. (0,56 N) average
Withdrawal Force:
(Single contact only)
1.4 oz (0,39 N) average
RoHS Compliant:
Yes

FILE NO. E111594

TIGER BEAM CONTACT™

POLARIZING KEY

Specify PK-01-07 for polarizing key. Also polarizes SMM Series socket strips.

ALSO AVAILABLE


Connector only (KTLSD Series). Call Samtec.

Note: TLSD Series assemblies are non-standard, non-returnable.

TYPE – NO. PINS PER ROW – END OPTION – LENGTH – 01 – PLATING OPTION – OTHER OPTION


–05, –08, –10, –12, –13, –15, –17, –20, –22, –25
(Call for other sizes)

–"XX.XX"
= Assembled Length




–L
= 10µ" (0,25 µm) Gold on contact area


–S
= Single End




–D
= Double End



–N
= Notch Polarization




–RW
= Reverse Wiring



Black wire opposite position #1.


TLSD
= Socket Strip




–SR
= Strain Relief

RUGGEDIZED by SAMTEC

- Strain relief
- Optional polarization and polarizing key




–RN1
= Reverse Notch End 1



Reverse notch option on end 1 only. Not Available with –R option.

–P "XX"
= Position Polarization



Specify "XX" as position number. Same position will be polarized on both ends.


–RN2
= Reverse Notch End 2



Reverse notch option on end 2 only. Not Available with –R option.


–B "XX"
= Breakout

Specify "XX" as number of conductors to be broken out.




Breakout starts with Number 1 lead indicated by brown wire or red stripe. Shown on top side.


–D "XX"
= Daisy Chain



–R
= Reversed




–M
= Middle Reverse



Requires –DXX

–O
= Outside Reverse



Requires –DXX

Due to technical progress, all designs, specifications and components are subject to change without notice.

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 **SAMTEC NORTHERN CALIFORNIA** • Tel: 408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 **SAMTEC UNITED KINGDOM** • Tel: 44 01236 739292 **SAMTEC GERMANY** • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 **SAMTEC ITALY** • Tel: 39 039 6890337 **SAMTEC NORDIC/BALTIC** • Tel: +46-84477280 **SAMTEC BENELUX** • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 **SAMTEC INDIA** • Tel: +91-80-3272 1612 **SAMTEC ASIA PACIFIC** • Tel: 65 6745-5955 **SAMTEC JAPAN** • Tel: 045-475-1385 **SAMTEC CHINA** • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 **SAMTEC HONG KONG** • Tel: 852-26904858 **SAMTEC KOREA** • Tel: 82-31-717-5685 **SAMTEC ANZ** • Tel: 613 9580 0683