

**Description**

- Industry standard SMD crystal
Plastic encapsulated
Low profile version also available please contact our sales offices for details
- Model 86SMX
- Model Issue number 10

Frequency Parameters

- Frequency 11.05920MHz
- Frequency Tolerance @ 25°C $\pm 50.00\text{ppm}$
- Frequency Stability $\pm 100.00\text{ppm}$
- Operating Temperature Range -20.00 to 70.00°C
- Overtone Order Fundamental
- Ageing $\pm 5\text{ppm}$ max per year at 25°C

Electrical Parameters

- Load Capacitance (C_L) 20.00pF
- Shunt Capacitance (C_0) 5pF max
- Drive Level 100 μ W max
- ESR 50 Ω max

Environmental Parameters

- Vibration: 1.5mm amplitude, 10Hz-55Hz, 1min in 3 mutually perpendicular planes, duration 2hrs each plane
- Storage Temperature Range: -40 to 90°C
- Drop: 75cm drop (3 times) onto hard wooden board


Compliance

- RoHS Status Compliant
- REACH Status Compliant


Packaging

- Pack Type: Bulk Loose in bulk pack
- Pack Size 100
- Alternative packing option available

This document is correct at the time of printing; please contact your local office for the latest version.

**Outline (mm)**

Pad Connections
1. Crystal
2. N/C
3. N/C
4. Crystal

Solder Pad Layout**Sales Office Contact Details:**

UK: +44 (0)1460 270200

Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18

USA: +1 (0) 408 455 2426

Email: info@iqdfrequencyproducts.comWeb: www.iqdfrequencyproducts.com