







STRAIGHT BACKSHELL - TYPE 1




STRAIGHT BACKSHELL - TYPE 2




45° BACKSHELL - TYPE 1




45° BACKSHELL - TYPE 2




90° BACKSHELL - TYPE 1



90° BACKSHELL - TYPE 2



90° BACKSHELL - TYPE 1
STAINLESS STEEL AND
NICKEL ALUMINIUM BRONZE



90° BACKSHELL - TYPE 2
STAINLESS STEEL AND
NICKEL ALUMINIUM BRONZE

DRAWN	K.WINCZURA	DATE	04/12/2014
CHECKED		DATE	04/12/2014
APPROVED	K.SHEPPARD	DATE	11/12/2014
APPROVED	H.SMITH	DATE	07/07/2015
REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
D	REVISED PER ECO-15-002398	17/02/2015	H.SMITH
E	REVISED PER ECO-15-009981	07/07/2015	H.SMITH
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792			



3RD ANGLE
PROJECTION
NOT TO
SCALE

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS IN MILLIMETRES
GENERAL TOL
LINEAR +/-0,25MM
ANGULAR +/- 1°

TITLE:

TINEL-LOCK BACKSHELL

ASSY USED ON:

MIL-C-5015 MS "V" THREAD END BELLS

TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING
AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD
INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.

DRAWING NO:
TXR15

DRAWING REV:
E

SHT
2



TABLE 1

										THESE DIMENSIONS APPLY IF BACKSHELL IS STAINLESS STEEL OR NICKEL ALUMINIUM BRONZE		
ORDER NUMBER	SHELL SIZE	A THREAD	ØB MAX	MAX ENTRY	C ±0,5	D ±0,5	W ±0,5	T ±0,5	E ±0,5	W ±0,5	T ±0,5	E ±0,5
03	8S & 10S	1/2-28UNEF	21,5	05	12,6	27,5	21,7	13,0	28,0	22,2	13,0	28,2
04	10SL, 12 & 12S	5/8-24UNEF	25,0	07	14,0	28,0	24,9	14,4	29,5	25,4	14,4	29,7
06	14 & 14S	3/4-20UNEF	28,0	08	15,0	29,0	27,9	15,9	31,0	28,4	15,9	31,2
08	16 & 16S	7/8-20UNEF	31,1	10	15,6	29,7	31,3	18,3	32,7	31,8	18,3	32,9
10	18	1-20UNEF	35,0	12	16,3	30,5	34,3	19,3	34,3	34,8	19,3	34,3
12	20 & 22	1 3/16-18UNEF	39,0	16	17,2	30,9	40,4	22,9	35,8	40,9	22,9	36,1
16	24 & 28	1 7/16-18UNEF	45,2	20	17,9	32,1	44,0	24,0	38,9	44,5	24,0	39,1
20	32	1 3/4-18UNS	54,9	24	24,3	32,1	50,3	27,3	42,8	50,8	27,3	42,8
24	36	2-18UNS	62,0	24	26,9	29,3	57,8	31,1	46,8	58,3	31,1	46,8
28	40	2 1/4-16UN	68,6	24	31,8	30,7	64,4	34,5	51,0	64,9	34,5	51,0

TABLE 2

										THESE DIMENSIONS APPLY IF BACKSHELL IS STAINLESS STEEL OR NICKEL ALUMINIUM BRONZE		
ENTRY SIZE	ØZ MIN	ØS	ØY ±0,3	ØK MAX	F ±0,5	G ±0,5	H ±0,5	M ±0,5	J ±0,5	H ±0,5	M ±0,5	J ±0,5
04	6,35	9,49 +/-0,04	14,00	NA	NA	NA	NA	NA	NA	NA	NA	NA
05	7,92	11,06 +/-0,04	15,50	NA	NA	NA	NA	NA	NA	NA	NA	NA
06	9,53	12,66 +/-0,04	17,10	21,0	12,5	27,5	24,0	15,5	27,95	24,3	17,2	28,2
07	11,10	14,21 +/-0,07	18,70	21,0	12,5	27,5	24,0	15,5	27,95	24,3	17,2	28,2
08	12,70	15,81 +/-0,07	20,30	24,5	13,1	28,0	27,0	17,0	29,45	28,3	19,4	29,7
10	15,88	18,96 +/-0,08	23,50	29,0	13,5	29,0	31,0	19,5	31,00	31,1	21,0	31,2
12	19,05	22,14 +/-0,08	26,70	32,5	14,5	29,7	34,0	21,0	32,70	34,2	22,8	32,9
14	22,23	25,30 +/-0,08	29,80	35,5	15,5	30,5	35,0	20,0	34,25	38,5	25,3	34,5
16	25,40	28,48 +/-0,08	33,00	37,0	16,1	30,9	38,0	21,5	35,80	40,7	26,1	36,1
18	28,58	31,65 +/-0,08	36,20	40,0	16,5	31,1	42,0	24,0	37,40	43,7	27,6	37,6
20	31,75	34,83 +/-0,08	39,40	43,5	17,0	32,1	45,0	25,5	38,90	46,4	29,1	39,1
22	34,93	37,98 +/-0,08	42,50	48,5	18,5	35,3	54,5	31,0	42,00	50,0	31,0	42,0
24	38,10	41,15 +/-0,08	45,70	52,1	21,9	38,1	58,0	33,0	46,00	53,5	33,0	46,0

If this document is printed it becomes uncontrolled. Check for the latest revision

DRAWN	K.WINCZURA	DATE	04/12/2014	 3RD ANGLE PROJECTION NOT TO SCALE	TITLE:				 Polamco			
CHECKED		DATE	04/12/2014							TINEL-LOCK BACKSHELL		
APPROVED	K.SHEPPARD	DATE	11/12/2014		ASSY USED ON:							
APPROVED	H.SMITH	DATE	07/07/2015							MIL-C-5015 MS "V" THREAD END BELLS		
REVISIONS												
LTR	DESCRIPTION	DATE	APPROVED									
D	REVISED PER ECO-15-002398	17/02/2015	H.SMITH									
E	REVISED PER ECO-15-009981	07/07/2015	H.SMITH									
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792				TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.				DRAWING NO:		DRAWING REV:		SHT
				TXR15				E		3		