

FAIRCHILD DIODES

DIODES

COMPUTER DIODES (BY ASCENDING t_{rr}) GLASS PACKAGE

Item	DEVICE NO.	t_{rr} ns Max	BV V Min	I_R nA Max	@	V_R V	V_F V Max	@	I_F mA	C pF Max	Package No.
1	FD700	0.70	30	50		20	1.1		50	1.0	DO-7
2	1N4376	0.75	20	100		10	1.1		50	1.0	DO-7
3	BAY82	0.75	15	100		12	1.0		20	1.3	DO-7
4	FD777	0.75	15	100		8.0	1.0		20	1.3	DO-7
5	1N5282	2.0	80	100		55	1.3		500	2.5	DO-35
6	1N4153	2.0	75	50		50	0.88		20	4.0	DO-35
7	1N4151	2.0	75	50		50	1.0		50	4.0	DO-35
8	1N4305	2.0	75	100		50	0.85		10	2.0	DO-35
9	BAY71	2.0	50	100		35	1.0		20	2.0	DO-35
10	1N4152	2.0	40	50		30	0.88		20	4.0	DO-35
11	1N4154	2.0	35	100		25	1.0		30	4.0	DO-35
12	1N914	4.0	100	25		20	1.0		10	4.0	DO-35
13	1N914A	4.0	100	25		20	1.0		20	4.0	DO-35
14	1N914B	4.0	100	25		20	1.0		100	4.0	DO-35
15	1N916	4.0	100	25		20	1.0		10	2.0	DO-35
16	1N916A	4.0	100	25		20	1.0		20	2.0	DO-35
17	1N916B	4.0	100	25		20	1.0		30	2.0	DO-35
18	1N4148	4.0	100	25		20	1.0		10	4.0	DO-35
19	1N4149	4.0	100	25		20	1.0		10	2.0	DO-35
20	1N4446	4.0	100	25		20	1.0		20	4.0	DO-35
21	1N4447	4.0	100	25		20	1.0		20	4.0	DO-35
22	1N4448	4.0	100	25		20	1.0		100	2.0	DO-35
23	1N4449	4.0	100	25		20	1.0		30	2.0	DO-35
24	1N3604	4.0	75	50		50	1.0		50	2.0	DO-35
25	1N3600	4.0	75	100		50	1.0		200	2.5	DO-35
26	FDH600	4.0	75	100		50	1.0		200	2.5	DO-35
27	1N3064	4.0	75	100		50	1.0		10	2.0	DO-35
28	1N4150	4.0	75	100		50	1.0		200	2.5	DO-35
29	1N4454	4.0	75	100		50	1.0		10	2.0	DO-35
30	BAX13	4.0	50	200		50	1.0		20	3.0	DO-35
31	BAY74	4.0	50	100		35	1.1		300	3.0	DO-35
32	FDH900	4.0	45	500		40	1.1		100	3.0	DO-35