





Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	title LPVCC SMT 2.3 TOP ENTRY ASSY, STACKABLE, WITH 0.64/.025 LOCATING FEATURES
ltr	ecn no	dr	date	linear	angular		
A	S00044	JPEH	3/21/00	linear	X.X±0.3/.XX±.01	projection MM/INCH	product family LPVCC
B	S00065	JPEH	4/25/00	linear	X.XX±0.13/.XXX±.005		
C	S05-0103	KBM	4/8/05	angles	X.XXX±0.051/.XXX±.0020	scale 10:1	code —
				dr	ANGLES ±2°		
				enrg	JPEH 4/25/00	size dwg no	sheet 1 of 2
				chr	JPEH 4/25/00		
				appd	KB MAH 4/8/05	A	63473
					JOEY NG 4/8/05		
sheet index	revision	C	C				
	sheet	1	2				

cage code
22526

STATUS: Released

Printed: Nov 27, 2010

ACAD


PDM: Rev:C

PRODUCT NO ⑥	POSITIONS	DIM. A	DIM. B	DIM. C
63473-X20	2 X 10	18,00/,709	19,74/,777	16,00/,630

CONTACT AREA PLATING OPTIONS
1 = 0,76um/30u" Au CONTACT AREA
3 = 0,38um/15u" Au CONTACT AREA

NOTES :

- 1 HOUSING MAT'L : HIGH TEMP PLASTIC.
- 2 TERMINAL MAT'L : BeCu.
- 3 TERMINAL RETENTION 0,5 Kg/1,1 Lbs.
- ④ SOLDERTAIL PLATING:
 - a) SOLDERTAIL OF P/N:63473-XXX IS TIN/LEAD PLATED.
 - b) SOLDERTAIL OF P/N:63473-XXXLF IS 100% MATTE TIN PLATED.
- 5 'V' CUT OPTIONAL - MANUFACTURING PROCESS OPTION.
- ⑥ PRODUCT DESCRIPTION CODE :
 XXXXX-XXXLF
 LEAD FREE ④ ⑨
 TOTAL POSITIONS
 CONTACT AREA PLATING
 BASE NUMBER
- 7 PACKAGING :
 - (a) XXXXX-XXX --- STD PACKAGING IN TUBE.
 - (b) XXXXX-XXXTR --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITH PICK-UP CAP (SEE FIG 1).
 - (c) XXXXX-XXXTRN --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITHOUT PICK-UP CAP.
- 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 255° C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- ⑨ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



RECOMMENDED PAD LAYOUT




FIG. 1
NOTE 7 (b)

CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com
litr	ecr no	dr	date	linear	angles		
C				X.X±0.3/.XX±.01	ANGLES ±2°	projection	title
				X.XX±0.13/.XXX±.005		MM/INCH	LPVCC SMT 2.3 TOP ENTRY ASSY, STACKABLE, WITH 0.64/.025 LOCATING FEATURES
				X.XXX±0.051/.XXX±.0020		scale	product family LPVCC
						1:1	code
				dr JPEH 4/25/00			size
				enrg JPEH 4/25/00			dwg no
				chr KB MAH 4/8/05			63473
				appd JOEY NG 4/8/05			sheet 2 of 2
sheet index	revision sheet						

cage code
22526

STATUS: Released

Printed: Nov 27, 2010

ACAD

PDM: Rev:C