

Section 17


Push Buttons and Operator Interface



16 mm XB6



22 mm XB4



30 mm Type K



30 mm Type SK




30 mm Type KX



Type KY Enclosure



Pendant Stations

Type B
Wall StationXVL
Compact LightType O
Compact LightType J
Compact Light

Indicating Banks

Type A
Foot Switch

22 and 30 mm Most Common Complete Operators

9001	,	30	X 4-X 5 22	t	17-2
t	t	t	h	t t	t
t . t t-t	-	-	t	t	h t
h			t .		

16 mm Push Buttons

XB6 16 mm Push Buttons,	t	th	,	t h t h	t	17-4
t	t	h	t	t	t- , h	
t		t				

22 mm Push Buttons

XB4 22 mm Push Buttons,	t	th	,	t h t h	t	17-15
t t	t	t	h			
XB5 22 mm	h	t	h X 4	t	t	17-34
t	t		t t h	t	/	
t	t					

30 mm Push Buttons

Class 9001 Type K	t	th /	t th t	t	t	17-55
t t	t	h	t	t	t	
Class 9001 Type SK	-	t	t th t	t		17-68
h h						
Class 9001 Type KX	t		t	t	t h t	17-87
t	t h	h h h	t			
h tt	t h t	t		t		
Class 9001 Type KY	t	t	t t		t	17-102
t	t					

Indicating Banks and Beacons

XVB	XVPI	t	t t	t	17-108
h		h	t	h h	
t	t	t	h t		
t	t	t	t	t	
t t	h		360	t	

Pendant Stations

h	t t t	t	h t	17-115
t	h	h t t	t BW	
XAC	t t h h	t SKYP	t	

Compact Pilot Lights

h	t P t h t	h	Type J	t h t, h t-t t	17-106
t t t t		t	h	Type O	
t	t	h	XVL	t	

Foot Switches

h	Type A	t	th	h	t	t	th h h	17-120
		t	t		t			

Rotary Cam Switches – A New Extended Offer


K10, K2 and K30–K150 Rotary Cam Switches.					t	,	t	17-122
P	th	th					t	
	th	10	t	h	h	150	th	

Control Stations & Enclosures


XAL	t	t t	-	t		17-95
h	t	t t	h	tt	t h t	h XB5
22	. XAP				t	
t	t	h	t			
Type B	t	t	t t t	1,2	3 tt	t
		t	t t t			

Push Buttons
Class 9001 Type K, SK—30 mm
Common Operators, Complete with Contact Blocks


BLACK—Start Push Buttons

Operator Style	Description	Contact Block	Type	Price	Legend Plate	Price
			1 13	\$54.	201	\$2.90
			1 13	54.	101 P	2.90

BLACK—Off-On Selector Switch

Operator Style	Description	Contact Sequence (Contact Block Included)	Type	Price	Legend Plate	Price
			11 13	\$64.	244	\$2.90
			11 13	64.	144 P	2.90

RED—120 Vac—On Pilot Light

Operator Style	Description	Type	Price	Legend Plate	Price
		P1 31	\$102.	203	\$2.90
		P1 31	102.	103 P	2.90

RED—120 Vac—On Push-To-Test Pilot Light

Operator Style	Description	Type	Price	Legend Plate	Price
					

BLACK—Start Push Buttons (flush head)

Operator Style	Description	Contact Block	Type	Price	Legend Plate	Price
X 4 _h t			X 4 21	\$17.50	2303	\$1.70
X 5 _l t			X 5 21	17.50	2303	1.70

BLACK—Off-On Selector Switch

Operator Style	Description	Contact Block	Type	Price	Legend Plate	Price
X 4 _h t			X 4 21	\$23.00	2367	\$1.70
X 5 _l t			X 5 21	23.00	2367	1.70

RED—120 Vac LED—On Pilot Light

Operator Style	Description	Light Module	Type	Price	Legend Plate	Price
X 4 _h t		120 ▼ ▲E	X 4 ▼ 4	\$32.40	2311	\$1.70
X 5 _l t		120 ▼ ▲E	X 5 ▼ 4	32.40	2311	1.70

RED—40 mm Mushroom Emergency Stop (Push-Pull)

Operator Style	Description	Contact Block	Type	Price	Legend Plate	Price
X 4 _h t			X 4 42	\$31.20	9330	\$1.70
X 5 _l t			X 5 42	31.20	9330	1.70

RED—Stop Push Buttons (extended head)

Operator Style	Description	Contact Block	Type	Price	Legend Plate	Price
X 4 _h t			X 4 ▲ 42	\$17.50	2304	\$1.70
X 5 _l t			X 5 ▲ 42	17.50	2304	1.70

Hand-Off-Auto Selector Switch

Operator Style	Description	Contact Block	Type	Price	Legend Plate	Price
X 4 _h t			X 4 33	\$31.10	2387	\$1.70
X 5 _l t			X 5 33	31.10	2387	1.70

GREEN—120 Vac LED—Off Pilot Light

Operator Style	Description	Light Module	Type	Price	Legend Plate	Price
X 4 _h t		120 ▼ ▲E	X 4 ▼ 3	\$32.40	2312	\$1.70
X 5 _l t		120 ▼ ▲E	X 5 ▼ 3	32.40	2312	1.70

RED—40 mm Mushroom Emergency Stop (Turn-To-Release)

Operator Style	Description	Contact Block	Type	Price	Legend Plate 60 mm Round	Price
X 4 _h t			X 4 542	\$50.00	9330	\$1.70
X 5 _l t			X 5 542	50.00	9330	1.70



E164353



▲ 44087
3211 03




E164353
2

t t , t #9001 0001.


Push Buttons—XB6 16 mm
Characteristics and Complete Devices

Characteristics


Table with 3 main sections: Environment, Electrical characteristics of LED pilot lights, and Electrical characteristics of contacts. It includes various technical specifications and standards.



XB6DW...B



XB6CE...B




XB6AF...B

Illuminated Push Buttons (12–24 Vac/Vdc LED included)
Complete Units with Quick Connectors/Solder Tabs


Large table detailing illuminated push button specifications. Columns include Type of Push, Type of Contact (N.O., N.C.), Color, Rectangular, Square, Round, and Price. Rows list various models and their configurations.

Note: Illuminated Push Buttons 120 Vac LED
12 24 V t . h V t (2) t . E : X 6 1B1 (h t 24 V, 1 . .)
X 6 1G1 .


t t , t #9001 0001.




XB6DD***B




XB6CD***B



XB6AD***B



XB6DG**B



XB6CG**B



XB6AG**B

Selector Switches (Switching Angle: Handle: 60°, Key: 70°)
Complete Units with Quick Connectors/Solder Tabs

Type of Operator	Type of Contact		Number and Type of Positions					Price
	N.O.	N.C.			Catalog Number			
	1	...	2- t		X 6 221	X 6 221	X 6 221	\$13.50
	1	1	2- t		X 6 225	X 6 225	X 6 225	17.10
			3- t		X 6 235	X 6 235	X 6 235	17.10
	2	...	3- t		X 6 233	X 6 233	X 6 233	17.10
Type of Operator	Type of Contact		Number and Type of Positions					Price
	N.O.	N.C.			Catalog Number			
	1	1	2- t		X 6 5	X 6 5	X 6 5	\$31.10
			2- t		X 6 5	X 6 5	X 6 5	31.10
			3- t		X 6 5	X 6 5	X 6 5	31.10
	2	...	3- t		X 6 3	X 6 3	X 6 3	31.10

1 t h t .

Selector Switch Sequence

2 Position Selector Switch			
		t t	▲
	X	1 . . (t h t)	
X		1 . . (t h t)	
	X	1 . .	
X		1 . .	

3 Position Selector Switch				
			t t	▲
		X	1 . . (t)	
X		X	2 . . parallel ()	
X			1 . . (h t)	
	X	X	1 . . (h t)	
X	X		1 . . (t)	
	X		2 . . series ()	

▲ h t h .

t t , t #9001 0001.



ZB6DW•




ZB6CE•



ZB6AF•



ZB6DV•



ZB6CV•



ZB6AV•

Heads for Illuminated Push Buttons
(To combine with complete bodies and contact blocks, see page 17-7)

Type of Push	Color				Price
		Rectangular	Square	Round	
Catalog Number					
h , t	h t	6 1	6 1	6 1	\$7.20
		6 3	6 3	6 3	
		6 4	6 4	6 4	
		6 5	6 5	6 5	
		6 6	6 6	6 6	
	5 ▲	6 9	6 9	6 9	8.20
	h t ■	6 0	6 0	6 0	6.20
h , t	h t	6 1	6 1	6 1	7.20
		6 3	6 3	6 3	
		6 4	6 4	6 4	
		6 5	6 5	6 5	
		6 6	6 6	6 6	
	5 ▲	6 9	6 9	6 9	8.20
	h t ■	6 0	6 0	6 0	6.20
E t , t	h t	6 E1	6 E1	6 E1	7.20
		6 E3	6 E3	6 E3	
		6 E4	6 E4	6 E4	
		6 E5	6 E5	6 E5	
		6 E6	6 E6	6 E6	
	5 ▲	6 E9	6 E9	6 E9	8.20
	h t ■	6 E0	6 E0	6 E0	6.20

▲ h t h h (h t, , , ,).
■ h tt t , 17-12.

Heads for Pilot Lights
(To combine with light modules, see page 17-7.)

Color				Price
	Rectangular	Square	Round	
	Catalog Number			
h t	6 ▼1	6 ▼1	6 ▼1	\$4.10
	6 ▼3	6 ▼3	6 ▼3	
	6 ▼4	6 ▼4	6 ▼4	
	6 ▼5	6 ▼5	6 ▼5	
	6 ▼6	6 ▼6	6 ▼6	
5 ◆	6 ▼9	6 ▼9	6 ▼9	5.10
h t ★	6 ▼0	6 ▼0	6 ▼0	3.10

◆ h t h h (h t, , , ,).
★ h t , 17-12.



ZB6DA•



ZB6CA•



ZB6AA•



ZB6AC•



ZB6AS834



ZB6AS934



ZB6Y7330

Heads for Push Buttons
 (To combine with complete bodies and contact blocks, see page 17-7.)

Type of Push	Color				Price
		Rectangular	Square	Round	
		Catalog Number			
h , t	h t	6 1	6 1	6 1	\$7.20
		6 2	6 2	6 2	
		6 3	6 3	6 3	
		6 4	6 4	6 4	
		6 5	6 5	6 5	
		6 6	6 6	6 6	
	6 ▲	6 9	6 9	6 9	8.20
h t ■	6 0	6 0	6 0	6.20	
E t , t		6 14	6 14	6 14	7.20

▲ t h h (h t , , , , ,).
 ■ h t t t , t , 17-12.

Mushroom Heads for Push Buttons (24 mm)

Shape of Head	Type of Push	Color of Cap	Catalog Number	Price
	t	h t	6 1	\$12.40
			6 2	
			6 3	
			6 5	
			6 6	

Mushroom Heads for Trigger Action Push Buttons (30 mm)♦

Shape of Head	Type of Push	Color of Cap	Catalog Number	Price
	-t -		6 834	\$24.80
			6 934	31.10

Circular Legends, 45 mm

Description	Color	Text	Catalog Number	Price
, 45			6 7001	\$1.70
		E t	6 7330	
		t '	6 7130	

♦ t h h t h t h t t t t t t t t h t .

t t , t #9001 0001.

Heads for Non-Illuminated Selector Switches▲◆
(To combine with complete bodies and contact blocks, see page 17-7.)

Number and Type of Positions	Color of Handle	Rectangular	Square	Round	Price
		Catalog Number			
Switching angle: maintained positions 60°, spring return positions 45°					
2- t			6 22	6 22	\$8.80
2- t			6 28■	6 28■	
3- t			6 23	6 23	
2- t t t			6 24	6 24	
3- t t t			6 25	6 25	
3- t h t t t			6 26	6 26	
3- t t t t			6 27	6 27	

▲ h 2 t t , h t t , 90°
◆ th t th h t 17-11.

Heads for Illuminated Selector Switches★△
(To combine with complete bodies and contact blocks, see page 17-7.)

Number and Type of Positions			Rectangular	Square	Round	Price
			Catalog Number			
Switching angle: maintained positions 60°, spring return positions 45°						
2- t			6 02	6 02	6 02	\$6.70
2- t			6 08 ▼	6 08 ▼	6 08 ▼	
3- t			6 03	6 03	6 03	
2- t t t			6 04	6 04	6 04	
3- t t t			6 05	6 05	6 05	
3- t h t t t			6 06	6 06	6 06	
3- t t t t			6 07	6 07	6 07	

★ h t (), h 2 t t ,
▼ th t t t , 90°
△ t th h t 17-11.

Handles for Illuminated Selector Switches


Description	Color	Catalog Number	Price
h t		6 1	
		6 3	
t t th □		6 4	\$2.10
		6 5	
		6 6	

Handles for Non-Illuminated Selector Switches


Description	Color	Catalog Number	Price
- t t t th		6 2	
		6 4	\$2.10

□ t h h h h () / t t t h t t (17-7).


Heads for Ronis Key Operated Selector Switches
 (To combine with complete bodies and contact blocks, see page 17-7.)



ZB6DG•



ZB6CG•



ZB6AG•

Number and Type of Positions		Key Withdrawal				Price
			Rectangular	Square	Round	
Catalog Number						
Switching angle: maintained positions 70°, spring return positions 45°						
2- t		h h t	6	6	6	\$22.80
		t t	6	6	6	
		h t	6	6	6	
2- t h t t		t t	6 	6 	6 	
3- t		 h h t	6	6	6	
		t t	6 E	6 E	6 E	
		 h h t t	6	6	6	
		h h t	6	6	6	
		3 t	6	6	6	
		 h h t h h	6	6	6	
3- t t t		h h t t	6	6	6	
		t t	6	6	6	
		h h t t	6 P	6 P	6 P	
3- t h t t		 h h t	6	6	6	
		t t	6	6	6	
		 h h t t	6	6	6	
3- t t t		t t	6	6	6	

\$22.80

l t h t .

Selector Switch Sequence (using contact block assemblies, page 17-7)

2 Position Selector Switch		
		t t ▲
	X	1 . . (t h t)
X		1 . . (t h t)
	X	1 . .
X		1 . .

3 Position Selector Switch			
			t t ▲
		X	1 . . (t)
X		X	2 . . parallel ()
X			1 . . (h t)
	X	X	1 . . (h t)
X	X		1 . . (t)
	X		2 . . series ()

▲ h t h .

t t , t #9001 0001.

Push Button Caps—Unmarked

Application	Color				Price
		Rectangular	Square	Round	
Catalog Number					
 I h t h tt h	h t	6 1	6 1	6 1	\$1.00
		6 3	6 3	6 3	
		6 4	6 4	6 4	
		6 5	6 5	6 5	
		6 6	6 6	6 6	
 I t t h tt h	h t	6 E1	6 E1	6 E1	1.00
		6 E3	6 E3	6 E3	
		6 E4	6 E4	6 E4	
		6 E5	6 E5	6 E5	
		6 E6	6 E6	6 E6	
 - t h tt	h t	6 1	6 1	6 1	1.00
		6 2	6 2	6 2	
		6 3	6 3	6 3	
		6 4	6 4	6 4	
		6 5	6 5	6 5	
	6 6	6 6	6 6	6 6	

Lens Caps

Application	Color				Price
		Rectangular	Square	Round	
Catalog Number					
P t h t	h t	6 ▼1	6 ▼1	6 ▼1	\$1.00
		6 ▼3	6 ▼3	6 ▼3	
		6 ▼4	6 ▼4	6 ▼4	
		6 ▼5	6 ▼5	6 ▼5	
		6 ▼6	6 ▼6	6 ▼6	

Standard Legend Plate (24 X 28 mm) for 8 X 21 mm Legend

Description	Background Color of Legend	Catalog Number	Price
I t t	...	6 20	\$1.00
I h t	h t	6 21	1.70
		6 22	1.70

8 x 21 mm Marked Legends (for 24 x 28 mm legend holder ZB6YD20)

Color	Marking	Catalog Number	Price
   h t t (t h) t	I t t	-I 6 2178	\$0.80
		I-II 6 2179	
		I- -II 6 2186	
		← → 6 2190	
	E h	- - 6 2387	
		↖ E 6 2314	
		6 2308	
		6 2305	
		↖ 6 2334	
		↖ E 6 2310	
		6 2312	
		6 2303	
		PE 6 2313	
		E E 6 2323	
		E▼E E 6 2306	
		I 6 2309	
		6 2311	
		P 6 2304	
		P 6 2307	

t t , t #9001 0001.

Push Button Caps—Marked



ZB6YD•10



ZB6YC•10



ZB6YA•10



ZB6YD•17



ZB6YD•19



ZB6YC•19




ZB6YA•19

Ink Marking Color: White on colored cap Black on white cap	Color				Price
		Rectangular	Square	Round	
		Catalog Number			
For non-illuminated push buttons					
0	h t	6 100	6 100	6 100	\$2.10
		6 200	6 200	6 200	
1	h t	6 101	6 101	6 101	
		6 201	6 201	6 201	
2	h t	6 102	6 102	6 102	
		6 202	6 202	6 202	
3	h t	6 103	6 103	6 103	
		6 203	6 203	6 203	
4	h t	6 104	6 104	6 104	
		6 204	6 204	6 204	
5	h t	6 105	6 105	6 105	
		6 205	6 205	6 205	
6	h t	6 106	6 106	6 106	
		6 206	6 206	6 206	
7	h t	6 107	6 107	6 107	
		6 207	6 207	6 207	
8	h t	6 108	6 108	6 108	
		6 208	6 208	6 208	
9	h t	6 109	6 109	6 109	
		6 209	6 209	6 209	
ON	h t	6 117	6 117	6 117	
		6 317	6 317	6 317	
OFF		6 224	6 224	6 224	
		6 424	6 424	6 424	
I	h t	6 111	6 111	6 111	
		6 311	6 311	6 311	
O		6 210	6 210	6 210	
		6 410	6 410	6 410	
R		6 226	6 226	6 226	
		6 626	6 626	6 626	
START	h t	6 140	6 140	6 140	
		6 340	6 340	6 340	
STOP		6 241	6 241	6 241	
		6 441	6 441	6 441	
II	h t	6 112	6 112	6 112	
		6 212	6 212	6 212	
III	h t	6 113	6 113	6 113	
		6 213	6 213	6 213	
+	h t	6 114	6 114	6 114	
		6 214	6 214	6 214	
-	h t	6 115	6 115	6 115	
		6 215	6 215	6 215	
UP	h t	6 127	6 127	6 127	
		6 227	6 227	6 227	
DOWN	h t	6 128	6 128	6 128	
		6 228	6 228	6 228	
CLOSE	h t	6 132	6 132	6 132	
		6 232	6 232	6 232	
↑	h t	6 119	6 119	6 119	
		6 219	6 219	6 219	
↓	h t	6 120	6 120	6 120	
		6 220	6 220	6 220	
→	h t	6 121	6 121	6 121	
		6 221	6 221	6 221	
←	h t	6 122	6 122	6 122	
		6 222	6 222	6 222	

t t , t #9001 0001.



ZB6Y009




ZB6Y905




ZB6Y002




ZB6Y003



ZB6Y001



ZB6YA001



ZB6YD001



ZB6Y005



ZB6Y007



ZB6Y7330

Accessories

Description	Application	Catalog Number	Price
	tt t t	6 009	\$1.00
th t t + t t	h th h	6 905	2.10
t t	h	6 016	2.10
t t t	t t	6 018	2.10
h t t	...	6 019	6.20
t	h t	6 002	1.00
t- t t t	t th , E t	6 003	1.00
t	h 22 t- t h h tt t h t	6 002	3.10
h	P t t t t tt h	6 001	1.70
P t t	h h tt th	6 001	8.30
	t h h tt th	6 001	8.30
t / t	t 100	6 004	0.21
	P t	6 005	2.10
, 2	h t t th t	6 007	3.10
l t , t 1 1/4	6 ▼	6 006	1.00
	12 ▼	6 012	1.00
	28 ▼▲	6 028	1.00
	110/230 ▼■	6 095	2.10
h	t 3 t t	6 017	0.52
h t	E h , h , , h , lt	X 2	52.00
h h t - h , 66 , 4 (297 t. 210)	P t h t , t	6 003	3.10
	P t h t ,	6 003	
	P t h t ,	6 003	
	l t h tt , t	6 013	
	l t h tt ,	6 013	
	l t h tt ,	6 013	

▲ 28 ▼ , 24 ▼ , 110/230 ▼.
■ 95 ▼ ,

Circular Legends, 45 mm

Description	Color	Text	Catalog Number	Price
, 45			6 7001	\$1.70
		E t	6 7330	
		t '	6 7130	

t t , t #9001 0001.

Environment

Degree of protection	t IE 529 t 50 22.2 .94	IP65, IP66, 1, 2, 3, 4, 4X, 12, 13, 14
Conforming to standards		IE 947-1, IE /E 60947-5-1, IE 947-5-4, E 60947-1, I 4520, 508, 22.2 .14
Product certifications	 E164353  44087 3211 03  E164353 2	t : 600; 600 h : 600; 600 X 4-P : 600; 300
	  	t t t t t

Electrical Characteristics of Operators and Contact Blocks

Cabling capacity	t IE 947-1	: 1 24 (0.22) h t 1 22 (0.34) h t 2 16 (1.5) h t 2 14 (2.5) h t h (P I I t 1) tt t4 5.5
Maximum Contact Block Usage	X 4/ 4	P h tt (-I t) 9 t th (-I t) 6 P h tt t (I t) 6 h , P h P (-I t) 6 h , P h P (I t) 4 h , -t - (-I t) 6 h , t (-I t) 4 P h - /P h - (-I t) 3 P h - /P h - (I t) 2
Rated operational characteristics Conforming to IEC/EN 60947-5-1	t t : t -15 t t : t -13	t 600: = 600 h = 1.2 t = 240 t = 3 t = 120 h = 6 t: 10 t 600: = 600 h = 0.1 t = 250 t = 0.27 t = 125 h = 0.55 t X 4-P : 300: = 125 h = 0.22 t = 250 t = 0.1
Electrical durability Conforming to IEC/EN 60947-5-1 Appendix C Operating rate 3600 operating cycles/hour. Load factor: 0.5	t t t 1 -15 t , t t t 1 -13 t ,	t t : 24 120 230 4 3 2 t h t : 24 120 230 3 1.5 1 t t : 24 110 0.5 0.2 t h t : 24 110 0.4 0.15

Electrical Characteristics of Light Modules

Cabling capacity	t IE 947-1	: 1 24 (0.22) h t 1 22 (0.34) h t 2 16 (1.5) h t
------------------	------------	--


Specific Characteristics of Protected LED® Light Modules Only

Voltage limits	t	24 19.2 t 30 21.6 t 26.4 ; 120 102 t 132 ; 240 195 t 264
Current consumption	t	24 / : 18 120 : 14 240 : 14

t t , t #9001 0001.



XB4BA31



XB4BA4322




XB4BP51



XB4BL42



XB4BC21



XB4BL845

Non-Illuminated Push Buttons, Momentary (screw clamp terminal connections)

Shape of Head	Type of Push	Type of Contact		Marking	Color of Cap	Catalog Number (Components)	Price
		N.O.	N.C.				
	h	1	...	...		X 4 21 (4 101 + 4 2)	\$17.50
						X 4 31 (4 101 + 4 3)	
						X 4 51 (4 101 + 4 5)	
						X 4 61 (4 101 + 4 6)	
		1	1	...		X 4 42 (4 102 + 4 4)	25.60
						X 4 25 (4 105 + 4 2)	
						X 4 35 (4 105 + 4 3)	
						X 4 45 (4 105 + 4 4)	
						X 4 55 (4 105 + 4 5)	
						X 4 65 (4 105 + 4 6)	
	h	1	...	$\begin{smallmatrix} I \\ (h\ t) \end{smallmatrix}$		X 4 3311 (4 101 + 4 331)	20.30
	h	...	1	$\begin{smallmatrix} O \\ (h\ t) \end{smallmatrix}$		X 4 4322 (4 102 + 4 432)	20.30
	$\begin{smallmatrix} h\ t \\ (h\ t) \end{smallmatrix}$	1	...	...		X 4 P21 (4 101 + 4 P2)	23.90
						X 4 P31 (4 101 + 4 P3)	
						X 4 P51 (4 101 + 4 P5)	
						X 4 P61 (4 101 + 4 P6)	
		...	1	...		X 4 P42 (4 102 + 4 P4)	23.90
	E t	...	1	...		X 4 442 (4 102 + 4 44)	17.50
		1	1	...		X 4 445 (4 105 + 4 44)	25.60
	$\begin{smallmatrix} h \\ 40\ h \end{smallmatrix}$	1	...	...		X 4 21 (4 101 + 4 2)	25.70

Two Button Push Buttons, Momentary (screw clamp terminal connections)

Shape of Head	Type of Push	Type of Contact		Degree of Protection	Catalog Number (Components)	Price
		N.O.	N.C.			
	$\begin{smallmatrix} h \\ (h\ t) \\ t \\ (h\ t) \end{smallmatrix}$	1	1	IP40	X 4 4845 (4 105 + 4 48434)	\$31.50

t t , t #9001 0001.

Non-Illuminated Emergency Stop Mushroom Head Push Buttons, Ø 40 mm (Red)
(screw clamp terminal connections)



XB4BT845



XB4BS9445



XB4BS542

Shape of Head	Type of Push	Type of Contact				Catalog Number (Components)	Price
		N.O.	N.C.				
	h - ▲	1	1			X 4 845 (4 105 + 4 84)	\$46.00
	t - t ▲	1	1			X 4 8445 (4 105 + 4 844)	75.00
	t ▲ (.455)	1	1			X 4 9445 (4 105 + 4 944)	75.00
	P h -	...	1			X 4 42 (4 102 + 4 4)	31.20
	-t -	...	1			X 4 542 (4 102 + 4 54)	50.00
	(.455)	...	1			X 4 142 (4 102 + 4 14)	67.00

▲ t h h t h t t t t t t t t h t .

Non-Illuminated Selector Switches and Key Switches (screw clamp terminal connections)



XB4BD33



XB4BJ33



XB4BG33

Shape of Head	Type of Operator	Type of Contact		Number and Type of Positions		Catalog Number (Components)	Price
		N.O.	N.C.				
	t ,	1	...	2- t		X 4 21 (4 101 + 4 2)	\$23.00
		1	1	2- t		X 4 25 (4 105 + 4 2)	31.10
		2	...	3- t		X 4 33 (4 103 + 4 3)	31.10
				3- t t t		X 4 53 (4 103 + 4 5)	33.80
	E t ,	1	...	2- t		X 4 21 (4 101 + 4 2)	23.00
		2	...	3- t		X 4 33 (4 103 + 4 3)	31.10
				3- t t t		X 4 53 (4 103 + 4 5)	33.80
	(.455)	1	...	2- t		X 4 21 (4 101 + 4 2)	55.80
						X 4 41 (4 101 + 4 4)	55.80
				2- t t t		X 4 61 (4 101 + 4 6)	55.80
		2	...	3- t		X 4 03 (4 103 + 4 0)	63.90
						X 4 33 (4 103 + 4 3)	63.90

h Ω t h t ()

t t , t #9001 0001.

Push Buttons—XB4 22 mm

Complete Devices



Telemecanique

www.SquareD.com

For the most up-to-date information

Pilot Lights with PROTECTED LED (screw clamp terminal connections)

Shape of Head	Supply Voltage	Color	Catalog Number (Components)	Price
	24 V /	h t	X 4 1 (4 1+ 4 013)	\$32.40
			X 4 3 (4 3+ 4 033)	
			X 4 4 (4 4+ 4 043)	
			X 4 5 (4 5+ 4 053)	
			X 4 6 (4 6+ 4 063)	
	110 120 V	h t	X 4 1 (4 1+ 4 013)	32.40
			X 4 3 (4 3+ 4 033)	
			X 4 4 (4 4+ 4 043)	
			X 4 5 (4 5+ 4 053)	
			X 4 6 (4 6+ 4 063)	

Pilot Lights for BA9s Bulb (screw clamp terminal connections)

Shape of Head	Supply Voltage	Color	Catalog Number (Components)	Price
Direct supply, for BA9s (incandescent, LED, neon) V ≤ 250 V, 2.4 W bulb (bulb not included)				
	≤ 250 V /	h t	X 4 61 (4 6+ 4 01)	\$23.10
			X 4 63 (4 6+ 4 03)	
			X 4 64 (4 6+ 4 04)	
			X 4 65 (4 6+ 4 05)	
Transformer type with 1.2 VA, 6 V secondary. BA9s incandescent bulb included				
	110 120 V 50/60	h t	X 4 31 (4 3+ 4 01)	53.00
			X 4 33 (4 3+ 4 03)	
			X 4 34 (4 3+ 4 04)	
			X 4 35 (4 3+ 4 05)	

Illuminated Push Buttons, Momentary (screw clamp terminal connections)

Shape of Head	Description	Type of Contact		Supply Voltage	Color of Push	Catalog Number (Components)	Price
		N.O.	N.C.				
Flush							
	Protected LED	1	1	24 ▼ /	h t	X 4 31 5 (4 0 15+ 4 313)	\$54.00
						X 4 33 5 (4 0 35+ 4 333)	
						X 4 34 5 (4 0 45+ 4 343)	
						X 4 35 5 (4 0 55+ 4 353)	
						X 4 36 5 (4 0 65+ 4 363)	
				110 120 ▼	h t	X 4 31 5 (4 0 15+ 4 313)	54.00
						X 4 33 5 (4 0 35+ 4 333)	
						X 4 34 5 (4 0 45+ 4 343)	
						X 4 35 5 (4 0 55+ 4 353)	
						X 4 36 5 (4 0 65+ 4 363)	
	2.4 t 9 t	1	1	≤250 ▼ /	h t	X 4 3165 (4 065+ 4 31)	44.90
						X 4 3365 (4 065+ 4 33)	
						X 4 3465 (4 065+ 4 34)	
						X 4 3565 (4 065+ 4 35)	
	1.2 ▼ , 6 ▼ 9 t	1	1	110 120 ▼ 50/60	h t	X 4 3135 (4 035+ 4 31)	74.00
						X 4 3335 (4 035+ 4 33)	
						X 4 3435 (4 035+ 4 34)	
						X 4 3535 (4 035+ 4 35)	
				230 240 ▼ 50/60	h t	X 4 3145 (4 045+ 4 31)	74.00
						X 4 3345 (4 045+ 4 33)	
						X 4 3445 (4 045+ 4 34)	
						X 4 3545 (4 045+ 4 35)	
Extended							
	Protected LED	1	1	24 ▼ /	h t	X 4 11 5 (4 0 15+ 4 113)	51.40
						X 4 13 5 (4 0 35+ 4 133)	
						X 4 14 5 (4 0 45+ 4 143)	
						X 4 15 5 (4 0 55+ 4 153)	
						X 4 16 5 (4 0 65+ 4 163)	
				110 120 ▼	h t	X 4 11 5 (4 0 15+ 4 113)	51.40
						X 4 13 5 (4 0 35+ 4 133)	
						X 4 14 5 (4 0 45+ 4 143)	
						X 4 15 5 (4 0 55+ 4 153)	
						X 4 16 5 (4 0 65+ 4 163)	

t t , t #9001 0001.

Non-Illuminated Operators, Momentary—Unmarked

Shape of Head	Type of Push	Color of Cap	Catalog Number	Price
	h, h t ▲	...	4 0	\$5.50
	h, h t 6	h t	4 9	6.50
	h	h t	4 1	6.50
			4 2	
			4 3	
			4 4	
			4 5	
			4 6	
	h h t t ■	h t	4 8	8.00
			4 18	
			4 38	
			4 48	
			4 58	
	t ()	h t	4 68	12.90
			4 P1	
			4 P2	
			4 P3	
			4 P4	
			4 P5	
	t () ■	h t	4 P6	14.50
			4 P18	
			4 P38	
			4 P48	
			4 P58	
	E t	h t	4 P68	6.50
			4 I1	
			4 I2	
			4 I3	
			4 I4	
			4 I5	
		h t	4 I6	17.50
			4 16	
			4 26	
			4 36	
			4 46	
			4 56	
			4 66	

▲ t t , 17-31.
■ t t , 17-31.

Non-Illuminated Operators, Momentary—Premarked

Shape of Head	Type of Push	Marking Text	Color	Color of Cap	Catalog Number	Price
	h	I	h t	h t	4 331	\$9.30
			h t	h t	4 131	
			h t	h t	4 333	
			h t	h t	4 133	
			h t	h t	4 341	
			h t	h t	4 141	
		E E	h t		4 222	
			h t		4 245	
			h t		4 432	
			h t		4 232	
		P	h t		4 434	
			h t		4 234	
			h t		4 435	
			h t		4 235	
	E t	↑ ◆	h t	h t	4 334	9.30
			h t		4 335	
			h t		4 I432	
			h t		4 I232	
		P	h t		4 I434	
			h t		4 I234	
			h t		4 I435	
			h t		4 I235	

◆ t - , t t 4 t : ↑, ↓, ← or → t t , t #9001 0001.



ZB4BC24



ZB4BC2



ZB4BR2



ZB4BH02



ZB4BA8134



ZB4BL8312



ZB4BL9312

Mushroom Heads, Momentary

Shape of Head	Diameter of Head	Color of Head	Catalog Number	Price
	30		4 24	\$14.70
			4 34	
			4 44	
			4 54	
			4 64	
	40		4 2	14.70
			4 3	
			4 4	
			4 5	
			4 6	
	60		4 2	17.50
			4 3	
			4 4	
			4 5	
			4 6	

Non-Illuminated Push-on/Push-off Operators

Shape of Head	Type of Push	Color of Push	Catalog Number	Price
	h	h t	4 01	\$8.80
			4 02	
			4 03	
			4 04	
			4 05	
			4 06	
	E t	h t	4 1	8.80
			4 2	
			4 3	
			4 4	
			4 5	
			4 6	

Two Head Operators, Momentary

Shape of Head	Description	Color of Pushers	Degree of Protection▲	Catalog Number	Price
No Marking					
	h		IP40	4 8134	\$10.40
			IP66	4 9134	18.60
		h t	IP40	4 8112	10.40
			IP66	4 9112	18.60
	h t		IP40	4 8334	10.40
			IP66	4 9334	18.60
		h t	IP40	4 8312	10.40
			IP66	4 9312	18.60
Premarked					
	(h l)		IP40	4 8234	12.40
			IP66	4 9234	20.70
		h t	IP40	4 8212	12.40
			IP66	4 9212	20.70
	(h l) (t)		IP40	4 8434	12.40
			IP66	4 9434	20.70
		h t	IP40	4 8412	12.40
			IP66	4 9412	20.70

▲ IP66 t t ().

t t , t #9001 0001.



ZB4BS834



ZB4BT4



ZB4BS64



ZB4BS74

Mushroom Heads for Maintained Push Buttons

Shape of Head	Type of Push	Diameter of Head	Color	Catalog Number	Price
	P h - t ■	40		4 84	\$26.90
	-t - t ■	30		4 834	56.00
		40		4 844	56.00
	(.455)▲■		E	4 84430	59.00
		30		4 934	56.00
		40		4 944▲	56.00
	P h -	60		4 964	56.00
		40		4 2	20.20
		60		4 4	20.20
	-t -	40		4 X2	23.00
				4 X4	23.00
		30		4 42	39.00
				4 44	39.00
		40		4 52	39.00
				4 54	39.00
			E	4 5430	42.40
				4 55	39.00
	(.455)▲		t t	4 5550	42.40
		60		4 62	44.80
				4 64	44.80
		30		4 72	56.00
				4 74	56.00
		40		4 12	56.00
				4 14▲	56.00
		60		4 22	56.00
				4 24	56.00

▲ h .421E: h 12 t h t .
 .458 : h 10 t h t .
 .520E: h 14 t h t .
 .3131 : h 20 t h t .
 E h t t h h 40 t h h t h t t t t t h t t h .421E : 4 94412.
 ■ t t h h 40 t h h t h t t t t t h t t h .421E t .



ZBY9330

Circular Legends for Emergency Stop Mushroom Heads (yellow background)

Diameter	Text	Catalog Number	Price
60		9101	\$1.70
	E E E P	9330	
90		8101	
	E E E P	8330	

t t , t #9001 0001.

Push Buttons—XB4 22 mm
Selector Switches



ZB4BD4
Standard Lever



ZB4BJ3
Extended Lever

Non-Illuminated Selector Switches ■◆

Color▲	Number and Type of Positions				Price
			Standard Lever	Extended Lever	
	Catalog Number				
	2- t		4 2	4 2	\$12.00
	2- h tt t		4 4	4 4	14.70
	3- t		4 3	4 3	12.00
	3- t t t		4 5	4 5	14.70
	3- tt t		4 7	4 7	14.70
	3- h tt t		4 8	4 8	14.70

▲ , h t h t : 01 h t , 03 , 04 , 05 , 06 (E : 4 204).

Non-Illuminated Key Switches■

Shape of Head	Type of Operator	Number and Type of Positions	Catalog Number	Price
	(.455)★	2- t		4 2
				4 4
		2- h tt t		4 6
		3- t		4 0
				4 3
				4 03
				4 5
				4 9
				4 09
		3- tt t		4 1
		3- t t t		4 7
		3- t t h tt		4 8
				4 08
				58.00



ZB4BG8



h t t t h t t t (.) t t
◆ t t th
★ h
.421E: h 12 t h t
.458 : h 10 t h t
.520E: h 14 t h t
.3131 : h 20 t h t
E t : h t : 4 212. h h .421E 2 t t , t th , h h h h


Selector Switch Sequence (using contact block assemblies, page 17-27; or complete bodies, page 17-27.)

2 Position Selector Switch		
		t t ▼
	X	1 . . (t h t)
X		1 . . (t h t)
	X	1 . .
X		1 . .

3 Position Selector Switch			
			t t ▼
X			1 . . (t)
	X		2 . . series ()
		X	1 . . (h t)
X	X		1 . . (h t)
	X	X	1 . . (t)
X		X	2 . . parallel ()

▼ h t h .

t t , t #9001 0001.



ZB4BD922

Potentiometer Operator (with Mounting Collar)

Shape of Head	Description	Application	Catalog Number	Price
	h t t t h h t h 1.73 t 1.97 . (44 t 50) (t t t t)	h t 0.25 . (6.35)	4 922	\$71.00
		h t 0.24 . (6)	4 912	



XD4PA12

Joystick Controllers (54 mm, Extended Operating Shaft) ▲

Description	Contact Operation	Action	Catalog Number	Price
2 t	1 t 1 . . t t t	t	X 4P 12	\$125.00
		t	X 4P 22	
4 t	1 t 1 . . t t t	t	X 4P 14	158.00
		t	X 4P 24	

▲ It t t t t t t E10• () E20• ().

Legends for Joystick Controllers

Description	For use with	Color	Catalog Number	Price
	2 t		2201	\$1.70
		h t	2401	
	4 t		4201	
		h t	4401	



ZB4BD28

Two Position Toggle Switch

Shape of Head	Color	Type of Positions	Catalog Number	Price
		t	4 28	\$23.30
		t	4 48	



XB4BA8•1

Reset Operators, Flush, Adjustable Shaft

Shape of Head	Travel		Actuation Distance		Color	Catalog Number	Price
	IN	mm	IN	mm			
	0.39	10	0.24 0.63	6 16		X 4 821	\$13.70
						X 4 841	
						X 4 861	
			0.63 1.02	16 26		X 4 822	13.70
						X 4 842	
						X 4 862	
	0.55	14	1.18 5.12	30 130		X 4 921	16.40
						X 4 941	
						X 4 961	
			5.12 10.12	130 257		X 4 922	20.50
						X 4 942	
						X 4 962	

t t , t #9001 0001.

Heads for Momentary Illuminated Push Buttons

Shape of Head	Type of Push	Color	Catalog Number	Price
Only use with PROTECTED LED® light modules				
	h	h t	4 313	\$9.30
			4 333	
			4 343	
			4 353	
			4 363	
	h h t	h t	4 513	15.50
			4 533	
			4 543	
			4 553	
			4 563	
	h t	h t	4 18	8.00
			4 38	
			4 48	
			4 58	
			4 68	
	E t	h t	4 113	6.50
			4 133	
			4 143	
			4 153	
			4 163	
	h (40)		4 413	14.70
			4 433	
			4 443	
			4 453	
			4 463	

Only use with light modules for a BA9s incandescent bulb, neon or LED

	h	h t	4 31	9.30
			4 33	
			4 34	
			4 35	
			4 36	
			4 37	
	E t	h t	4 11	6.50
			4 13	
			4 14	
			4 15	
			4 16	
			4 17	

Heads for Maintained Illuminated Push Buttons

Shape of Head	Type of Push	Color of Lens	Catalog Number	Price
Only use with PROTECTED LED light modules				
	P h / P h (40)		4 613	\$23.00
			4 633	
			4 643	
			4 653	
			4 663	

Illuminated Push-on/Push-off Operators

Shape of Head	Type of Push	Color of Lens	Catalog Number	Price
Only use with PROTECTED LED light modules				
	h	h t	4 013	\$12.40
			4 033	
			4 043	
			4 053	
			4 063	
	E t	h t	4 13	9.80
			4 33	
			4 43	
			4 53	
			4 63	

t t , t #9001 0001.



ZB4BW812743



ZB4BW823743



ZB4BW841723



ZB4BK1343

Two Button with Clear Pilot Light, Momentary (IP40) ▲

Shape of Head	Description	Color of Pushers	Catalog Number	Price
Only use with PROTECTED LED® light modules (PROTECTED LED determines pilot light color)				
	1 h 1 t t h t 1 h		4 812743	\$14.50
			4 813743	
		h t	4 811723	
	1 h 1 t t h t 1 t		4 832743	14.50
			4 833743	
		h t	4 831723	
Only use with PROTECTED LED light modules (PROTECTED LED determines pilot light color)—premarked				
	1 h (l) 1 t t h t 1 h ()		4 822743	16.60
			4 823743	
		h t	4 821723	
	1 h (l) 1 t t h t 1 t ()		4 842743	16.60
			4 843743	
		h t	4 841723	

▲ IP66 t t , t t 008, 17-33.

Illuminated Selector Switches, Standard Lever

Shape of Head	Number and Type of Positions		Catalog Number ■	Price
Only use with PROTECTED LED light modules				
	2- t		4 12 3	\$17.50
	2- t h t t t		4 14 3	25.70
	3- t		4 13 3	17.50
	3- t t t		4 15 3	25.70
	3- t h t t t		4 18 3	25.70
	3- t t t t		4 17 3	25.70

■ t : 1 h t , 3 , 4 , 5 , 6 .

Selector Switch Sequence (using contact block assemblies, page 17-27; or complete bodies, page 17-27.)

2 Position Selector Switch			
		t t ♦	
	X	1 . . (t h t)	
X		1 . . (t h t)	
	X	1 . .	
X		1 . .	

3 Position Selector Switch			
			t t ♦
X			1 . . (t)
	X		2 . . series ()
		X	1 . . (h t)
X	X		1 . . (h t)
	X	X	1 . . (t)
X		X	2 . . parallel ()

♦ h t h t .

t t , t #9001 0001.



ZB4BZ101

Contact Blocks (Mounting Collar with Contact Blocks)

Description	Type of Contact		Catalog Number	Price
	N.O.	N.C.		
t t	1	...	4 101	\$11.00
	...	1	4 102	11.00
	2	...	4 103	19.10
	...	2	4 104	19.10
	1	1	4 105	19.10
	1	2	4 141	27.30

▲ - t 3 t h h t E : 4 1013 (- t 1 0.250" 2 0.110")
 ■ t t 9 t h h t (E : 4 1029).
 ♦ E t t h t t t
 ★ E t t h t t t t t

Complete Bodies (Mounting Collar + Single Contact Block + Light Module with PROTECTED LED)

Light Source	Type of Contact ▼		Color	Supply Voltage		Price
	N.O.	N.C.		24 Vac/dc	110–120 Vac	
				Catalog Number		

Screw clamp terminal connections

Protected
LED

	1	...	h t	4 0 11	4 0 11	\$36.70
				4 0 31	4 0 31	
				4 0 41	4 0 41	
				4 0 51	4 0 51	
				4 0 61	4 0 61	
	...	1	h t	4 0 12	4 0 12	36.70
				4 0 32	4 0 32	
				4 0 42	4 0 42	
				4 0 52	4 0 52	
				4 0 62	4 0 62	
	2	...	h t	4 0 13	4 0 13	44.90
				4 0 33	4 0 33	
				4 0 43	4 0 43	
				4 0 53	4 0 53	
				4 0 63	4 0 63	
	1	1	h t	4 0 15	4 0 15	44.90
				4 0 35	4 0 35	
				4 0 45	4 0 45	
				4 0 55	4 0 55	
				4 0 65	4 0 65	

▼ tt h t t t , 17-28.

Mounting Collar, Contact Block and Light Module (with screw clamp terminal connections) Δ

Supply	Light Source	Supply Voltage	Type of Contact Δ		Color of Light Source	Catalog Number	Price
			N.O.	N.C.			

Screw clamp terminal connections

t	9 2.4 t □	≤ 250 ▼ /	1	...	...	4 061	\$27.40
			...	1	...	4 062	27.40
			2	...	...	4 063	35.60
			1	1	...	4 065	35.60
1.2 ▼ , 6 ▼ t	9 t	110 120 ▼ 50/60	1	...	...	4 031	57.00
			1	1	...	4 035	65.00
		230 240 ▼ 50/60	1	...	...	4 041	57.00
			1	1	...	4 045	65.00
		440 480 ▼ 60	1	...	...	4 081	57.00
			1	1	...	4 085	65.00

△	tt	h	t	t t	,	17-28.
□		t	.			17-32.



ZB4B06•



ZB4BW0•5

t t t #9001 0001.

Electrical Components

For use with	Catalog Number	Price
E t (t t h t)	4 009	\$2.70

Description	Type of Contact		Catalog Number	Price
	N.O.	N.C.		
t t t ▲■	1	...	E101	\$8.20
	...	1	E102	8.20
t t t ▲■	2	...	E203	16.60
	...	2	E204	16.60
	1	1	E205	16.60
(t t t t t) ♦	1	...	E1016	16.40
	...	1	E1026	16.40

▲ - t 3 t h h t E : E1013 (- t 1 0.250" 2 0.110").
 ■ t t t t t 9 t h h t (E : E1029).

Description	Supply Voltage	Color of Light Source	Catalog Number	Price
Protected[®] LED	12 ▼ /	h t	▼ 1	\$25.90
			▼ 3	
			▼ 4	
			▼ 5	
			▼ 6	
	24 ▼ /	h t	▼ 1	25.90
			▼ 3	
			▼ 4	
			▼ 5	
			▼ 6	
	110 120 ▼	h t	▼ 1	25.90
			▼ 3	
			▼ 4	
			▼ 5	
			▼ 6	
	24 120 ▼ /	h t	▼ 1	25.90
			▼ 3	
			▼ 4	
			▼ 5	
		▼ 6		
230 240 ▼	h t	▼ 1	25.90	
		▼ 3		
		▼ 4		
		▼ 5		
		▼ 6		
2.4 t . 9 t	≤250 ▼ /	...	▼6	16.60
h t Protected[®] LED	12 ▼ /	h t	▼ 1	33.60
			▼ 3	
			▼ 4	
			▼ 5	
			▼ 6	
	24 ▼ /	h t	▼ 1	33.60
			▼ 3	
			▼ 4	
			▼ 5	
			▼ 6	
	48 120 ▼	h t	▼ 1	33.60
			▼ 3	
			▼ 4	
		▼ 5		
		▼ 6		

★	E	t		t	h	t		t	t		.	t		t	.
▼	E	t		t	h	t	-	t			t			t	.

t t , t #9001 0001.


Standard (30 x 40 mm) Legend Plates for 8 x 27 mm Legends▲

Description	Legend		Catalog Number	Price
	Color	Text		
h t	...	...	32	\$1.00
h ()	h t	...	2101 4101	1.70
(t E) 2 11 h t ()	h t	h t h t	2002 2004 4001 4005	7.10
h t t	■	() () I II -I I-II I- -II	2146 2931 2147 2148 2178 2179 2186	1.70
h E h	■	- - - E E E E E P - E - - I E - PE P E E E () E E () E E E I P P- P	2115 2364 2385 2314 2308 2330 2328 2305 2371 2316 2387 2321 2382 2310 2312 2367 2311 2313 2326 2323 2322 2306 2309 2334 2327 2303 2304 2366 2307	1.70

▲ 17-30.
 ■ t t t : h t t t . t t : h t t t (h) .

Standard (30 x 50 mm) Legend Plates for 18 x 27 mm Legends

Description	Color	Catalog Number	Price
h t t	...	33	\$1.00
h t	h t	6101 6102	1.70



t t , t #9001 0001.

Push Buttons—XB4 22 mm
Legend Plates, Inserts Only

Marked Legends for 8 x 27 mm (for 30 x 40 mm legend holders ZBZ32)

Color	Marking	Text	Catalog Number	Price
		()	02146	
	I t t			\$0.83



▲ t t t : h t tt . t t : h t tt (h).

Accessories

Description	Application	Color	Catalog Number	Price
	E 40 t t h h : X 4 8 X 4 8 X 4 9 4 8 4 8 4 9	h P t	1600	\$54.00
			1602	
			1604	
			1605	
			1606	
			1606	
P t ■	E 40 t		4 1905	12.90
	E 40 t		4 2005	
P	h tt		4 62	16.40
			4 64	
t t	h tt 4 • tt h t h		4 011	8.30
h t t ▲	22 t t		4 3	5.50
P t h t t t	22 t t		5 3	5.50

▲ t 4 009 / t t 0106 9802 8/03. 17-28.

BA9s Bulbs and Associated Accessories

Description	Characteristics	Catalog Number	Price
(9) t l t	6 V, 1.2	1 006	\$5.50
	12 V, 2	1 E012	
	24 V, 2	1 E024	
	120 130 V, 2.4	1 E130	
	120 130 V	1 110	7.60
	230 240 V	1 220	
t t		X X13	5.50
1 t h t t	l t h tt tt h h h	8	3.10
P (5) t	h (P l l t 1)	4 905	25.90
t t	t 22 h tt 30	41	5.20

Replacement Keys for Emergency Stop Push Buttons and Selector Switches

Description	Key Number	Catalog Number	Price
t 2	455	455	\$5.50
	421E	421E	
	458	458	
	520E	520E	
	3131	3131	

Degree of protection	t	IE	529		
	t	1,50	22.2	.94	

Conforming to standards

Product certifications

Electrical Characteristics of Operators and Contact Blocks

Cabling capacity	t IE 947-1
-------------------------	------------

Maximum Contact Block Usage	X 5/ 5
-----------------------------	--------

Rated operational characteristics
Conforming to
IEC/EN 60947-5-1

IP65, h t t
IP66, t h tt h

1, 2, 3, 4, 4X, 12, 13, h t t

IE 947-1, IE /E 60947-5-1, IE 947-5-4,
E 60947-1, I 4520,
A 508, 22.2 .14

t t t h t : 600; 600
A h t t t h t : 600; 600
I X 4-P : 600; 300

t t t t t h t

$$\begin{array}{ccccccc}
 : & 1 & 24 & (0.22) & 2 & h & t \\
 : & 1 & 22 & (0.34) & 2 &) & \\
 : & 2 & 16 & (1.5) & 2 & h & \\
 : & 2 & 14 & (2.5) & 2 & h & t \\
 & & & (P & l & \downarrow t & 1) \\
 P & h & tt & (& -l & t &) \\
 & & & t & th & (& -l & t &) \\
 P & h & tt & & t & (l & t &) \\
 & h & , & P & h & P & (& -l & t &) \\
 & h & , & P & h & P & (l & t &) \\
 & h & , & -t & - & (& -l & t &) \\
 & h & , & & t & (& -l & t &) \\
 P & h & - & /P & h & - & (& -l & t &) \\
 P & h & - & /P & h & - & (l & t &) \\
 & t & 600: & =600 \blacktriangledown & & =1.2 & h & =240 \blacktriangledown & & =3 \\
 & t & =120 \blacktriangledown & & h & =6 & & t & 10
 \end{array}$$



XB5AA31




XB5AA4322




XB5AP51



XB5AL42



XB5AC21



XB5AL845

Non-Illuminated Push Buttons, Momentary (screw clamp terminal connections)

Shape of Head	Type of Push	Type of Contact		Marking	Color of Cap	Catalog Number (Components)	Price
		N.O.	N.C.				
	h	1	...	...		X 5 21 (5 101 + 5 2)	\$17.50
						X 5 31 (5 101 + 5 3)	
						X 5 51 (5 101 + 5 5)	
						X 5 61 (5 101 + 5 6)	
		1	1	...		X 5 42 (5 102 + 5 4)	17.50
						X 5 25 (5 105 + 5 2)	
						X 5 35 (5 105 + 5 3)	
						X 5 45 (5 105 + 5 4)	
	h	1	...	(h t)		X 5 3311 (5 101 + 5 331)	20.30
						X 5 4322 (5 102 + 5 432)	
	h	1	...	(h t)		X 5 P21 (5 101 + 5 P2)	23.90
						X 5 P31 (5 101 + 5 P3)	
						X 5 P51 (5 101 + 5 P5)	
						X 5 P61 (5 101 + 5 P6)	
	E t	1	1	...		X 5 P42 (5 102 + 5 P4)	23.90
						X 5 442 (5 102 + 5 44)	
	h	1	...	...		X 5 445 (5 105 + 5 44)	25.60
						X 5 21 (5 101 + 5 2)	
	h	1	...	...		X 5 21 (5 101 + 5 2)	25.70

Two Button Push Buttons, Momentary (screw clamp terminal connections)

Shape of Head	Type of Push	Type of Contact		Degree of Protection	Catalog Number (Components)	Price
		N.O.	N.C.			
	(h h) (t h)	1	1	IP40	X 5 845 (5 105 + 5 8434)	\$31.50

t t , t #9001 0001.

Non-Illuminated Emergency Stop Mushroom Head Push Buttons, Ø 40 mm (Red)
(screw clamp terminal connections)

Shape of Head	Type of Push	Type of Contact		Catalog Number (Components)	Price
		N.O.	N.C.		
	h - ▲	1	1	X 5 845 (5 105 + 5 84)	\$46.00
	t - t - ▲	1	1	X 5 8445 (5 105 + 5 844)	75.00
	t (.455)▲	1	1	X 5 9445 (5 105 + 5 944)	75.00
	P h -	...	1	X 5 42 (5 102 + 5 4)	31.20
	-t -	...	1	X 5 542 (5 102 + 5 54)	50.00
	(.455)	...	1	X 5 142 (5 102 + 5 14)	67.00

▲ t h h t h t t t t t t t t h t .

Non-Illuminated Selector Switches and Key Switches (screw clamp terminal connections)

Shape of Head	Type of Operator	Type of Contact		Number and Type of Positions		Catalog Number (Components)	Price
		N.O.	N.C.				
	t ,	1	...	2- t		X 5 21 (5 101 + 5 2)	\$23.00
		1	1	2- t		X 5 25 (5 105 + 5 2)	31.10
		2	...	3- t		X 5 33 (5 103 + 5 3)	31.10
				3- t t t		X 5 53 (5 103 + 5 5)	33.80
	E t ,	1	...	2- t		X 5 21 (5 101 + 5 2)	23.00
		2	...	3- t		X 5 33 (5 103 + 5 3)	31.10
				3- t t t		X 5 53 (5 103 + 5 5)	33.80
	(.455)	1	...	2- t		X 5 21 (5 101 + 5 2)	55.80
						X 5 41 (5 101 + 5 4)	55.80
				2- t t t		X 5 61 (5 101 + 5 6)	55.80
		2	...	3- t		X 5 03 (5 103 + 5 0)	63.90
						X 5 33 (5 103 + 5 3)	63.90

h Ω t h t ()


t t , t #9001 0001.



XB5AVB1



XB5AV63



XB5AV34

Pilot Lights with PROTECTED LED (screw clamp terminal connections)

Shape of Head	Supply Voltage	Color	Catalog Number (Components)	Price
	24 V /	h t	X 5 1 (5 1+ 5 013)	\$32.40
			X 5 3 (5 3+ 5 033)	
			X 5 4 (5 4+ 5 043)	
			X 5 5 (5 5+ 5 053)	
			X 5 6 (5 6+ 5 063)	
	110 120 V	h t	X 5 1 (5 1+ 5 013)	32.40
			X 5 3 (5 3+ 5 033)	
			X 5 4 (5 4+ 5 043)	
			X 5 5 (5 5+ 5 053)	
			X 5 6 (5 6+ 5 063)	

Pilot Lights for BA9s Bulb (screw clamp terminal connections)

Shape of Head	Supply Voltage	Color	Catalog Number (Components)	Price
Direct supply, for BA9s (incandescent, LED, neon) V ≤ 250 V, 2.4 W bulb (bulb not included)				
	≤ 250 V /	h t	X 5 61 (5 6+ 5 01)	\$23.10
			X 5 63 (5 6+ 5 03)	
			X 5 64 (5 6+ 5 04)	
			X 5 65 (5 6+ 5 05)	
Transformer type with 1.2 VA, 6 V secondary. BA9s incandescent bulb included				
	110 120 V 50/60	h t	X 5 31 (5 3+ 5 01)	53.00
			X 5 33 (5 3+ 5 03)	
			X 5 34 (5 3+ 5 04)	
			X 5 35 (5 3+ 5 05)	

Illuminated Push Buttons, Momentary (screw clamp terminal connections)

Shape of Head	Description	Type of Contact		Supply Voltage	Color of Push	Catalog Number (Components)	Price
		N.O.	N.C.				
Flush							
	Protected LED	1	1	24 ▼ /	h t	X 5 31 5 (5 0 15+ 5 313)	\$54.00
					X 5 33 5 (5 0 35+ 5 333)		
					X 5 34 5 (5 0 45+ 5 343)		
					X 5 35 5 (5 0 55+ 5 353)		
					X 5 36 5 (5 0 65+ 5 363)		
				110 120 ▼	h t	X 5 31 5 (5 0 15+ 5 313)	54.00
					X 5 33 5 (5 0 35+ 5 333)		
					X 5 34 5 (5 0 45+ 5 343)		
					X 5 35 5 (5 0 55+ 5 353)		
					X 5 36 5 (5 0 65+ 5 363)		
	2.4 t 9 not	1	1	≤ 250 ▼ /	h t	X 5 3165 (5 065+ 5 31)	44.90
					X 5 3365 (5 065+ 5 33)		
					X 5 3465 (5 065+ 5 34)		
					X 5 3565 (5 065+ 5 35)		
	t 1.2 ▼ , 6 ▼ 9 t	1	1	110 120 ▼ 50/60	h t	X 5 3135 (5 035+ 5 31)	74.00
					X 5 3335 (5 035+ 5 33)		
					X 5 3435 (5 035+ 5 34)		
					X 5 3535 (5 035+ 5 35)		
				230 240 ▼ 50/60	h t	X 5 3145 (5 045+ 5 31)	74.00
					X 5 3345 (5 045+ 5 33)		
					X 5 3445 (5 045+ 5 34)		
					X 5 3545 (5 045+ 5 35)		
Extended							
	Protected LED	1	1	24 ▼ /	h t	X 5 11 5 (5 0 15+ 5 113)	\$51.40
					X 5 13 5 (5 0 35+ 5 133)		
					X 5 14 5 (5 0 45+ 5 143)		
					X 5 15 5 (5 0 55+ 5 153)		
					X 5 16 5 (5 0 65+ 5 163)		
				110 120 ▼	h t	X 5 11 5 (5 0 15+ 5 113)	51.40
					X 5 13 5 (5 0 35+ 5 133)		
					X 5 14 5 (5 0 45+ 5 143)		
					X 5 15 5 (5 0 55+ 5 153)		
					X 5 16 5 (5 0 65+ 5 163)		

t t , t #9001 0001.



ZB5AA0



ZB5AA5



ZB5AL3



ZB5AP1



ZB5CA2

Non-Illuminated Operators, Momentary—Unmarked

Shape of Head	Type of Push	Color of Cap	Catalog Number	Price
	h , h t ▲	...	5 0	\$5.50
	h , h t 6	6 ■	5 9	6.50
	h	h t	5 1	6.50
			5 2	
			5 3	
			5 4	
			5 5	
			5 6	
			5 8	
	h h t t ,	h t	5 18	8.00
			5 38	
			5 48	
			5 58	
			5 68	
	E t	h t	5 11	6.50
			5 12	
			5 13	
			5 14	
			5 15	
			5 16	
	t ()	h t	5 P1	12.90
			5 P2	
			5 P3	
			5 P4	
			5 P5	
			5 P6	
	t ()	h t	5 P18	14.50
			5 P38	
			5 P48	
			5 P58	
			5 P68	
	h P (h h h)	h t	5 14	16.10
			5 24	
			5 34	
			5 44	
			5 54	
			5 64	
	h	h t	5 1	13.50
			5 2	
			5 3	
			5 4	
			5 5	
			5 6	
	E t	h t	5 11	13.50
			5 12	
			5 13	
			5 14	
			5 15	
			5 16	

▲ t , h h 17-52.
■ (h t , , , , ,).
◆ t 17-52.

t t , t #9001 0001.

Non-Illuminated Operators, Momentary—Premarked

Shape of Head	Type of Push	Marking		Color of Cap	Catalog Number	Price
		Text	Color			
	h	I	h t		5 331	\$9.30
				h t	5 131	
			h t		5 333	
				h t	5 133	
			h t		5 341	
				h t	5 141	
			h t		5 345	
				h t		
		P		h t		
				h t		
				h t		
				h t		
		P			h t	
				h t	h t	
↑▲	h t	h t		5 344		
		h t		5 334		
		h t		5 335		
		E t		h t		5 432
					5 232	
P			h t		5 434	
					5 234	
			h t		5 435	
					5 235	
	h	I	h t		5 331	16.00
			h t		5 432	16.00
▲ t - , t t 4 t : ↑, ↓, ← OR →						

Mushroom Heads, Momentary

Shape of Head	Diameter of Head	Color of Head	Catalog Number	Price
 ZB5AC24	30		5 24	\$14.70
			5 34	
			5 44	
			5 54	
	40		5 64	14.70
			5 2	
			5 3	
			5 4	
	60		5 5	17.50
			5 6	
			5 2	
			5 3	
 ZB5AC2			5 4	17.50
			5 5	
			5 6	
			5 2	
 ZB5AR4			5 3	17.50
			5 4	
			5 5	
			5 6	

t t , t #9001 0001.



ZB5AH04

Non-Illuminated Push-on/Push-off Operators

Shape of Head	Type of Push	Color of Push	Catalog Number	Price
	h	h t	5 01	\$8.80
			5 02	
			5 03	
			5 04	
			5 05	
			5 06	
	E t	h t	5 1	8.80
			5 2	
			5 3	
			5 4	
			5 5	
			5 6	
	h	h t	5 01	17.60
			5 02	
			5 03	
			5 04	
			5 05	
			5 06	



ZB5AL8334

Two Head Operators, Momentary

Shape of Head	Description	Color of Pushers	Degree of Protection	Catalog Number	Price
No Marking					
	h		IP40	5 8134	\$10.40
			IP66	5 9134	18.60
		h t	IP40	5 8112	10.40
			IP66	5 9112	18.60
	h t		IP40	5 8334	10.40
			IP66	5 9334	18.60
		h t	IP40	5 8312	10.40
			IP66	5 9312	18.60
Premarked					
	(h l)		IP40	5 8234	12.40
			IP66	5 9234	20.70
		h t	IP40	5 8212	12.40
			IP66	5 9212	20.70
	(h l) (t)		IP40	5 8434	12.40
			IP66	5 9434	20.70
		h t	IP40	5 8412	12.40
			IP66	5 9412	20.70



ZB5AL8434



ZB5AL9334

t t , t #9001 0001.



ZB5AS844



ZB5AS934



ZB5AT4



ZB5AS54



ZB5AS64



ZBY9330

Mushroom Heads for Maintained Push Buttons

Shape of Head	Type of Push	Diameter of Head	Color	Catalog Number	Price
	P h - t ■	40		5 84	\$26.90
	-t - t ■	30		5 834	56.00
		40		5 844	56.00
	t (. 455) ■	30		5 934	56.00
		40		5 944 ▲	56.00
		60		5 964	56.00
	P h -	30		5 24	20.20
				5 44	
		40		5 2	20.20
				5 4	
		60		5 X2	23.00
				5 X4	
	-t -	30		5 42	39.00
				5 44	
		40		5 52	39.00
				5 54	
				5 55	44.80
		60		5 62	
				5 64	56.00
	(. 455)	30		5 72	
				5 74	56.00
		40		5 12	
				5 14 ▲	56.00
		60		5 22	
				5 24	56.00

▲ h . 421E: h 12 t h t .
 . 458 : h 10 t h t .
 . 520E: h 14 t h t .
 . 3131 : h 20 t h t .
 E h t h h 40 t h h t t t t t h t t i h . 421E : 5 94412.
 ■ h t h h 40 t h h t t t t t h t t i h . 421E : 5 94412.

Circular Legends for Emergency Stop Mushroom Heads (yellow background)

Diameter	Text	Catalog Number	Price
60	E E E P	9101	\$1.70
	E E E P	9330	
90	E E E P	8101	
	E E E P	8330	

t t , t #9001 0001.

For the most up-to-date information

h t t t h t (.) t t .
 ♦ h :
 .421E: h 12 t h t .
 .458 : h 10 t h t .
 .520E: h 14 t h t .
 .3131 : h 20 t h t .
 E : h t h h .421E 2 t t , t th, h h h
 t . 5 212

2004 h E t
h t
8/1/04

Reset Operators



XB5AA

Shape of Head	Actuation Distance		Text	Color	Catalog Number	Price
	IN	mm				
Flush	Adjustable Shaft					
	0.67 4.72	17 120	H t		X 5 831	\$17.10
					X 5 841	
					X 5 861	
				X 5 84101	20.70	
				X 5 86102	20.70	
	4.72 10.12	120 257	H t		X 5 832	19.70
					X 5 842	
					X 5 862	
					X 5 84201	22.80
					X 5 86202	22.80
Extended						
	0.67 4.72	17 120			X 5 84101	20.70
	4.72 10.12	120 257			X 5 84201	22.80

Potentiometer Operator (with Mounting Collar)



XD5PA12

Shape of Head	Description	Application	Catalog Number	Price
	h t t t h h t h 1.73 t 1.97 (44 t 50) (t t t t)	h t 0.25 .(6.35)	5 922	\$71.00
		h t 0.24 .(6)	5 912	

Joystick Controllers (54 mm, Extended Operating Shaft) ▲

Description	Contact Operation	Action	Catalog Number	Price
2 t	1 t 1 . . t t t	t	X 5P 12	\$125.00
		t	X 5P 22	
4 t	1 t 1 . . t t t	t	X 5P 14	158.00
		t	X 5P 24	

▲ h t t t t t t t E10 () E20 ()

Legends for Joystick Controllers

Description	For use with		Catalog Number	Price
30 48	2 t		2201	\$1.70
		h t	2401	
48 48	4 t		4201	
		h t	4401	



XB5DS•

Hour Counters ■

Characteristics	Supply Voltage	Catalog Number	Price
I t 0 9999.9	12 24 ▼ ▼ , 50/60	X 5	\$174.00
	120 ▼ , 60	X 5	
	230 240 ▼ , 50	X 5	



XB5KS•

Buzzer ■

Characteristics	Supply Voltage	Catalog Number	Price
80 (IP40 E 1) t t tt t	12 24 ▼ ▼ , 50/60	X 5	\$83.00
	120 ▼ , 60	X 5	
	230 240 ▼ , 50	X 5	

■ E191025, X 2 X 8.

Two Position Toggle Switch



ZB5AD28

Shape of Head	Color	Type of Positions	Catalog Number	Price
		t	5 28	\$23.30
		t	5 48	

t t , t #9001 0001.



ZB5AV053



ZB5AV01



ZB5CV063

Pilot Light Heads

Shape of Head	For use with Body Comprising Light Module Type	Color of Lens	Catalog Number	Price
	P E E E	h t	5 013	\$3.80
			5 033	
			5 043	
			5 053	
			5 063	
	P E (E)	h t	5 013	3.80
			5 033	
			5 043	
			5 053	
			5 063	
	9 E t , E	h t	5 01	3.80
			5 03	
			5 04	
			5 05	
			5 06	
	9 E t , (E)	h t	5 01	3.80
			5 03	
			5 04	
			5 05	
			5 06	
	P E E E	h t	5 013	13.50
			5 033	
			5 043	
			5 053	
			5 063	

t t , t #9001 0001.



ZB5AV6



ZB5AV3



ZB5AV**

Complete Bodies (Mounting Collar + Light Module for BA9s Incandescent Bulb, Neon or LED)

Description	Light Source	Supply Voltage (V)	Catalog Number	Price
Screw clamp terminal connections				
t	9 t 2.4	≤ 250	5 ▼6	\$19.30
t	9 t	24 ▼ 2 tt	5 ▼624	24.60
t	9 t	120 ▼ 2.4 tt	5 ▼6120	24.60
1.2 ▼ , 6 ▼ t	9 t	110 120 ▼ 50/60	5 ▼3	49.20
		230 240 ▼ 50/60	5 ▼4	
		400 50	5 ▼5	
		440 480 ▼ 60	5 ▼8	
		550 600 ▼ 60	5 ▼9	

▲ t , 17-53.

Complete Bodies (Mounting Collar + Light Module with PROTECTED LED)■

Light Source	Supply Voltage	Color of Light Source	Catalog Number	Price
Screw clamp terminal connections				
Protected [®] LED	12 ▼ /	h t	5 ▼ 1	\$28.60
			5 ▼ 3	
			5 ▼ 4	
			5 ▼ 5	
			5 ▼ 6	
	24 ▼ /	h t	5 ▼ 1	28.60
			5 ▼ 3	
			5 ▼ 4	
			5 ▼ 5	
			5 ▼ 6	
	24 120 ▼ /	h t	5 ▼ 1	28.60
			5 ▼ 3	
			5 ▼ 4	
			5 ▼ 5	
			5 ▼ 6	
	110 120 ▼	h t	5 ▼ 1	28.60
			5 ▼ 3	
			5 ▼ 4	
			5 ▼ 5	
			5 ▼ 6	
Protected [®] LED	24 ▼ /	h t	5 ▼18 1	33.10
			5 ▼18 3	
			5 ▼18 4	
			5 ▼18 5	
			5 ▼18 6	
	110 120 ▼	h t	5 ▼18 1	33.10
			5 ▼18 3	
			5 ▼18 4	
			5 ▼18 5	
			5 ▼18 6	

■ - t , 3 t h h t E : 5 ▼ 13 (- t 1 0.250" 2 0.110").

t t , t #9001 0001.



ZB5AW313



ZB5AW363



ZB5AW143



ZB5CW313



ZB5AW33

Heads for Momentary Illuminated Push Buttons

Shape of Head	Type of Push	Color	Catalog Number	Price
Only use with PROTECTED LED light modules				
	h	h t	5 313	\$9.30
			5 333	
			5 343	
			5 353	
			5 363	
	h t	h t	5 513	15.50
			5 533	
			5 543	
			5 553	
			5 563	
	h t	h t	5 18	8.00
			5 38	
			5 48	
			5 58	
			5 68	
	E t	h t	5 113	6.50
			5 133	
			5 143	
			5 153	
			5 163	
	h t	h t	5 313	13.50
			5 333	
			5 343	
			5 353	
			5 363	
	E t	h t	5 113	13.50
			5 133	
			5 143	
			5 153	
			5 163	
Only use with light modules for a BA9s incandescent bulb, neon or LED				
	h	h t	5 31	9.30
			5 33	
			5 34	
			5 35	
			5 36	
			5 37	
	E t	h t	5 11	6.50
			5 13	
			5 14	
			5 15	
			5 16	
			5 17	

Illuminated Push-on/Push-off Operators

Shape of Head	Type of Push	Color of Lens	Catalog Number	Price
Only use with PROTECTED LED light modules				
	h	h t	5 013	\$12.40
			5 033	
			5 043	
			5 053	
			5 063	
	E t	h t	5 13	9.80
			5 33	
			5 43	
			5 53	
			5 63	

t t , t #9001 0001.



ZB5AZ101

Contact Blocks (Mounting Collar with Contact Blocks)

Table with 5 columns: Description, Type of Contact (N.O., N.C.), Catalog Number, and Price. It lists various configurations of contact blocks with their respective part numbers and prices.

Technical specifications and dimensions for the contact blocks, including terminal spacing and mounting hole dimensions.

Complete Bodies (Mounting Collar + Single Contact Block + Light Module with PROTECTED LED)

Table with 5 columns: Light Source, Type of Contact (N.O., N.C.), Color, Supply Voltage (24 Vac/dc, 110-120 Vac), and Price. It lists complete button assemblies with their part numbers and prices.

Screw clamp terminal connections

Table showing screw clamp terminal connections for various button models. It includes columns for terminal numbers, contact types, and prices. A 'Protected LED' logo is also present.

Mounting Collar, Contact Block and Light Module (with screw clamp terminal connections) ▲

Table with 7 columns: Supply, Light Source, Supply Voltage, Type of Contact (N.O., N.C.), Color of Light Source, Catalog Number, and Price. It lists button assemblies with their part numbers and prices.

Screw clamp terminal connections

Table showing screw clamp terminal connections for button assemblies. It includes columns for terminal numbers, contact types, and prices.

Technical specifications and dimensions for the button assemblies, including terminal spacing and mounting hole dimensions.

Technical specifications and dimensions for the button assemblies, including terminal spacing and mounting hole dimensions.



Standard (30 x 40 mm) Legend Plates for 8 x 27 mm Legends▲

Description	Color	Legend	Text	Catalog Number	Price
h t t ...		...		32	\$1.00
(h) t		...		2101	
h t		...		4101	1.70
t t t		h t		2002	
(t) t		h t		2004	
(2 11 h) t		h t		4001	7.10
h t				4005	
		()		2146	
		()		2931	
h t t	■	I		2147	
		II		2148	1.70
		-I		2178	
		I-II		2179	
		I- -II		2186	
		-		2115	
		- -		2364	
		E		2385	
		E E E P		2314	
				2308	
				2330	
				2328	
		- E		2305	
		- -		2371	
				2316	
				2387	
		I		2321	
				2382	
h E h	■	E		2310	
		-		2312	1.70
				2367	
		PE		2311	
		P E		2313	
		E E ()		2326	
		E E ()		2323	
		E E E		2322	
		E E E		2306	
		I		2309	
				2334	
				2327	
		P		2303	
		P-		2304	
		P		2366	
				2307	

▲ 17-51.
■ t t t : h t tt . t t : h t tt (h).

Standard (30 x 50 mm) Legend Plates for 18 x 27 mm Legends

Description	For use with	Color	Catalog Number	Price
h t t	h	...	33	

Marked Legends for 8 x 27 mm (for 30 x 40 mm legend holders ZBZ32)



Color	Marking	Text	Catalog Number	Price
		()	02146	
		()	02931	
	I t t	I	02147	
		II	02148	
		-I	02178	
		I-II	02179	
		I- -II	02186	\$0.83
		-	02115	
		- -	02364	
		▲ E	02385	
		E E E P	02314	
			02308	
			02330	
			02328	
		- E▼	02305	
			02371	
		- -	02316	
		I	02387	
		▲E	02321	
	E h		02382	
		-	02310	
			02312	
			02367	
			02311	
		PE	02313	
		P E	02326	
		E E ()	02323	
		E E ()	02322	
		E▼E E	02306	
		I	02309	
		▲	02334	
			02327	
			02303	
		P	02304	
		P-	02366	
		P	02307	0.83

▲ t t t : h t t t . t t t : h t t t (h t t t).


Legends for Customer Engraving (inserts only)

Description	For use with	Color	Catalog Number	Price
8 27	30 40 h		0101	
		h t	0102	
18 27	30 50 h		5101	
		h t	5102	\$0.83

Legends for Factory Engraving (inserts only)

Description	For use with	Color	Text	Catalog Number	Price
8 27 t / t () 2 11 h t ()	30 40 h		h t	01002	
			h t	01004	
		h t		01001	
				01005	\$6.10
18 27 t / t () 3 11 h t ()	30 50 h		h t	05002	
			h t	05004	
		h t		05001	
				05005	6.10

t t , t #9001 0001.



ZBY1101

Sheets of Legends for Push Buttons, Switches, and Pilot Lights

Description	Marking	Text	Catalog Number	Price
h t 66 t t - h	I t t		1101	\$3.10
			1101	3.10
			1146	5.20
		I	1147	
		II	1148	
		III	1149	
		P	1304	
		→	1912	
	E h		1316	5.20
			1312	
			1311	
			1303	
h t	h t : E h , h , , h , lt	X 2		52.00

Push Button Caps—Unmarked

For use with	Type of Push	Color	Catalog Number	Price
5 0 h tt h h	h	h t	1	\$1.00
			2	
			3	
			4	
			5	
			6	
		6 ▲	9	2.10
	E t	h t	11	1.00
			12	
			13	
			14	
			15	
			16	
		6 ▲	19	2.10



ZBA•



ZBL•

Push Button Caps—Marked


For use with	Type of Push	Marking		Color of Cap	Catalog Number	Price
		Text	Color			
5 0 h tt h h	h	I ■	h t		331	\$2.10
				h t	131	
		■	h t		333	
				h t	133	
			h t		341	
				h t	141	
		P ■		h t	343	
		■	h t		344	
		⊕ ■	h t		345	
		⊕	h t		245	
		◇	h t		346	
		↑		h t	334♦	
			h t		335♦	
		■	h t		432	
					232	
		P ■	h t		434	
					234	
			h t		435	
					235	
		■	h t		639	



ZBA•33


▲ t 6 t : h t , , , , ,
♦ t t - , t t 4 t : ↑, ↓, ← or →

t t , t #9001 0001.






ZBP0



ZBW008



ZBV01•3



ZBV01•

Clear Boots

Description	For use with	Catalog Number	Price
t	t h tt tt h h	P0	\$6.20
	t t h tt tt h h	P0	6.20
t	h h tt , tt tt t t h t	008	16.40
	h t h tt t	008	16.40

Lens Caps

For use with	Color	Catalog Number	Price
--------------	-------	----------------	-------

Lens caps for PROTECTED LED light modules

P t h t	h t	▼0113	\$2.70
		▼0133	
		▼0143	
		▼0153	
		▼0163	
l t h tt tt h h h	h t	9113	2.70
		9133	
		9143	
		9153	
		9163	
l t h tt tt t h	h t	9313	2.70
		9333	
		9343	
		9353	
		9363	

Circular lens caps for BA9s light modules

P t h t	h t	▼011	2.70
		▼013	
		▼014	
		▼015	
		▼016	
		▼017	
l t h tt tt h h h	h t	911	2.70
		913	
		914	
		915	
		916	
		917	
l t h tt tt t h	h t	931	2.70
		933	
		934	
		935	
		936	
		937	

Square lens caps for PROTECTED LED light modules (ZB5C operators only)

P t h t 	h t	▼0113	4.70
		▼0133	
		▼0143	
		▼0153	
		▼0163	
l t h tt tt h h h 	h t	9113	4.70
		9133	
		9143	
		9153	
		9163	
l t h tt tt t h 	h t	9313	4.70
		9333	
		9343	
		9353	
		9363	

t t , t #9001 0001.

L

Ph

t

Push Buttons—Class 9001 Type K—30 mm
Heavy Duty Operators

Non-Illuminated Momentary Push Button Operators—UL Types 4, 13/NEMA 4, 13

Description		Color	Operator with 1 N.O. and 1 N.C. Contact (KA1)	Price	Operator with 1 N.O. Contact (KA2)	Operator with 1 N.C. Contact (KA3)	Price	Operator Only with No Contacts	Price
 9001 1			1 13	\$54.00	1 5	1 6	\$39.90	1	\$25.70
			1 13	54.00	1 5	1 6	39.90	1	25.70
			1 13	54.00	1 5	1 6	39.90	1	25.70
		▲	1 13	54.00	1 5	1 6	39.90	1	25.70
		■	1 ■ 13	54.00	1 ■ 5	1 ■ 6	39.90	1 ■	25.70
 9001 3			3 13	54.00	3 5	3 6	39.90	3	25.70
			3 13	54.00	3 5	3 6	39.90	3	25.70
			3 13	54.00	3 5	3 6	39.90	3	25.70
		▲	3 13	54.00	3 5	3 6	39.90	3	25.70
		■	3 ■ 13	54.00	3 ■ 5	3 ■ 6	39.90	3 ■	25.70
 9001 2	E t		2 13	54.00	2 5	2 6	39.90	2	25.70
			2 13	54.00	2 5	2 6	39.90	2	25.70
			2 13	54.00	2 5	2 6	39.90	2	25.70
		▲	2 13	54.00	2 5	2 6	39.90	2	25.70
		■	2 ■ 13	54.00	2 ■ 5	2 ■ 6	39.90	2 ■	25.70

▲ h t ■ h tt t t h tt t : , , , , h t .

Description		Color	Operator with 1 N.O. and 1 N.C. Contact (KA1)	Price	Operator with 1 N.O. Contact (KA2)	Operator with 1 N.C. Contact (KA3)	Price	Operator Only with No Contacts	Price
 9001 4	$1\frac{3}{8}$ h t tt	Snap-In Mushroom Button							
			4 13	\$83.00	4 5	4 6	\$68.00	4	\$54.00
			4 13	83.00	4 5	4 6	68.00	4	54.00
		◆	4 05 13	86.00	4 05 5	4 05 6	72.00	4 05	57.00
			4 13	83.00	4 5	4 6	68.00	4	54.00
		■ ★	4 ★ 13	83.00	4 ★ 5	4 ★ 6	68.00	4 ★	54.00
		Screw-On Mushroom Button With Set Screw Security							
			24 13	83.00	24 5	24 6	68.00	24	54.00
			24 13	83.00	24 5	24 6	68.00	24	54.00
		■ ★	24 ★ 13	83.00	24 ★ 5	24 ★ 6	68.00	24 ★	54.00
 9001 5	$2\frac{1}{4}$ h t tt	Snap-In Mushroom Button							
			5 13	83.00	5 5	5 6	68.00	5	54.00
			5 13	83.00	5 5	5 6	68.00	5	54.00
		◆	5 05 13	86.00	5 05 5	5 05 6	72.00	5 05	57.00
			5 13	83.00	5 5	5 6	68.00	5	54.00
		■ ★	5 ★ 13	83.00	5 ★ 5	5 ★ 6	68.00	5 ★	54.00
		Screw-On Mushroom Button With Set Screw Security							
			25 13	83.00	25 5	25 6	68.00	25	54.00
			25 13	83.00	25 5	25 6	68.00	25	54.00
		■ ★	25 ★ 13	83.00	25 ★ 5	25 ★ 6	68.00	25 ★	54.00

◆ h h E t tt h h h t h t .
★ t .

Color	■ KR1, 2, 3 Place Color Code in Type Number	★ KR4, 5, 24, 25 Place Color Code in Type Number
h t	▲	▲
	E	...

▲ h t	17-77
t t	17-78
t t	17-80
▲ P t	17-81
t P t	17-83
t P t	17-86

t t , t #9001 0001.

17

▼ h t t
EXAMPLE: KR9 with a yellow knob = KR9Y

△ h t t 17-77.
EXAMPLE: KR8P with a 277 V 50–60 Hz voltage = KR8P8

□ h t h t E h t h , . , E ,

◇ h t ,
☆ h t h t t h t h t

▽ 11 h 1 1 (1 . . 1 . .) 12 1 h 2 1 (2 . . 2 . .)
○ t P h E t t tt t 05

* 1³/₈" 2¹/₄" -20 -21 17-84.
9001 54 t (E 6 t) -20 -21 t t h

t t -20 -21
Example: 9001KR9R would be 9001KR9R20 or 9001KR9R21. No price adder.

Color	KR6, KR7, KR67	KR11, KR12	KR8, KR9
◆			
h t ◆		! , ... E	! , ...

17-57

Heavy Duty Operators



For the most up-to-date information

h t 17-79.

17 PUSH BUTTONS AND OPERATOR INTERFACE

Description		Voltage and Frequency	Style	With Red Color Cap and 1 N.O. and 1 N.C. Contact (KA1)	With Green Color Cap and 1 N.O. and 1 N.C. Contact (KA1)	Price □	With Other Color Cap Without Contact Block ▲	Price ◇
 9001 1A1		110 120 V, 50 60		1A1 13	1A1 13	\$140.	1A1▼	\$111.
		220 240 V, 50 60		1A7 13	1A7 13	140.	1A7▼	111.
		24 28 V /	▼ t	1A35 13	1A35 13	120.	1A35▼	92.
			h	1A■ 13	1A■ 13	140.	1A■▼	111.
			▼ t	1A■ 13	1A■ 13	120.	1A■▼	92.
			t ◆	1A■ 13	1A■ 13	120.	1A■▼	92.
AE ★	1A■ 13		1A■ 13	140.	1A■▼	111.		
 9001 3A1		110 120 V, 50 60		3A1 13	3A1 13	140.	3A1▼	111.
		220 240 V, 50 60		3A7 13	3A7 13	140.	3A7▼	111.
		24 28 V /	▼ t	3A35 13	3A35 13	120.	3A35▼	92.
			h	3A■ 13	3A■ 13	140.	3A■▼	111.
			▼ t	3A■ 13	3A■ 13	120.	3A■▼	92.
			t ◆	3A■ 13	3A■ 13	120.	3A■▼	92.
AE ★	3A■ 13		3A■ 13	140.	3A■▼	111.		
 9001 2A1		110 120 V, 50 60		2A1 13	2A1 13	131.	2A1▼	102.
		220 240 V, 50 60		2A7 13	2A7 13	131.	2A7▼	102.
		24 28 V /	▼ t	2A35 13	2A35 13	111.	2A35▼	83.
			h	2A■ 13	2A■ 13	131.	2A■▼	102.
			▼ t	2A■ 13	2A■ 13	111.	2A■▼	83.
			t ◆	2A■ 13	2A■ 13	111.	2A■▼	83.
AE ★	2A■ 13		2A■ 13	131.	2A■▼	102.		
 9001 2A 20		110 120 V, 50 60		2A1 20 13	2A1 20 13	131.		
		220 240 V, 50 60		2A7 20 13	2A7 20 13	131.		
		24 28 V /	▼ t	2A35 20 13	2A35 20 13	111.		
			h	2A■ 20 13	2A■ 20 13	131.		
			▼ t	2A■ 20 13	2A■ 20 13	111.		
			t ◆	2A■ 20 13	2A■ 20 13	111.		
AE ★	2A■ 20 13		2A■ 20 13	131.				
 9001 2A 21		110 120 V, 50 60		2A1 21 13	2A1 21 13	131.		
		220 240 V, 50 60		2A7 21 13	2A7 21 13	131.		
		24 28 V /	▼ t	2A35 21 13	2A35 21 13	111.		
			h	2A■ 21 13	2A■ 21 13	131.		
			▼ t	2A■ 21 13	2A■ 21 13	111.		
			t ◆	2A■ 21 13	2A■ 21 13	111.		
AE ★	2A■ 21 13		2A■ 21 13	131.				

▲ h t 17-80 t h h t t . 17-85. h t t t t.

■ $\frac{h}{t}$ $\frac{h}{h}$
Example: K2L▲ with 240 Vac/dc = K2L25

Example: RZL with 240 Vac/dc = RZL25

Example: K2L25♦ with a blue 1³/₈ mushroom button = K2L25L20

Example: R2E25V with a blue 1/8 mushroom button = R2E25E20

△ h	t	(2▲)	t	h	tt	t	h
□ P	t, h t	, t t	.				
◇ P	t, h t						


[illegible]

$\lambda_h t$	17-77
$t t$	17-78
$t t$	17-80
$\lambda P t$	17-81
	17-83
$t P t$	17-86

t t t #9001 0001.

Non-Illuminated 2 Position Selector Switch Operators—UL Types 4, 13/NEMA 4, 13

h t t t 17-79. t .

Contact Block Required					1—Contact Closed 0—Contact Open			
Contact Block Position	Quantity and Type		Mount on Side		Left	Right	Left	Right
 Top View	1	3	#2	3 #2	1	0	0	1
	2	2		2 #2	0	1	1	0
	1	3	#1	3 #1	1	0	0	1
	2	2		2 #1	0	1	1	0
Cam (see page 17-64)					E		D	
Non-Illuminated Operators					Type		Type	Price

Manual Return

Operator Only▲

h t	11	12	\$ 28.50
h t	11	12	35.10
h h	11■	12■	35.10
h h t h E10 (1,2,3)◆★	11◆	12◆	92.00
h t t t ()			
h 1 1 #2	11 13	...	64.00
h 1 1 #1	11 1	...	64.00
h 1 1 #1 1 1 #2	11 2	...	92.00

Spring Return from Left

t	25	...	47.60
h t	25	...	54.00
h t	25■	...	54.00
h h t h E10 (2)	25 2	...	111.00

Spring Return From Right

t	...	34	47.60
h t	...	34	54.00
h t	...	34■	54.00
h h t h E10 (1)	...	34 1	111.00

▲ h t h t 17-80 t h t h t t t . h t h 17-85. h t t .
 ■ h h h 17-80 t h t h t t t t . h t h 17-85. h t t t .
 ◆ Example: KS11■ with a green gloved-hand knob = KS11FG
 ★ Example: KS11K◆ with key withdrawal in the right position only = KS11K2
 ★ h h t t t t . E10 (t / h . 2941101100, \$6.60 per key).

◆ Key Withdrawal Code





Code	Position
1	h t
2	h t
3	h t h t

Selector Switch Knobs

Standard Knob		Gloved-Hand Knob		Coin Operated			
							
Color	Knob Code	Type	Knob Code	Type	Knob Code	Type	Price
h t	h	11 8 8 8 11 h 8 8 8 8	h	25 24 24 24 25 h 24 24 24 24	h	18 16 16 16 ... h 16 16	\$6.60

Push Buttons—Class 9001 Type K—30 mm
Heavy Duty Selector Switches

Illuminated 2 Position Selector Switch Operators – UL Types 4, 13/NEMA 4, 13

Contact Block Required					1 — Contact Closed 0 — Contact Open		
Contact Block Position	Quantity and Type		Mount on Side		Left Right	Left Right	
 Top View	1	3	#2	3 #2	1 0	0 1	
		2		2 #2	0 1	1 0	
	1	3	#1	3 #1	1 0	0 1	
		2		2 #1	0 1	1 0	
Cam (see page 17-64)					E	D	
Illuminated Operators					Type	Type	Price
					11 1	12 1	\$105.
					11 1	12 1	111.
					11 ■	12 ■	105.
					11 ■	12 ■	86.
					11 ■◆	12 ■◆	111.
					11 ■◆	12 ■◆	92.
					25 1	...	123.
					25 1	...	131.
					25 ■	...	123.
					25 ■	...	105.
					25 ■◆	...	131.
					25 ■◆	...	111.
					...	34 1	123.
					...	34 1	131.
					...	34 ■	123.
					...	34 ■	105.
					...	34 ■◆	131.
					...	34 ■◆	111.
Example: K25J■ with 60 Vac/dc = K25J37.							
Example: K25J35◆ with a green knob = K25J35G.							

Selector Switch Knobs

Standard Knob		Gloved-Hand Knob		Coin Operated		Price
Color	◆ Knob Code	Type	◆ Knob Code	Type	◆ Knob Code	
h t	▲	8	▲	24	▲	\$6.60
		8		24		
		8		24		
		▲8		▲24		
		8		24		
		8		24		

Two Color Selector Switch

Knob	Factory Assembled Form Number Δ	Price Adder
t	178	\$28.50
-	1781	28.50
Δ t t , ... 11 1 Form Y178.		

▲ h t	17-77
t t	17-78
t t	17-80
▲ P t	17-81
t P t	17-83
	17-86

Non-Illuminated 3 Position Selector Switch Operators—UL Types 4, 13/NEMA 4, 13

[illegible]

◆Key Withdrawal Codes

Code	Position
4	h t
5	t
6	h t
7	h t t
8	h t h t
9	t h t
10	h t, t h t


Selector Switch Knobs

							
Standard Knob			Gloved-Hand Knob		Coin Operated		
Color	 Knob Code	Type	 Knob Code	Type	 Knob Code	Type	Price
h t		11		25		18	\$6.60
		8		24		16	
		8		24		16	
		8		24		16	
		11		25		16	
		8		24		16	
		8		24		16	
		8		24		16	
		8		24		16	
		8		24		16	

t t t #9001 0001.

For the most up-to-date information

17 PUSH BUTTONS AND OPERATOR INTERFACE



CONTACT BLOCK REQUIRED				1 — Contact Closed 0 — Contact Open									
Contact Block Position	Quantity and Type		Mount on Side	Center	Center	Center	Center	Center	Center	Center	Center	Center	
				Left Right	Left Right	Left Right	Left Right	Left Right	Left Right	Left Right	Left Right		
 Top View			#2	1 0 0	1 0 0	0 0 1	1 0 0	1 0 0	1 0 0	1 0 0	0 1 0	1 1 0	
				#2	0 1 1	0 0 1	0 1 0	0 1 0	0 0 1	0 1 1	0 1 1	1 0 0	0 0 1
			#1	0 0 1	1 0 0	0 0 1	1 0 0	0 1 0	0 0 1	1 0 1	0 0 1	0 1 1	
				#1	1 1 0	0 0 1	0 1 0	0 1 0	0 0 1	1 0 0	0 1 0	0 1 0	1 0 0
Cam (see page 17-64)				B	C	D	E	F	G	J	L	M	
Illuminated Operators				Type	Type	Type	Type	Type	Type	Type	Type	Type	Price
				42 1 42 1 42 ■ 42 ■	43 1 43 1 43 ■ 43 ■	44 1 44 1 44 ■ 44 ■	45 1 46 1 45 ■ 45 ■	46 1 46 1 46 ■ 46 ■	47 1 47 1 47 ■ 47 ■	49 1 49 1 49 ■ 49 ■	401 1 401 1 401 ■ 401 ■	402 1 402 1 402 ■ 402 ■	\$105. 111. 105. 86.
				42 ■◆ 42 ■◆	43 ■◆ 43 ■◆	44 ■◆ 44 ■◆	45 ■◆ 45 ■◆	46 ■◆ 46 ■◆	47 ■◆ 47 ■◆	49 ■◆ 49 ■◆	401 ■◆ 401 ■◆	402 ■◆ 402 ■◆	111. 92.
				62 1 62 1 62 ■ 62 ■	63 1 63 1 63 ■ 63 ■	64 1 64 1 64 ■ 64 ■	65 1 65 1 65 ■ 65 ■	66 1 66 1 66 ■ 66 ■	67 1 67 1 67 ■ 67 ■	69 1 69 1 69 ■ 69 ■	601 1 601 1 601 ■ 601 ■	602 1 602 1 602 ■ 602 ■	123. 131. 123. 105.
				62 ■◆ 62 ■◆	63 ■◆ 63 ■◆	64 ■◆ 64 ■◆	65 ■◆ 65 ■◆	66 ■◆ 66 ■◆	67 ■◆ 67 ■◆	69 ■◆ 69 ■◆	601 ■◆ 601 ■◆	602 ■◆ 602 ■◆	131. 111.
				72 1 72 1 72 ■ 72 ■	73 1 73 1 73 ■ 73 ■	74 1 74 1 74 ■ 74 ■	75 1 75 1 75 ■ 75 ■	76 1 76 1 76 ■ 76 ■	77 1 77 1 77 ■ 77 ■	79 1 79 1 79 ■ 79 ■	701 1 701 1 701 ■ 701 ■	702 1 702 1 702 ■ 702 ■	123. 131. 123. 105.
				72 ■◆ 72 ■◆	73 ■◆ 73 ■◆	74 ■◆ 74 ■◆	75 ■◆ 75 ■◆	76 ■◆ 76 ■◆	77 ■◆ 77 ■◆	79 ■◆ 79 ■◆	701 ■◆ 701 ■◆	702 ■◆ 702 ■◆	131. 111.
				52 1 52 1 52 ■ 52 ■	53 1 53 1 53 ■ 53 ■	54 1 54 1 54 ■ 54 ■	55 1 55 1 55 ■ 55 ■	56 1 56 1 56 ■ 56 ■	57 1 57 1 57 ■ 57 ■	59 1 59 1 59 ■ 59 ■	501 1 501 1 501 ■ 501 ■	502 1 502 1 502 ■ 502 ■	123. 131. 123. 105.
				52 ■◆ 52 ■◆	53 ■◆ 53 ■◆	54 ■◆ 54 ■◆	55 ■◆ 55 ■◆	56 ■◆ 56 ■◆	57 ■◆ 57 ■◆	59 ■◆ 59 ■◆	501 ■◆ 501 ■◆	502 ■◆ 502 ■◆	131. 111.

▲ h t 17-80 t h h t t . h t h 17-85. t h t t.

EXAMPLE: K43J with 60 Vac/dc = K43J37

EXAMPLE: K43J35♦ with a green knob = K43J35G

★ h t h h h t h , . . , h

Color	Knob Code	Type	Knob Code	Type	Knob Code	Type	Price
△		11		25		18	\$6.60
		8		24		16	
		8		24		16	
		8		24		16	
△		11		25		16	
		8		24		16	
h t	h	8	h	24	h	16	
		8		24		16	
		8		24		16	
		8		24		16	

$$\Delta \quad - \quad \uparrow$$

$k_h t$	17-77
$t t$	17-78
$t t$	17-80
$k_i P t$	17-81
	17-83
$t P t$	17-86

t t t #9001 0001.

Non-Illuminated and Illuminated 4 Position Selector Switch Operators

h t 17-79. 4, 13/ E 4, 13
t t t t

CONTACT BLOCK REQUIRED				1—Contact Closed 0—Contact Open	
Contact Block Position	Quantity and Type		Mount on Side		
 Top View					
Non-Illuminated Operators			Cam (see page 17-64)	Type	Price
				88	\$28.50
				88	35.10
				88■	35.10
				88◆	92.00
				89	47.60
				89	54.00
				89■	54.00
Illuminated Operators					
				88 1	105.00
				88 1	111.00
				88 ▼	105.00
				88 ▼	86.00
				88 ▼■	111.00
				88 ▼■	92.00
				89 1	123.00
				89 1	131.00
				89 ▼	123.00
				89 ▼	105.00
				89 ▼■	131.00
				89 ▼■	111.00

▲ h t t h t t . 17-80 t h t h 17-85. h
■ h h h t t t h t t.
◆ EXAMPLE: KS88 ■ with a green gloved-hand knob = KS88FG.
♦ EXAMPLE: KS88K ♦ with key withdrawal in the right position only = KS88K12.
★ E₁₀(t . 2941101100, \$6.60).
▼ h t t t t t 17-77. E t
△ h t t h E h t h , . . , E ,
□ h t t h t

◆ **Key Withdrawal Code**

Code	Position
11	1 4
12	4
13	1
14	1, 2, 3 4
15	2, 3 4

Selector Switch Knobs

 Standard Knob			 Gloved-Hand Knob		 Coin Operated		
Color	Knob Code	Type	Knob Code	Type	Knob Code	Type	Price
◇		11		25		18	\$6.60
◇		8		24		16	
		8		24		16	
		8		24		16	
		11		25		16	
h t		8		24		16	
		8		24		16	
		8		24		16	

Lector Switches Guide



For the most up-to-date information

Step No. 1

Step No. 2

Step No. 3

Step No. 4:

Table 3: 4 Position Selector Switch contact sequence. . . Use Car

~~Use Cam Type~~

Use Contact Block Type

Mount on
— side no.
(See page 17-80)

[illegible]

2004 h E t
h t
8/1/04

Pilot Lights—UL Types 4, 13/NEMA 4 & 13

17-79.

Description	Voltage	Style	With Red Fresnel Color Cap	With Green Fresnel Color Cap	With Other Color Cap	Price	Without Color Cap	Price
 (P t P t h t h)	110 120 ▼ 50 60 220 240 ▼ 50 60 24 28 ▼ /	▼ t	P1 31 P7 31 P35 31	P1 31 P7 31 P35 31	P1■ P7■ P35■	\$102. 102. 83.	P1 P7 P35	\$95. 95. 77.
	h t ▼ t t 17-77.	▼ t , h E t ★	P▲ 31 P▲ 31	P▲ 31 P▲ 31	P▲■ P▲■	102. 83.	P▲ P▲	95. 77.
 (P h - - tP t h t h)	110 120 ▼ 50 60 220 240 ▼ 50 60 24 28 ▼ /	▼ t	1 31 7 31 35 31	1 31 7 31 35 31	1■ 7■ 35■	131. 131. 111.	1 7 35	123. 123. 105.
	h t ▼ t t 17-77.	▼ t , h E t ★	▲ 31 ▲ 31	▲ 31 ▲ 31	▲■ ▲■	131. 111.	▲ ▲	123. 105.
 (t tP t h t h)	120 ▼ 24 28 ▼ h t ▼ t	▼ t ▼ ▼ t ▼	38 31 35 31	38 31 35 31	38■ 35■	131. 131.	38 35	123. 123.
	t 17-77.▼	▼ t t ▼	▲ 31	▲ 31	▲■	131.	▲	123.

▲ h t h t 17-77.

EXAMPLE: KT▲R31 with 60 Vac red LED = KT37LRR31

EXAMPLE: KP1 with a blue fresnel cap = KP1L31

$$h \quad t \quad h \quad h \quad E \quad h \quad t \quad h, \dots, E,$$

★ h t
▼ t t t t h t t t
th ▲ E t


Push-to-Test Ground Detector Pilot Light

(Contact Block Included—But NOT Legend Plate or Color Cap)


Voltage and Frequency	Type	Price
110 120 V, 50 60	50	\$171.

Color	 ■ Plastic Fresnel	 ■ Plastic Domed	 ■ Glass
h t	31 31 31 31 31 31 31	9 9 9 9 9 9 9	6 6 6 6 6 6 6

Typical Wiring Diagrams



Push-To-Test Pilot Light



Remote Test Pilot Light

t t , t #9001 0001.

Specialty Operators



For the most up-to-date information

h t 17-79.



Description				Operator With Contacts	Price	Operator Without Contacts ▲	Price
	3 P t t	t t t t	H t ▲ th	71 7	\$197.	71	\$168.
		t t t t	H ▲ th	70 7		70	
		t t t t	H t ▲ th	73 7		73	
		t t t t	H ▲ th	72 7		72	
	3 P t t	t t t t	H t ▲ th	31 8	197.	31	168.
		t t t t	H ▲ th	30 8		30	
		t t t t	H t ▲ th	33 8		33	
		t t t t	H ▲ th	32 8		32	
	5 P t t	t t t t	H t ▲ th	35 2	263.	35	206.
		t t t t	H ▲ th	34 2		34	
		t t t t	H t ▲ th	37 2		37	
		t t t t	H ▲ th	36 2		36	

▲ h t t h t t t t (4) t t . h h 17-80

Operator Positions		Contact Block Type	Contact Block Location	Contact	Handle position (with ref. to Nib)				
					1	2	OFF	3	4
	3	3	P 1 (3)		...	1	0	...	0
		3	P 2 (4)		...	0	0	...	1
	3	2	P 1 (3)		1	...	0	0	...
		2	P 2 (4)		0	...	0	1	...
	5	1	P 1 (3)		0	1	0	0	0
					1	0	0	0	0
		1	P 2 (4)		0	0	0	0	1
					0	0	0	1	0



Inserts

Contact Block Required		Two Position Operators												Three Position Operators			
		0—Contact Open				1—Contact Closed				F—Free D—Depressed							
Quantity and Type	Mount on Side	Left	Right	Left	Right	Left	Right	Left	Right	Left	Right	Left	Right	Left	Center	Right	
		FD	FD	FD	FD	FD	FD	FD	FD	FD	FD	FD	FD*	FD	FD	FD	
 1- -1	#2	0 0 0 1	1 0 0 1	0 0 0 1	1 0 0 0	0 0 0 1	1 1 0 0	1 1 0 0	1 0 0 1	1 0 0 1	0 0 0 1	1 0 0 1	... 0 ... 1	1 0 0 1	1 0 0 0	1 1 0 0	P 17-78, 17-79.
 1- -1	#1	0 0 0 1	1 1 0 0	0 0 0 1	1 0 0 0	1 1 0 0	0 0 0 1	1 0 0 1	1 1 0 0	1 1 0 0	0 0 0 1	1 0 0 1	... 0 ... 1	1 1 0 0	1 0 0 0	1 0 0 1	
Cam ⬆		P		R		S		T		Y		Z		U			
Color Insert		Type		Type		Type		Type		Type		Type		Type			Price
h t l t ■		11		12		13		14		15		18		27			\$53.
		11		12		13		14		15		18		27			\$4.



**Selector Push Button
9001KQ**

Key operated push buttons 17-79.

t t h tt h t t t h tt h t . E

tandem (total of four blocks). Up to two Type KA contact blocks can be mounted in

Description	Lockable Positions			Type	Price
	Extended	Flush	Depressed		
P h t t h .	X ... X	X ... X	 X X	131 132 133 137	\$83.
P h t t h h t . P h t t t .	X ... X	... X X	... X X	141 142 143 147	
h , h h t t t h h t t h t t h t .		X ...	... X	152 153	



Key Operated Push Button
9001KB



Potentiometer
with Dial Plate
9001K21

Potentiometer with Dial Plate ▲—NEMA 4, 13 (Not UL Listed)

Watts		Description		Type	Price
2		t	P t	20	\$134.
		t h	P t	21 ■	191.
		t	P t	22	209.
		t h	P t	23 ♦	266.

Suffix ■	Ohms	Suffix ■	Ohms	Suffix ■	Ohms	Suffix ♦	Tandem Pots Ohms	
							Front	Rear
01	50	07	5	13	500	82	1000	1000
02	100	08	10	37	750	83	5000	5000
38	200	40	15	14	1.0	85	10	10
03	250	09	25	15	2.5	88	50	50
04	500	35	35	16	5.0	89	100	100
05	1000	10	50	17	5.0			
32	1500	36	75					
39	2000	11	100					
06	2500	12	250					
33	3500							

▲ h t t 651580090501. \$2.90.
 ■ t t .E : 2105
 ♦ t t .E : 2382



Emergency Break-Glass
Operator 9001K15

**Emergency Break-Glass Operator—
UL 4, 13/NEMA 4, 13★**

t h h h h , t t t t . h h	
t .P 5 h t .	
Type	Price
15	\$83.

9001K15 Replacement Parts

Description	Part Number	Price
h	3105211101	\$ 9.50
t	3105206750	19.10
t	6512232801	11.10
P	9001 40	2.90
t h h	9001 57	11.10
	2540902240	1.70

★ 17-103.



Rocker Arm
Operating Lever
9001K50

Rocker Arm Operating Lever

t t h tt t t t t h	
h .P t t h tt 17-81, 17-82, 17-56	
h h t t .	
Type	Price
50	\$51.00

Alternate Action—Push-on, Push-off Module

h t h tt t t 9001 , X, h h	
(2) h . h t t h h	
t t t h 9001 3 h h	
t t h 9001 1 9001 4. t, h	
t t h 9001 6.	
Type	Price
85	\$28.50



Push-on Push-off
Module 9001K85

**Off Delay Push Button—
UL Types 4, 13/NEMA 4, 13**

Description	Type (All Colors)			
	Full Guard	Extended Guard	No Guard	Price
 Timed Contact 1 N.O. and 1 N.C.	1 1	2 1	3 1	\$168.
 Timed Contact 2 N.O. and 2 N.C.	1 2	2 2	3 2	311.

t tt h t 0.1 t 60
 t t h h tt . 17-84
 t t t

Note: h t t tt h t . h t
 t h h t tt h , t . t
 t t , h .



Time Delay Push Button
9001KRD

**Wobble Stick
For easy operation of any standard push button.**



Type	Price
8	\$28.50

Push Buttons—Class 9001 Type SK—30 mm
Corrosion Resistant Non-Illuminated Operators

Non-Illuminated Momentary Push Button Operators—UL Types 4, 4X, 13/NEMA 4, 4X, 13

17-79.								
t t h t t t h t .								
Description	Color	Operator with 1 N.O. and 1 N.C. Contact (KA1)	Price	Operator with 1 N.O. Contact (KA2)	Operator with 1 N.C. Contact (KA3)	Price	Operator Only No Contacts ▼	Price
 9001 1		1 13	\$54.00	1 5	1 6	\$39.90	1	\$25.70
		1 13	54.00	1 5	1 6	39.90	1	25.70
		1 13	54.00	1 5	1 6	39.90	1	25.70
	▲	1 13	54.00	1 5	1 6	39.90	1	25.70
	h ■	1■ 13	54.00	1■ 5	1■ 6	39.90	1■	25.70
 9001 3		3 13	54.00	3 5	3 6	39.90	3	25.70
		3 13	54.00	3 5	3 6	39.90	3	25.70
		3 13	54.00	3 5	3 6	39.90	3	25.70
	▲	3 13	54.00	3 5	3 6	39.90	3	25.70
	h ■	3■ 13	54.00	3■ 5	3■ 6	39.90	3■	25.70
 9001 2 E t		2 13	54.00	2 5	2 6	39.90	2	25.70
		2 13	54.00	2 5	2 6	39.90	2	25.70
		2 13	54.00	2 5	2 6	39.90	2	25.70
	▲	2 13	54.00	2 5	2 6	39.90	2	25.70
	h ■	2■	54.00	2■ 5	2■ 6	39.90	2■	25.70
▲ h h tt t h h t t : , , , , h t . ■ t .								

Description	Color	Operator with 1 N.O. and 1 N.C. Contact (KA1)	Price	Operator with 1 N.O. Contact (KA2)	Operator with 1 N.C. Contact (KA3)	Price	Operator Only No Contacts ▼	Price
Snap-In Mushroom Button								
 9001 4 1 3/8 h tt		4 13	\$83.00	4 5	4 6	\$68.00	4	\$54.00
		4 13	83.00	4 5	4 6	68.00	4	54.00
	◆	4 05 13	86.00	4 05 5	4 05 6	72.00	4 05	57.00
		4 13	83.00	4 5	4 6	68.00	4	54.00
	h ★	4★ 13	83.00	4★ 5	4★ 6	68.00	4★	54.00
Screw-On Mushroom Button with Set Screw Security								
 9001 5 2 1/4 h tt		24 13	83.00	24 5	24 6	68.00	24	54.00
		24 13	83.00	24 5	24 6	68.00	24	54.00
		24 13	83.00	24 5	24 6	68.00	24	54.00
	h ★	24★ 13	83.00	24★ 5	24★ 6	68.00	24★	54.00
		24 13	83.00	24 5	24 6	68.00	24	54.00
Snap-In Mushroom Button								
 9001 5 2 1/4 h tt		5 13	83.00	5 5	5 6	68.00	5	54.00
		5 13	83.00	5 5	5 6	68.00	5	54.00
	◆	5 05 13	86.00	5 05 5	5 05 6	72.00	5 05	57.00
		5 13	83.00	5 5	5 6	68.00	5	54.00
	h ★	5★ 13	83.00	5★ 5	5★ 6	68.00	5★	54.00
Screw-On Mushroom Button with Set Screw Security								
 9001 5 2 1/4 h tt		25 13	83.00	25 5	25 6	68.00	25	54.00
		25 13	83.00	25 5	25 6	68.00	25	54.00
		25 13	83.00	25 5	25 6	68.00	25	54.00
	h ★	25★ 13	83.00	25★ 5	25★ 6	68.00	25★	54.00
		25 13	83.00	25 5	25 6	68.00	25	54.00

◆ h h E t tt h h h t h t t .
★ h t .
▼ h t h t t h t t . , 17-85. h h 17-80 t h h t t

Color	■ SKR1, 2, 3 Place Color Code in Type Number	★ SKR4, 5, 24, 25 Place Color Code in Type Number
h t	h	...
	E	...

h t	17-77
t t	17-78
t t	17-80
h P t	17-81
t P t	17-83
t P t	17-86

t t , t #9001 0001.

Multifunction Operators—UL Types 4, 4X, 13/NEMA 4, 4X, 13

h t 17-79.

	Description	Color	Contacts ☆	Price	Without Contacts ◇	Price
 9001SKR11U	1 t 11 tt t	h ■ ▲	11 1 11 ■ 1	\$108. 108.	11 11 ■	\$80. 80.
	1 t tt tt t t	h ■ ▲	12 1 1 12 ■ 1 1	165. 165.	12 12 ■	108. 108.

▲ 11,12 2 h , , , , h t .
 ■ h h tt t t t t t tt t .
EXAMPLE: An SKR11 with top button gray and bottom button orange = SKR11ES

Non-Illuminated	Description	Color	With 2 N.C. Contacts (1 KA3, 1 KA5)	With 1 N.O./1 N.C. Contact (1 KA1)	Price	Without Contacts ◇	Price
 9001SKR9R Non-Illuminated 1 5/8" t 179 P P t t P h t	3 P l l t P - t t P h -	lt ★	8 25 8 25 8★ 25		\$86. 86. 86.	8 8 8★	\$57. 57. 57.
	2 P l l t P - t P h	lt ★		9 13 9 13 9★ 13	114. 114. 114.	9 9 9★	86. 86. 86.

 9001SKR9P1 Illuminated 1 5/8" t 179 P P t t t P h t	Description	Voltage	With Red Knob and 2 N.C. Contacts (1 KA3, 1 KA5)	With Other Color Knob and 2 N.C. Contacts (1 KA3, 1 KA5)	Price	With Other Color Knob Without Contacts ◇	Price
	3 P I I t P - t P h -	110 120 V, 50 60 Hz E, h Δ t t, □	8P1 25 8P▼ 25 8P▼ 25	8P1★ 25 8P▼★ 25 8P▼★ 25	\$162. 162. 143.	8P1★ 8P▼★ 8P▼★	\$134. 134. 114.
	Description	Voltage	With Red ♦ Knob and 1 N.O. & 1 N.C. Contact (KA1)	With Other Color Knob and 1 N.O. & 1 N.C. Contact (KA1)	Price	With Other Color Knob Without Contacts	Price
	2 P I I t P - t P h	110 120 V, 50 60 Hz E, h Δ t t, □	9P1 13 9P▼ 13 9P▼ 13	9P1★ 13 9P▼★ 13 9P▼★ 13	\$191. 191. 171.	9P1★ 9P▼★ 9P▼★	\$162. 162. 143.

♦	t			h	P	h	E		t	t	t	h				t	t	5		\$2.10 t h
★	h								t											
	EXAMPLE: SKR9★ with a yellow knob = SKR9Y																			
▼	h	t							h											17-77.
	EXAMPLE: SKR8P▼ with 277 V 50–60 Hz = SKR8P8																			
△	h			t	h				h	E	h	t	h					A E ,		
□																				
◇	h			t																
									t	h	t	t	t						17-85.	h
☆	h																			
	11	h	h	1	1(1	..1	..)		12	1	h	2	1	(2	..2	..)			t h	t t.

Color	SKR11, SKR12■	SKR8, SKR9
▽		
h t ▽	h ... E	h ...

$$\nabla h \quad t \quad t \quad h - \quad t$$

t t t #9001 0001.

Corrosion Resistant Operators



For the most up-to-date information

17 PUSH BUTTONS AND OPERATOR INTERFACE

Description		Voltage and Frequency	Style	With Red Color Cap and 1 N.O. and 1 N.C. Contact (KA1)	With Green Color Cap and 1 N.O. and 1 N.C. Contact (KA1)	Price □	With Other Color Cap Without Contact Blocks ▲	Price ◇
 9001 1A1	I P h t tt	110 120 V, 50 60		1A1 13	1A1 13	\$140.	1A1 ★	\$111.
		220 240 V, 50 60		1A7 13	1A7 13	140.	1A7 ★	111.
		24 28 V /	▼ t	1A35 13	1A35 13	120.	1A35 ★	92.
		h t ■	, h	1A■ 13	1A■ 13	140.	1A■ ★	111.
			▼ t	1A■ 13	1A■ 13	120.	1A■ ★	92.
			t , ◆	1A■ 13	1A■ 13	120.	1A■ ★	92.
AE ▼	1A■ 13		1A■ 13	140.	1A■ ★	111.		
 9001 2A1	I P h t tt	110 120 V, 50 60		2A1 13	2A1 13	131.	2A1 ★	102.
		220 240 V, 50 60		2A7 13	2A7 13	131.	2A7 ★	102.
		24 28 V /	▼ t	2A35 13	2A35 13	111.	2A35 ★	83.
		h t ■	, h	2A■ 13	2A■ 13	131.	2A■ ★	102.
			▼ t	2A■ 13	2A■ 13	111.	2A■ ★	83.
			t , ◆	2A■ 13	2A■ 13	111.	2A■ ★	83.
AE ▼	2A■ 13		2A■ 13	131.	2A■ ★	102.		
 9001 2A1 20	1 ³ / ₈ I h t h	110 120 V, 50 60		2A1 20 13	2A1 20 13	131.	2A■ ★△	
		220 240 V, 50 60		2A7 20 13	2A7 20 13	131.		
		24 28 V /	▼ t	2A35 20 13	2A35 20 13	111.		
		h t ■	, h	2A■ 20 13	2A■ 20 13	131.		
			▼ t	2A■ 20 13	2A■ 20 13	111.		
			t , ◆	2A■ 20 13	2A■ 20 13	111.		
AE ▼	2A■ 20 13		2A■ 20 13	131.				
 9001 2A1 21	2 ¹ / ₄ I h t h	110 120 V, 50 60		2A1 21 13	2A1 21 13	131.	2A■ ★△	
		220 240 V, 50 60		2A7 21 13	2A7 21 13	131.		
		24 28 V /	▼ t	2A35 21 13	2A35 21 13	111.		
		h t ■	, h	2A■ 21 13	2A■ 21 13	131.		
			▼ t	2A■ 21 13	2A■ 21 13	111.		
			t , ◆	2A■ 21 13	2A■ 21 13	111.		
AE ▼	2A■ 21 13		2A■ 21 13	131.				

▲ h t t t h t t 17-85. h t t t.
■ h t 17-80 h h t t 17-77. h t' h t h t t.

EXAMPLE: SK2L with 240 Vac/dc = SK2L25.

★ h t h h E h t h . , E ,

EXAMPLE: SK2L25▼ with a blue 13/8" mushroom button = SK2L25L20.

EXAMPLE: SKZL25 with a blue 13/8 mushroom button = SKZL25L20.

Δ h	t	(2A)	t	h	tt	t	h
$\square$ P	t, h t	, t t	.				
$\diamond$ P	t, h t	.					

Color Caps

[illegible]

$\lambda_h t$	17-77
$t t$	17-78
$t t$	17-80
$\lambda P t$	17-81
	17-83
$t P t$	17-86

t t t #9001 0001.

Non-Illuminated 2 Position Selector Switch Operators—UL Types 4, 4X, 13/NEMA 4, 4X, 13



Standard Knob
Selector Switch
9001SKS

h t t t 17-79.

Contact Block Required				1—Contact Closed 0—Contact Open			
Contact Block Position	Quantity and Type	Mount on Side		Left	Right	Left	Right
 Top View	1	3	#2	1	0	0	1
	2	2		0	1	1	0
	1	3	#1	1	0	0	1
	2	2		0	1	1	0

Cam (see page 17-64)		E	D	Price
Non-Illuminated Operators		Type	Type	
▲ h t t t h h t t h h t t h h t t () h h t t () h 1 1 h #2 (13) h 1 1 #1 (1) h 1 1 #1 1 1 #2 (2)		11	12	\$28.50
		11	12	35.10
		11■	12■	35.10
		11 13	...	64.00
t t ▲ t h h t h h () h t h t h h t h h ()		25	...	47.60
		25	...	54.00
		25■	...	54.00
t t h t h h t h h ()		...	34	47.60
		...	34	54.00
		...	34■	54.00

▲ h h t 17-80 t h h t t t h t h 17-85. h t t t.
 Example: SKS11FB + H13 = SKS11FBH13
 ■ Example: SKS11■ with a green gloved-hand knob = SKS11FG

Selector Switch Knobs

Standard Knob			Gloved-Hand Knob		Coin Operated		Price
Color	Knob Code	Type	Knob Code	Type	Knob Code	Type	
h t	1	11	1	25	1	18	\$6.60
		8		24		16	
		8		24		16	
		8		24		16	
		11		25		...	
		18		24		16	
		8		24		...	
		8		24		...	

t t , t #9001 0001.

Non-Illuminated 3 Position Selector Switch Operators—UL Types 4, 4X, 13/NEMA 4, 4X, 13

CONTACT BLOCK REQUIRED			1 — Contact Closed 0 — Contact Open									
Contact Block Position	Quantity and Type	Mount on Side	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	Center ↖ ↗	
 Top View	1 2 3	#2 #1	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	
	1 2 3	#2 #1	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	
	1 2 3	#2 #1	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3
	1 2 3	#2 #1	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3	1 2 3
Cam (see page 17-64)			B	C	D	E	F	G	J	L	M	Price
Non-Illuminated Operators			Type	Type	Type	Type	Type	Type	Type	Type	Type	
			42	43	44	45	46	47	49	401	402	\$28.50 35.10 35.10
			42	43	44	45	46	47	49	401	402	
			42 ■	43 ■	44 ■	45 ■	46 ■	47 ■	49 ■	401 ■	402 ■	
			42 13	43 13	44 13	45 13	46 13	47 13	49 13	401 13	402 13	64.00 64.00 92.00
			42 1	43 1	44 1	45 1	46 1	47 1	49 1	401 1	402 1	
			42 2	43 2	44 2	45 2	46 2	47 2	49 2	401 2	402 2	
			62	63	64	65	66	67	69	601	602	47.60 54.00 54.00
			62	63	64	65	66	67	69	601	602	
			62 ■	63 ■	64 ■	65 ■	66 ■	67 ■	69 ■	601 ■	602 ■	
			72	73	74	75	76	77	79	701	702	47.60 54.00 54.00
			72	73	74	75	76	77	79	701	702	
			72 ■	73 ■	74 ■	75 ■	76 ■	77 ■	79 ■	701 ■	702 ■	
			52	53	54	55	56	57	59	501	502	47.60 54.00 54.00
			52	53	54	55	56	57	59	501	502	
			52 ■	53 ■	54 ■	55 ■	56 ■	57 ■	59 ■	501 ■	502 ■	

EXAMPLE: SKS43■ with a green gloved-hand knob = SKS43FG.

Selector Switch Knobs






 Standard Knob			 Gloved-Hand Knob		 Coin Operated		
Color	Knob Code	Type	Knob Code	Type	Knob Code	Type	Price
h t		11		25		18	\$6.60
		8		24		16	
		8		24		16	
		8		24		16	
		11		25		16	
		8		24		16	
		8		24		16	
		8		24		16	
		8		24		16	
		8		24		16	

t t t #9001 0001.

8/1/04

Non-Illuminated 4 Position Selector Switch Operator UL Types 4, 4X, 13/NEMA 4, 4X, 13

17-79.

CONTACT BLOCK REQUIRED						
Contact Block Position	Quantity	and Type				
 Top View	1	3				
	2	#2	2 #2	0 0 1 0		
	3	#1	3 #1	0 0 0 1		
	2	#1	2 #1	0 1 0 0		
Non-Illuminated Operators				Cam (see page 17-64)	Type	Price
					88	\$28.50
					88	35.10
					88■	35.10
					89	47.60
					89	54.00
					89■	54.00
Illuminated Operators						
					88 1	105.00
					88 1	111.00
					88 ♦	105.00
					88 ♦	86.00
					88 ■ ♦	111.00
					88 ■ ♦	92.00
					89 1	123.00
					89 1	131.00
					89 ♦	123.00
					89 ♦	105.00
					89 ■ ♦	131.00
					89 ■ ♦	111.00

▲ h h t 17-80 t h t t t . h t h 17-85. h t t .

■ h h h t t t t t . h t h 17-77.

♦ EXAMPLE: SKS88■ with a green gloved-hand knob = SKS88FG.

★ EXAMPLE: SK88J♦ with 60 Vac/dc = SK88J37.

▼ h t , .

Standard Light Modules for Types K, SK, and KX Control Units ★



Voltage	Description	For Use With Single Lamp III. Operators as Indicated ▲	Light Module Type ♦	Price of Light Module	Voltage Assembly Code	Rating	Replacement Lamp Part Number ♦♦	Price of Replacement Lamp
6 ▼ /	▼ t		31	\$57.	31	.9 ▼	2550101020	\$8.30
12 14 ▼ /	▼ t		32	57.	32	1.2 ▼	2550101037	8.30
18 ▼ /	t		33	57.	33	1.4 ▼	2550101037	8.30
24 28 ▼ /	▼ t		35	57.	35	1.2 ▼	2550101002	8.30
24 28 ▼ /	▲E	E t■	35▲	77.	35▲	.28 ▼	6508805210	28.50
24 28 ▼ /	▲E	E t■	35▲	77.	35▲	.28 ▼	6508805212	28.50
24 28 ▼ /	▲E	E t■	35▲	77.	35▲	.28 ▼	6508805211	28.50
24 28 ▼ /	▲E h t	E t■	35▲	77.	35▲	.28 ▼	6508805214	28.50
24 28 ▼ /	▲E	E t■	35▲▲	77.	35▲▲	.28 ▼	6508805213	28.50
48 ▼ /	▼ t		36	57.	36	2.6 ▼	2550101025	8.30
110 120 ▼, 50 60		E t■	1	77.	1	2.4 ▼	2550101020	8.30
110 120 ▼, 50 60	h	E t■	1	77.	1	.85 ▼	2550101036	11.00
120 ▼ /	t		38	57.	38	3.0 ▼	2550101027	8.30
120 ▼ /	▼ t		38	57.	38	3.0 ▼	2550101027	8.30
120 ▼ /		E t■	11	57.	11	0.2 ▼	2550101013	21.90
120 ▼ /	▲E	E t■	38▲	77.	38▲	1.4 ▼	6508805210	28.50
120 ▼ /	▲E	E t■	38▲	77.	38▲	1.4 ▼	6508805212	28.50
120 ▼ /	▲E	E t■	38▲	77.	38▲	1.4 ▼	6508805211	28.50
120 ▼ /	▲E h t	E t■	38▲	77.	38▲	1.4 ▼	6508805214	28.50
120 ▼ /	▲E	E t■	38▲▲	77.	38▲▲	1.4 ▼	6508805213	28.50
208 220 ▼, 50 60		E t■	3	77.	3	2.5 ▼	2550101020	8.30
220 240 ▼, 50 60		E t■	7	77.	7	2.0 ▼	2550101020	8.30
240 ▼ /	t	E t■	25	57.	25	6.0 ▼	2550101027	8.30
240 ▼ /		E t■ X	12	57.	12	0.3 ▼	2550101013	21.90
277 ▼, 50 60		E t■	8	77.	8	2.4 ▼	2550101020	8.30
380 480 ▼, 50 60		E t■	5	77.	5	2.8 ▼	2550101020	8.30
480 ▼ /		E t■ X	14	57.	14	0.5 ▼	2550101013	21.90
550 600 ▼, 50 60		E t■	6	77.	6	2.5 ▼	2550101020	8.30

Note: t h t h t t t t / h E t

Shallow Depth Light Modules For Types K and SK Control Units ★



Voltage	Description	Light Module Type ♦	Price of Light Module	Voltage Assembly Code	Rating	Replacement Lamp Part Number ♦	Price of Replacement Lamp
24 28 ▼ /	▼ t	55	\$57.	55	1.2 ▼	2550101002	\$8.30
110 120 ▼ /	▼ t	58	57.	58	3.0 ▼	2550101027	8.30

▲ 9001 , X.
■ t t t t t h t
♦ h t h t ▲E 12 ▼ 14 ▼ ▲E
★ h t t X t t t t t
▼ h h t



E42259



▲ 25490
3211 03



t t , t #9001 0001.

Push Buttons—Class 9001 Type K, SK and KX—30 mm

Type K, SK and KX—30 mm

Class 9001



www.SquareD.com





For the most up-to-date information

h 9001 t t l E E t t
(t ▼ E 0106 P t 100). h h t
t (t) / t t . h t t
t h t t, h t t h
t t t t t t 2 #12 #24
t 7 - . th t t

Standard Contact Blocks

Description	Symbol	Type	Price
		1	\$28.50
		2	14.30
		3	14.30
		4	28.50
		5	14.30
		6	14.30

Additional Circuit Arrangements Available

		4 1	\$57.00
		4 5	42.80

▲ h tt t - t t th t . / h E t .

Symbol	Contact Blocks with Binder Head Screws (not FINGERSAFE)		Price	Gold Flashed Contacts with Standard Pressure Wire Terminals	
	Type	Quantity		Type	Price
	21	25	\$28.50	31	\$47.60
	22	25	14.30	32	23.70
	23	25	14.30	33	23.70
	24	25	28.50	34	47.60
	25	25	14.30	35	23.70

■ tt 25. h t t t .

Contact blocks listed below are not FINGERSAFE, but provide:

- h t t t / t
- h t t t t (0.75" . 0.97" h l E E)
- t t
- t h , 1989.
- 238 (t t # E : 9001 1 13 238)



Symbol	Type	Price	Symbol	Type	Price
	1	\$28.50		4	\$28.50
	2	14.30		5	14.30
	3	14.30		6	14.30

Contact blocks listed below are not FINGERSAFE, but have Quick-Connect terminals.

Symbol	Type	Price
	12	\$23.70
	13	23.70

..... t 9001 0001

Maximum Current Ratings For Control Circuit Contacts—Types KA1–KA6, KA21–25, KA31–35, KA1G–KA6G


Volts	AC						Volts	DC				
	Inductive (NEMA / UL Type A600) 35% Power Factor					Resistive 75% Power Factor Make, Break and Continuous Amperes		Inductive and Resistive (NEMA Q600)				Continuous Carrying Amperes
	Make		Break		Continuous Carrying Amperes			Make and Break				
	Amperes	VA	Amperes	VA				KA1	KA2 KA3	KA4	KA5 KA6	
120	60	7200	6.0	720	10	10	125	0.55	0.55	...	...	2.5
240	30	7200	3.0	720	10	10	250	0.27	0.27	...	...	2.5
480	15	7200	1.5	720	10	10	600	0.10	0.10	...	...	2.5
600	12	7200	1.2	720	10	10						

t t , t #9001 0001.

For			Use
Class	Division	Group(s)	
I	1		1. I t t
I	1	, ,	1. 9001 t t 2. I t t
I	2		1. 9001 , , X t t t h t t ▲ 2. I t t
I	2	, ,	1. 9001 t t 2. 9001 , , X t t t h t t ▲ 3. I t t
II	1	E, ,	1. 9001 t t 2. I t t t
II	2	E,	1. 9001 t t 2. 9001 , , X t t t h t t ▲ 3. I t t
II	2		1. 9001 t t 2. 9001 , , X t t t h t t ■ 3. I t t
III	1, 2	...	1. 9001 t t 2. 9001 , , X t t t h t t ■ 3. I t t


▲ 9001 X t l
 2h (40) : (50) t t 2
 1. (40) (50) t t
 2. t t
 3. X t t 4 h t , 2 h t
 4. h h t t E 4 & 13
 ■ 9001 X 9001
 ♦ 243 t P h - t t h t .
 ▲ ■ : E10054 () IV.

Dimensions When Using Contact Blocks



All contact blocks listed below accept #12–18 solid or stranded wire.

Hermetically Sealed Logic Reed Contact Blocks Δ

Description	Symbol	Type	Price
		41	\$57.00
		42	28.50
		43	28.50
		44	57.00
		45	57.00

Max. Volts AC/DC	Maximum Load		
	Resistive	Inductive	Continuous
32/30	.25	.10	.5
120/100	8 ▼	3 ▼	.5

h t t / t t

t t , except:

- 3 t t th h , , E , , 1 , ,
t t one side only (h), 2
- 4 t t th , t one side
only (h), 2 t .
- t 8 8 h - t , t
one side only (h), 2 t

Hermetically Sealed Power Reed Contact Blocks^Δ

Description	Symbol	Type	Price
		51	\$95.
		52	67.
		53	67.
		54	95.
		55	95.

Volts	AC NEMA C300 ★				
	Make		Break		Continuous Carrying Amps
	Amps	VA	Amps	VA	
120	10.00	1200	1.000	120	3.0
240	5.00	1200	.500	120	3.0

Volts	DC NEMA Q150 ▼				Continuous Carrying Amps
	Make		Break		
	Amps	VA	Amps	VA	
115	.50	58	.50	58	3.0

h t t t h t t t h h
E 4. t 35% P 5 t h t 1 .
★ | t t t t
▼ | t t t t
Δ | t t t t

t t t #9001 0001.

Push Buttons—Class 9001 Type K, SK and KX—30 mm

Contact Block “H” Numbers



www.SquareD.com

For the most up-to-date information

h t h 9001 t t h t
/ t .
h t t t t t h t
t t t t h t .
EXAMPLE: 1 h tt h 2 1 t t
9001 1 H2.

Suffix No. (Add to Operator Type)	Price	Positions					
		1	2	3	4	5	6
1	\$28.50	1					
2	57.00	1	1				
3	86.00	1	1	1			
4	114.00	1	1	1	1		
5	14.30	2					
6	14.30	3					
7	28.50	2	2				
8	28.50	3	3				
9	57.00	4	1				
10	42.80	4	5				
11	86.00	1	1		1		
12	57.00	2	3	2	3		
13	28.50		1				
14	14.30		3				
15	42.80	2	3	2			
16	42.80	2	3		3		
17	71.00	1	1	2			
18	71.00	3	1	3		3	
19	143.00	1	1	1	1	1	
21	28.50	2	3				
23	171.00	1	1	1	1	1	1
24	42.80	1	2				
25	28.50	5	3				
26	86.00	1	1	4			
27	42.80	3	3	3			
28	42.80	1	3				
29	143.00	1	4	1	5	1	3
31	57.00	2	2	1			
32	57.00		1		1		
33	57.00	1	3	3			
34	42.80	5	1				
36	14.30		2				
37	28.50	3	2				
38	57.00	3	2	3	2		
39	57.00	5	1		3		
40	86.00	1	1		4		
41	42.80	3	2		2		
42	86.00	1	1	2	2		
43	42.80	2	2	2			
44	42.80	3	2		3		
45	71.00	1	2	3	2		
46	42.80	2	2		2		
47	86.00	5	3	3	5	3	3
48	114.00	1	1	4	4		
50	59.00	5	3	3	3		
51	59.00	5	3		4		
52	59.00	3	1	3			
53	42.80	4	2				
54	59.00	4	5	2			
55	86.00	1	2	2		1	
56	59.00	2	2	2	2		
57	42.80	5	4				
58	14.30		5				
59	71.00	1	2	1			
60	86.00	1	2	1		3	
61	59.00	2	2	5	5		
62	59.00	1	2	3			
63	42.80	1		3			
64	42.80	3	2	2			
66	86.00	3	1	3	1		
71	59.00	3	3	3	3		
72	28.50	3	5				
73	71.00	1	1	3			
74	71.00	1	2	5	5		
75	86.00	1	3	3	3	3	
76	86.00	1	2	2	2	2	
77	59.00	1		1			
78	59.00	1	2		5		
79	42.80	3	3		5		
80	86.00	4	4	5	5		
81	86.00	1	1	2	3		
82	95.00	12	12	13	13		
83	47.60	35	33				
86	42.80	3	2	3			
87	71.00	3	2	3	2	3	

Suffix No. (Add to Operator Type)	Price	Positions					
		1	2	3	4	5	6
89	\$ 42.80	3	1				
90	100.00	1	1	3	3	3	
91	86.00	1	2	1	2		
92	86.00	1	2	3	2	3	
93	86.00	3	2	3	5	5	3
94	128.00	1	1	1	3	3	3
95	42.80	2	1				
97	59.00	1	3		2		
98	114.00	1	1	1	2	2	2
99	71.00	2	2	2	2	2	
100	86.00	1	3	1	2		
101	86.00	2	2	2	2	2	2
102	59.00	1	3		3		
103	86.00	1	1	3	3		
104	128.00	1	1	1	2	2	2
105	47.60	31					
106	95.00	31	31				
107	43.50	3	2	5			
109	43.50	3	3	2			
110	86.00	3	3	3	3	3	3
111	100.00	4	4	4	5		
112	47.60	33	33				
113	71.00	1	1	5			
114	28.50	21					
115	71.00	3	1	5	3		
116	71.00	3	1	3	2		
117	86.00	2	3	1	2	2	
118	42.80	1	5				
119	86.00	1	1	5	3		
120	57.00	3	4	3			
121	57.00	3	3	3	5		
122	57.00	1	3		5		
124	28.50		3		3		
125	42.80	5	5	3			
126	28.50	42					
127	28.50	43					
128	57.00	41					
129	28.50	2		2			
130	42.80	2	3		2		
131	42.80	2		3		2	
132	57.00	2	2	3	3		
133	28.50	3		2			
134	57.00	3	3	2	2		
135	57.00	3	2	2	2		
136	28.50	3		5			
137	228.00	45	45	44	44		
138	42.80	3	3		2		
139	28.50	5	5				
140	57.00	44					
141	57.00	43	43				
142	114.00	1	1	41			
143	57.00	3	1	5			
144	57.00		85		4		
145	95.00	51					
146	134.00	53	52				
147	67.00	53					
148	189.00	51	51				
149	40.50	71					
150	40.50	71	71				
151	95.00	71	71				
152	57.00	1	2	53	2		
153	200.00	53	52				
154	42.80	4	5				
155	71.00	42	43	2	1	2	2
156	143.00	1	1	1	1		
157	71.00	1		1	3	2	
158	71.00	1	2	3	3		
159	86.00	1	1		2		
161	67.00	52					
162	28.50	2		5			
163	57.00	85		4			
164	114.00	85	85	4	4		
165	95.00	55					
166	28.50	22	22				
167	14.30	23	23				
168	14.30	22					
170	285.00	54	51		51		
171	162.00	53	51				
172	28.50	23	23				
173	189.00	54	51				
174	86.00	1	3	1	3		
175	57.00	6	2	5	5		
176	28.50	4					
177	42.80	3	4				
178	42.80	85		3			
179	161.00	53	55				

h t

t t , t #9001 0001.

Legend Plates

Standard Markings	Plastic Legend Plates for use with Types K and SK Operators									Aluminum Legend Plates for use with Type K Operators		
	1.7" Square			2 1/4" Square			2 1/2" Square			Black Legend	Black Legend	Blue Legend
	Silver Legend with Black Letters	White Legend with Black Letters	Black Legend with White Letters	Silver Legend with Black Letters	White Legend with Black Letters	Black Legend with White Letters	Silver Legend with Black Letters	White Legend with Black Letters	Black Legend with White Letters			
	KN200	KN300	KN800	KN200	KN300	KN800	KN200	KN300	KN800	KN200	KN300	KN800
For Push Button or Pilot Light												
t ()	200 P	200 P	200 P	100 P	100 P	100 P	700 P	700 P	700 P	200	300	800
t t	200 P	200 P	200 P	100 P	100 P	100 P	700 P	700 P	700 P	200	300	800
t	201 P	201 P	201 P	101 P	101 P	101 P	701 P	701 P	701 P	201	301	801
	202 P	202 P	202 P	102 P	102 P	102 P	702 P	702 P	702 P	202	302	802
	203 P	203 P	203 P	103 P	103 P	103 P	703 P	703 P	703 P	203	303	803
	204 P	204 P	204 P	104 P	104 P	104 P	704 P	704 P	704 P	204	304	804
E . t	205 P	205 P	205 P	105 P	105 P	105 P	705 P	705 P	705 P	205	305	805
	206 P	206 P	206 P	106 P	106 P	106 P	706 P	706 P	706 P	206	306	806
	207 P	207 P	207 P	107 P	107 P	107 P	707 P	707 P	707 P	207	307	807
	208 P	208 P	208 P	108 P	108 P	108 P	708 P	708 P	708 P	208	308	808
	209 P	209 P	209 P	109 P	109 P	109 P	709 P	709 P	709 P	209	309	809
	210 P	210 P	210 P	110 P	110 P	110 P	710 P	710 P	710 P	210	310	810
t	211 P	211 P	211 P	111 P	111 P	111 P	711 P	711 P	711 P	211	311	811
h	212 P	212 P	212 P	112 P	112 P	112 P	712 P	712 P	712 P	212	312	812
h	213 P	213 P	213 P	113 P	113 P	113 P	713 P	713 P	713 P	213	313	813
h	214 P	214 P	214 P	114 P	114 P	114 P	714 P	714 P	714 P	214	314	814
h	215 P	215 P	215 P	115 P	115 P	115 P	715 P	715 P	715 P	215	315	815
h	216 P	216 P	216 P	116 P	116 P	116 P	716 P	716 P	716 P	216	316	816
l	217 P	217 P	217 P	117 P	117 P	117 P	717 P	717 P	717 P	217	317	817
	218 P	218 P	218 P	118 P	118 P	118 P	718 P	718 P	718 P	218	318	818
	219 P	219 P	219 P	119 P	119 P	119 P	719 P	719 P	719 P	219	319	819
	220 P	220 P	220 P	120 P	120 P	120 P	720 P	720 P	720 P	220	320	820
	221 P	221 P	221 P	121 P	121 P	121 P	721 P	721 P	721 P	221	321	821
	222 P	222 P	222 P	122 P	122 P	122 P	722 P	722 P	722 P	222	322	822
t	223 P	223 P	223 P	123 P	123 P	123 P	723 P	723 P	723 P	223	323	823
t	224 P	224 P	224 P	124 P	124 P	124 P	724 P	724 P	724 P	224	324	824
t	225 P	225 P	225 P	125 P	125 P	125 P	725 P	725 P	725 P	225	325	825
t	226 P	226 P	226 P	126 P	126 P	126 P	726 P	726 P	726 P	226	326	826
t	227 P	227 P	227 P	127 P	127 P	127 P	727 P	727 P	727 P	227	327	827
t	228 P	228 P	228 P	128 P	128 P	128 P	728 P	728 P	728 P	228	328	828
l	229 P	229 P	229 P	129 P	129 P	129 P	729 P	729 P	729 P	229	329	829
h	230 P	230 P	230 P	130 P	130 P	130 P	730 P	730 P	730 P	230	330	830
h	231 P	231 P	231 P	131 P	131 P	131 P	731 P	731 P	731 P	231	331	831
t	232 P	232 P	232 P	132 P	132 P	132 P	732 P	732 P	732 P	232	332	832
t	233 P	233 P	233 P	133 P	133 P	133 P	733 P	733 P	733 P	233	333	833
t	234 P	234 P	234 P	134 P	134 P	134 P	734 P	734 P	734 P	234	334	834
t	236 P	236 P	236 P	136 P	136 P	136 P	736 P	736 P	736 P	236	336	836
t	237 P	237 P	237 P	137 P	137 P	137 P	737 P	737 P	737 P	237	337	837
P	238 P	238 P	238 P	138 P	138 P	138 P	738 P	738 P	738 P	238	338	838
P	/	/	/	179 P	179 P	179 P	779 P	779 P	779 P	/	379	/
For Selector Switch or Selector Push Button												
t	239 P	239 P	239 P	139 P	139 P	139 P	739 P	739 P	739 P	239	339	839
t	240 P	240 P	240 P	140 P	140 P	140 P	740 P	740 P	740 P	240	340	840
t	241 P	241 P	241 P	141 P	141 P	141 P	741 P	741 P	741 P	241	341	841
t	242 P	242 P	242 P	142 P	142 P	142 P	742 P	742 P	742 P	242	342	842
t	243 P	243 P	243 P	143 P	143 P	143 P	743 P	743 P	743 P	243	343	843
t	244 P	244 P	244 P	144 P	144 P	144 P	744 P	744 P	744 P	244	344	844
t	245 P	245 P	245 P	145 P	145 P	145 P	745 P	745 P	745 P	245	345	845
t	246 P	246 P	246 P	146 P	146 P	146 P	746 P	746 P	746 P	246	346	846
t	247 P	247 P	247 P	147 P	147 P	147 P	747 P	747 P	747 P	247	347	847
t	248 P	248 P	248 P	148 P	148 P	148 P	748 P	748 P	748 P	248	348	848
t	250 P	250 P	250 P	150 P	150 P	150 P	750 P	750 P	750 P	250	350	850
t	251 P	251 P	251 P	151 P	151 P	151 P	751 P	751 P	751 P	251	351	851
t	253 P	253 P	253 P	153 P	153 P	153 P	753 P	753 P	753 P	253	353	853
t	254 P	254 P	254 P	154 P	154 P	154 P	754 P	754 P	754 P	254	354	854
t	255 P	255 P	255 P	155 P	155 P	155 P	755 P	755 P	755 P	255	355	855
t	256 P	256 P	256 P	156 P	156 P	156 P	756 P	756 P	756 P	256	356	856
t	257 P	257 P	257 P	157 P	157 P	157 P	757 P	757 P	757 P	257	357	857
t	258 P	258 P	258 P	158 P	158 P	158 P	758 P	758 P	758 P	258	358	858
t	259 P	259 P	259 P	159 P	159 P	159 P	759 P	759 P	759 P	259	359	859
t	260 P	260 P	260 P	160 P	160 P	160 P	760 P	760 P	760 P	260	360	860
t	262 P	262 P	262 P	162 P	162 P	162 P	762 P	762 P	762 P	262	362	862
t	263 P	263 P	263 P	163 P	163 P	163 P	763 P	763 P	763 P	263	363	863
t	264 P	264 P	264 P	164 P	164 P	164 P	764 P	764 P	764 P	264	364	864
t	265 P	265 P	265 P	165 P	165 P	165 P	765 P	765 P	765 P	265	365	865
t	267 P	267 P	267 P	167 P	167 P	167 P	767 P	767 P	767 P	267	367	867
t	270 P	270 P	270 P	170 P	170 P	170 P	770 P	770 P	770 P	270	370	870
t	277 P	277 P	277 P	177 P	177 P	177 P	777 P	777 P	777 P	277	377	877
t	278 P	278 P	278 P	178 P	178 P	178 P	778 P	778 P	778 P	278	378	878

Push Buttons—Class 9001 Type K and SK— 30 mm
Accessories


Legend Plates—Special Marking

Legend Plate	Description	Type	Price
t		t	
100*P (P t) ▲ 2 1/4"		P . 17-81	\$2.90
()	h t	199 P	
		199 P	12.30
		199 P	
		199 P	
200	t	t	
()		P . 17-81	2.90
		299	
		299	12.30
		299	
200*P (P t) ▲ 1.7"		t	
()	h t	P . 17-81	2.90
		299 P	
		299 P	12.30
		299 P	
		299 P	
300	t	t	
()		P . 17-81	2.90
		399	
		399	12.30
400		400	6.60
()		499	15.20
500	t	t	2.90
()		599	
		519	12.30
600		600	6.60
()		699	
		699	15.20
		t	
		17-81	2.90
700*P (P t) ▲ 2 1/2"		799 P	
()	h t	799 P	12.30
		799 P	


▲ h (t):

h h t t t

Mounting Hole For All Types K, SK, and KX Control Unit



HOLE PUNCH:
Use Greenlee Tool #60242 for punching mounting hole and notch.



Minimum Centerline Spacing for Type K & SK Control Units

Legend Plate	Operator	Centerline Spacing (Inches)					
		A	B	C	D	E	F
Legend Plate Orientation Position #1							
2 5	t P h tt	1.75	1.31	1.44	2.25	1.69	0.88
	1 3/8" . h	1.75	1.31	1.44	2.25	1.69	0.88
	2 1/4" . h	2.25	1.31	1.44	2.25	2.25	1.12
	t th	1.75	1.31	1.44	2.25	1.69	0.88
3	t P h tt	2.00	1.31	1.44	2.25	1.75	0.88
	1 3/8" . h	2.00	1.31	1.44	2.25	1.75	0.88
	2 1/4" . h	2.25	1.31	1.44	2.25	2.25	1.12
	t th	2.00	1.31	1.44	2.25	1.75	0.88
4	t P h tt	1.94	1.31	1.44	2.25	1.62	0.88
	1 3/8" . h	1.94	1.31	1.44	2.25	1.62	0.88
	2 1/4" . h	2.25	1.31	1.44	2.25	2.25	1.12
	t th	1.74	1.31	1.44	2.25	1.62	0.88
6	t P h tt	2.38	1.62	1.44	2.25	2.25	1.12
	1 3/8" . h	2.38	1.62	1.44	2.25	2.25	1.12
	2 1/4" . h	2.38	1.62	1.44	2.25	2.25	1.12
	t th	2.38	1.62	1.44	2.25	2.25	1.12

Legend Plate Orientation Position #2

2 5	t P h tt	1.62	1.31	1.44	2.25	1.75	0.88
	1 3/8" . h	1.62	1.31	1.44	2.25	1.75	0.88
	2 1/4" . h	2.25	1.31	1.44	2.25	1.12	
	t th	1.62	1.31	1.44	2.25	1.75	0.88
3	t P h tt	1.75	1.31	1.44	2.25	2.00	0.88
	1 3/8" . h	1.75	1.31	1.44	2.25	2.00	0.88
	2 1/4" . h	2.25	1.31	1.44	2.25	1.12	
	t th	1.75	1.31	1.44	2.25	2.00	0.88
4	t P h tt	1.62	1.31	1.44	2.25	1.94	1.00
	1 3/8" . h	1.62	1.31	1.44	2.25	1.94	1.00
	2 1/4" . h	2.25	1.31	1.44	2.25	1.12	
	t th	1.62	1.31	1.44	2.25	1.94	1.00
6	t P h tt	2.25	1.31	1.62	2.38	2.38	0.88
	1 3/8" . h	2.25	1.31	1.62	2.38	2.38	0.88
	2 1/4" . h	2.25	1.31	1.62	2.38	2.38	1.12
	t th	2.25	1.31	1.62	2.38	2.38	0.88

Special Legend Plates

	Type KN500 (For Use with Dual Function Operators KR6, KR7 and KR67)	
	Standard Markings	
Type	Green	Red
500 501 502	t t	t
Type	Black	Black
520 521 522 523 524 525 526	t t	t


For the most up-to-date information

2004 h E t
h t
8/1/04


(Does not include Color Caps, Mushroom Buttons, Knobs, Selector Switch Cams, Contact Blocks, Light Modules or Legend Plates)

Description	For UL Types/NEMA		Price
	1, 3R, 4, 12, 13	4, 4X, 13	
-l t P h tt (E t)	2	2	\$25.70
-l t P h tt ()	3	3	25.70
-l t P h tt (h tt / -)	20	20	25.70
-l t P h tt (t)	6	...	52.00
-l t P h tt (t l t)	67	...	81.00
-l t P h tt (t l t)	7	...	81.00
t P t t t P h	8 ▲★	8 ▲	50.00
t P t P h	9 ▲★	9 ▲	80.00
l t P h tt (P t)	1▲, ■	1▲, ■	28.50
l t P h tt P h - - t()	2▲, ■ ♦	2▲, ■ ♦	19.20
l t P h tt (t)	3▲, ■	...	28.50
t P t▲h t	P	P	19.20
3P t t t th	4 ▲	4 ▲	24.20
3P t t h t t t th	5 ▲	5 ▲	43.20
3P t t ▲ t t t th	6 ▲	6 ▲	43.20
3P t t h t t t th	7 ▲	7 ▲	43.20


▲ t t t t h (9001 2) h t .
 ■ t t t - t t t t (9001 2).
 ★ h t h h-t t t t .
 2¼% *21 t t h 1% 2¼% . 1% *20 t t . h * t h h 17-84.



2 Position



3 Position



4 Position

$$(I \quad X)$$

2 blocks mounted side by side only: 2, 3 4 t
t t th (- t , t).

2 blocks mounted in tandem on one side only: 2 t h tt .

2 blocks mounted in tandem (total of four blocks):

3 blocks mounted in tandem (total of six blocks): $h \quad tt \quad (\quad - \quad t \quad t \quad)$.



#42259



25490
3211 03



E10054()



▲ 26817
3218 02

-22 t +140 h h t t 50% t h t
-30 t +60

X: h () X t
1, 2, 3, 3, 4, 6, 12 13 t

: h t
1, 2, 3, 3 , 4, 4X, 6, 12 13 t .
. X: h t 17-79.

, X: t 9001 0001.

t 9001 0001.

X: t 9001 0001.

t t t #9001 0001.

Push Buttons—Class 9001 Type K and SK—30 mm
Replacement Parts

Ring Nuts

Used On	Type	Used On	Type	Price
1	44	1	44	\$12.30
30- 37	45	...	...	2.90
70- 73	45	...	...	2.90
20, 21, 22, 23	45	20, 21, 22, 23	45	2.90
20, 21, 22, 23	46	20, 21, 22, 23	46	2.90
2	49	2	49	2.90
3	111	...	...	12.30
P	41	P	41	2.90
1	41	1	41	2.90
11	42	11	42	2.90
12	42	12	42	2.90
12	41	12	41	2.90
13, 14, 15	55	...	...	2.90
2	42	2	42	2.90
20	49	...	...	2.90
24	49	...	...	2.90
25	49	...	...	2.90
3	40	3	40	2.90
4	41	4	41	2.90
5	41	5	41	2.90
6	47	...	...	2.90
67	47	...	...	2.90
7	47	...	...	2.90
8	58	8	6509704401	2.90
9	41	9	41	2.90
	45		45	2.90
	46		46	2.90
			41	2.90
			40	2.90
	49		49	2.90

Replacement Lamps For Series A-F (black) Light Modules

Light Module Type	Lamp Number (ANSI)	Square D Replacement Lamps	
		Part Number	Price
1	E44★	...	...
2	E1490	2550101003	\$ 8.30
3	E44★	...	...
4	E1490	2550101003	8.30
5	E44★	...	...
6	E44★	...	...
7	E44★	...	...
8	E44★	...	...
9	E755	2550101020	8.30
0.4()5599.(568)		050 0.4(40)10(03) / 2 19 31.77 0 -0.0211 .0 (3)530(0) / 1 1.97 -31.5 -1.2 -0.0154. 1 568 0.4(2)5599.(568)	

★ E44 E755 t h (E755).l E44 t h t
E755 (2550101020) t t t . 17-77.

Repair Parts

Description	Part Number	Price
E10	2941101100	\$6.60
11, 12, 11, 12	3105217001	6.60
t t () 9001 44 & 44	4487 63XI	5.30
t t	6509701801	1.30
t P t l t h -P	6509701901	1.30
t t t th	3105406401	1.30
t t t (	6509702001	1.30
t)	6509704901	N/C
h -l h t	6512231201	1.30
h h t h (t . t)	6509705001	1.30
P h -P t t t th	6512240601	1.30
	54	N/C
	6512243201	4.80
	4458 20X3	6.30

KU Replacement Ring Nuts (Threaded Inside and Out)

Used On	Part Number	Price
1h h 8, 27, 37, 47	3105204101	\$2.90
17, 18	3105205901	7.10

Interlock

	h t t h tt h t tt h h h 9001 KR11, KR12, SKR11, SKR12, SKRU1 SKRU11 t . t t h tt K3 t . t . h tt h tt t t t . h K3 t . does not h t t h tt th t . t . t h h tt h K3 t . t h h t . h t t	
	Type	Price
	3	\$19.10

Screwdriver

	
t th t t h t .	
Type	Price
69	\$23.70

Wrenches

			
95		1	
Where Used		Type	Price
t h t t , X, t t		95	\$28.50
t t t		1	47.60

h t t t h , t / t , t t , h t (t t)
h h h h t t . l h t t t t 17-88 h h 17-92. t
h t t h , t P t t t -603. 4, 4X, 13/ E 4, 4X, 13.
h t 17-79.


Single Illuminated and Non-Illuminated Push Buttons

Description	Button Color	Legend Marking	Contacts	Type	Price
		t t		X 101	\$57.00
		t t		X 102	
		t t		X 133	42.80
		t		X 134	42.80
	h	E t		X 105	86.00
Illuminated	h	E t		X 135	71.00
	h	E t		X 103	134.00
	h	E t		X 104	
Illuminated—110-120 V, 50-60 Hz		t t		X P106	162.00
	h	E t		X P106	


Dual Push Buttons

Description	Top Button (#1)	Bottom Button (#2)	Contacts	Type	Price
	(t t)	(t t)		X 111	\$114.
	(t t)	(t t)		X 136	86.
	(t t)	(t t)		X 112	119.
	(t t)	(t t)		X 113	119.
	(t t)	(t t)		X 114	119.
	(t t)	(t t)		X 140	90.
	(t t)	(t t)		X 141	90.
	(t t)	(t t)		X 142	90.
	(t t)	(t t)		X E115	114.
	(t t)	(t t)		X 116	114.

Dual Push Button With One Pilot Light

Description	Top Button (#1)	Middle Lens (#2)	Bottom Button (#3)	Contacts	Type	Price
	(t t)	()	(t t)		X 117	\$209.
	(t t)	()	(t t)		X 137	180.
	(t t)	()	(t t)		X 118	219.
	(t t)	()	(t t)		X 119	219.
	(t t)	()	(t t)		X 120	171.

Dual Push Button With Dual Pilot Lights

Description	Top Button (#1)	Left Lens (#2)	Right Lens (#3)	Bottom Button (#4)	Contacts	Type Number	Price
	(t t)	()	()	(t t)		X 121	\$323.
	(h t)	1	2	(t t)		X 132	333.
	(t t)	()	()	(t t)		X 138	294.
	(t t)	()	()	(t t)		X 122	351.

Selector Switches

Non-Illuminated						
Description	Positions	Legend	Knob	Contacts	Type	Price
	2- t.	-			X 125	\$66.
	2- t.	-			X 139	52.
	3- t.	- - t.			X 126	66.
	3- t.	- - t.			X 127	95.

Illuminated—110-120 V, 50-60 Hz, Transformer


Description	Positions	Legend	Knob	Contacts	Type	Price
	2- t.	-			X 128	\$143.
	3- t.	- - t.			X 129	143.
	3- t.	- - t.			X 130	171.
	3- t.	- - t.			X 130	171.

Single Pilot Light

Description	Lens Color	Legend Marking	Type	Price
	t		XP 107	\$105.
	P h - - t		X 109	134.

Dual Push-To-Test Pilot Light

(Pushing Button #1 Tests Pilot Light #2—Pushing Button #4 Tests Pilot Light #3)

Description	Top Button (#1)	Left Lens (#2)	Right Lens (#3)	Bottom Button (#4)	Type	Price
					X 123	\$312.
					X 123	\$312.

Dual Pilot Light

Description	Left Lens (#1)	Right Lens (#2)	Type	Price
			XP 124	\$191.
			XP 124	\$191.

Four-Field Pilot Light

Description	Top Left (#1)	Top Right (#2)	Bottom Left (#3)	Bottom Right (#4)	Type Number	Price
	h t				XP 131	\$362.
	h t				XP 131	\$362.

Push Buttons—Class 9001 Type KX—30 mm

Square Multifunction Operators




www.SquareD.com

For the most up-to-date information

Push Button and Pilot Light Combinations—UL Types 4, 4X, 13/NEMA 4, 4X, 13




Single Button
Momentary
9001KXRA, KXRB




Dual Push Button
(Non-Illuminated Only)
9001KXRC, KXRD, KXRE, KXRF




Two Push Buttons
(1 & 3)
One Pilot Light (2)
9001KXRG, KXRH, KXRJ, KXRK




Two Push Buttons
(1 & 4)
Two Pilot Lights (2 & 3)
9001KXRL, KXRM



Single Push Button Operator
Non-Illuminated




Dual Push Button Operator
Non-Illuminated




Single Push Button Operator
Illuminated

Dual Push Button Operator
Illuminated



Dual Lamp Push Button Operator



Dual Dimensions: **INCHES**
Millimeters

h t 17-79. h t t h h t . h t t t (t t t h X
X P t), h 17-94. l t t t t h t ,
t t 17-93.

◇ 9001 KX

Square Multifunction

Single and Dual Push Button Codes

Standard Single Momentary (Non-Illuminated)	RA
Standard Single Momentary (Illuminated) □	RB
Two Momentary (Non-Illuminated)	RC
Two Momentary with Interlock (Non-Illuminated)	RD
Two Maintained with Interlock (Non-Illuminated)	RE
One Momentary/One Maintained with Interlock (Non-Illuminated)	RF
Mushroom Single Momentary (Non-Illuminated)	RN
Mushroom Single Momentary (Illuminated) □	RP

Push Button & Pilot Light Combination Codes

Two Momentary Push Buttons with No Interlock and a Single Pilot Light □	RG
Two Momentary Push Buttons with Interlock and a Single Pilot Light □	RH
Two Maintained Push Buttons with Interlock and a Single Pilot Light □	RJ
One Momentary/One Maintained with Interlock and a Single Pilot Light □	RK
Two Momentary Push Buttons with No Interlock and Dual Pilot Lights △	RL
Two Momentary Push Buttons with Interlock and Dual Pilot Lights △	RM

Illuminated Operators Only: Add Voltage Assembly Code

Non-Illuminated Operators

Blank

Color Codes ■▼

(Choose one lens color per lens location)

Leave blank if location does not exist or no lens is required.

Amber	A
Black★	B
Green	G
Blue	L
Red	R
White	W
No lens color or no location	Blank

1	1
2	2
3	3
4	4

X , X	X , X
X , X P	X E , X
X , X	X , X
X , X	X

Blank

"H" Code Contact Block Assembled to Operator

No Contact Blocks

Blank

Price

\$19.10

19.10

38.00

42.80

66.00

66.00

42.80

42.80

47.60

57.00

86.00

38.00

77.00

105.00

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C

N/C


N/C

N/C


N/C




9001KXS



Selector Switch Operator Non-Illuminated



**Selector Switch Operator
Illuminated**



Key Operator Selector Switch

Dual Dimensions: **INCHES**
Millimeters

Non-Illuminated and Illuminated 2 Position Selector Switch Operators— UL Types 4, 4X, 13/NEMA 4, 4X, 13

h t 17-79. t

★ 9001 KX


Square Multifunction

Selector Switch Codes

t	(-l t) Δ	SA
t	h tt h t(-l t)	SB
t	h tt h t(-l t) Δ	SC
t	(l t)	SJ
t	h tt h t(l t)	SK
t	h tt h t(l t) Δ	SL
t	t Δ	SR
t	t h tt h t	SS
t	t h tt h t Δ	ST

Cam Codes

(Choose one based on contact closure sequence, refer to page 17-64)



Illuminated Operator Only: Add Voltage Assembly Code

Non-Illuminated Operators or Keyed

Key Withdrawal Codes (Keyed Operators Only)



Color Codes ■


Amber	A	6.60
Black (Non-Illuminated only)	B	6.60
Green	G	6.60
Blue	L	6.60
Red	R	6.60
White	W	6.60
No Color, Keyed, or Two Color Knob	Blank	N/C

"H" Code Contact Block Assembled to Operator	◆	
No Contact Blocks	Blank	N/C

Two Color Selector Switch Knob▼

t	Y178	28.50
-l t t	Blank	N/C

■ h 17-77. P h t h
 ◆ E t th h 17-80. (, , t t) :2 .Note: t t = (4 t t). P t t t t
 ★ t t , t 17-87. I h t t t t h h t t t t t t . Do not add knob color code
 when using Form Y178.
 △ E



2 Position

t		17-94
t	t	17-78
t	t	17-80
t	t	17-93
t	t	17-94
t	tP t	17-94
		17-84

t t t #9001 0001.

Push Buttons—Class 9001 Type KX—30 mm

Square Multifunction Operator Selector Switches


SQUA
www.S
For the r

Non-Illuminated and Illuminated 3 Position Selector Switch Oper
UL Types 4, 4X, 13/NEMA 4, 4X, 13


h t 17-79. t t +



9001KXS



Selector Switch Operator
Non-Illuminated



Selector Switch Op
Illuminate

Push Buttons—Class 9001 Type KX—30 mm

Accessories

SQUARE D
www.SquareD.com
For the most up-to-date information

Lockout for Push Buttons

Used On	Type	Price
X - X E X - X X - X X - X X - X	X 4	\$28.50

Closing Plate


Type	Price
X 52	\$9.50

Boot for Push Buttons and Pilot Lights

Used On	Type	Price
P h X P t t h t	X 7	\$19.10

Boot For Selector Switches

Description	Used On	Knob Color	Type	Price
t with knob h t t t t t	X t t t (t) t		X 17 X 17 X 17	\$28.50



Shrouds (used to color code Type KX operators)

Type	Used On	Color	Type	Price
h	P h t t P t h t		X 41E X 41 X 41 X 41 X 41	\$4.80
h t	X t		X 40E X 40 X 40 X 40 X 40 X 40	4.80
			Type	Price
			6508900401	N/C

Lamp and Lens Removal Kit

Type	Price
X 11	\$14.30

Button Covers

Description	For Use on	Color	Type	Code	Price
2- X 200	XP X	h t	X 28▲ X 28▲ X 28▲ X 28▲ X 28▲	▲ ▲ ▲ ▲ ▲	\$6.60
X 400	X (P t 1 & 4)	h t	X 4 X 4 X 4 X 4 X 4		6.60
X 500	X (P t 2 & 3)	h t	X 5 X 5 X 5 X 5 X 5		6.60
1 X 100	XP	h t	X 48■ X 48■ X 48■ X 48■ X 48■	◆ ◆ ◆ ◆ ◆	6.60
X 100	X X	h t	X 1 X 1 X 1 X 1 X 1		6.60
X 100	X P	h t	X 1 X 1 X 1 X 1 X 1		11.40
X 200	X X X X X	h t	X 2 X 2 X 2 X 2 X 2		6.60
X 300	X (P t 2) X (P t 2) X (P t 2) X (P t 2)	h t	X 3 X 3 X 3 X 3 X 3		6.60
X 400	X (P t 1 & 3) X (P t 1 & 3) X (P t 1 & 3) X (P t 1 & 3) X (P t 1 & 3) X (P t 1 & 4) X (P t 1 & 4)	h t	X 4 X 4 X 4 X 4 X 4 X 4 X 4		6.60
X 500	X (P t 2 & 3) X (P t 2 & 3)	h t	X 5 X 5 X 5 X 5 X 5		6.60
X 100	XP	h t	X 8 X 8 X 8 X 8 X 8		6.60
X 100	X X	h t	X 1 X 1 X 1 X 1 X 1		6.60

▲ E h X 28
t #1 #2 h t XP h t , 2 t X 28.
▲ h t #1 #2 h t XP h t , 2 t X 28.
\$6.60.
■ E h X 48
t #1 #2 h t XP h t , 2 t X 48.
◆ h t #1 #2 h t XP h t , 2 t X 48.
\$6.60.
★ h t #1 #2 h t XP h t , 2 t X 48.
t #2.

t t , t #9001 0001.

Environment

t t	t IE 529	IP65, h t t IP66, t h tt h
	t 50, 22.2 .94	1, 4X, 12, 13, h t t
t t	CE	IE 947-1, IE /E 60947-5-1, IE 947-5-4, E 60947-1, I 4520, 508, 22.2 .14
P t t t	UL E164353 SP 44087 3211 03	t h t h t t t t : 600; 300

Contact Block Characteristics

Electrical Characteristics

t	t IE 947-1	1 24 (0.22 3) h t 1 22 (0.34 3) 2 16 (1.5 2) h h (P l l t 1) tt t4 5.5
t t h t t t IE /E 60947-5-1	t t : t -15	600: = 600 ▼ = 1.2 , = 240 ▼ = 3 , = 120 ▼ = 6 t h t = 10
	t t : t -13	300: = 250 ▼ = 0.1 , = 125 ▼ = 0.22
▼ t t P E E IE	t	24 ▼; 19.2 t 30 ▼; 21.6 t 24.6 ▼ 120 ▼; 102 t 132 ▼ 240 ▼; 195 t 264 ▼
t t P E E IE	t	24 ▼ / : 18 120 ▼ : 14 240 ▼ : 14



XALD101

Start or Stop Function (light gray base, RAL7035; dark gray lid, RAL7016)

Description	Type of Push	Type of Contact		Marking	Catalog Number	Price
		N.O.	N.C.			

Marking on Legend Holder

1 t h tt	h	1	...	t t	X 101	\$32.80
	h	...	1	t	X 111	32.80

Marking on Legend Holder

1 h h h tt 40 t		...	1	E t	X 164	38.20
-----------------------	--	-----	---	-----	-------	-------



XALK174

Emergency Stop Function (light gray base, RAL7035; yellow lid, RAL1012)

Description	Type	Type of Contact		Catalog Number	Price
		N.O.	N.C.		
1 h h h tt 40 t	t	...	1	X 174	\$53.00
	t	...	1	X 178	67.00
1 h h h tt 40 (.455)	t	...	1	X 184	67.00
	t	...	1	X 188	67.00
1 h h h tt 40 P h -	t	...	1	X 194	44.80



XALD211

Start-Stop Function (light gray base, RAL7035; dark gray lid, RAL7016)

Description	Type of Push	Type of Contact		Text	Catalog Number	Price
		N.O.	N.C.			

Text on legend plate

2 t h tt	1 h	1	...	t t	X 211	\$32.80
	1 h	...	1	t		
	1 h	1	...		X 221	32.80
	1 h	1	...			

Three Function (light gray base, RAL7035; dark gray lid, RAL7016)

Description	Type of Push	Type of Contact		Text	Catalog Number	Price
		N.O.	N.C.			

Text on push button—no legend plates

3 t h tt	1 h 1 h 1 h	1	...		X 341	\$65.
		...	1	t		
		1	...			
		1	...			
		...	1	t	X 311	65.
		1	...			
		1	...			
		...	1	t		
		1	...		X 321	65.



XALD321

t t , t #9001 0001.



XALD02




ZENL1111



ZALV**



ZB5SZ3



ZB5AZ905

Empty Enclosures ▲

Table with 4 columns: Description, Number of Holes, Catalog Number, Price. Rows include data for enclosures with 1 to 5 holes and catalog numbers X 01 to X 05.

Electrical Block and Accessories (for mounting on metal plate at back of enclosure) ▲

Table with 5 columns: Description, Type, Color, Catalog Number, Price. Rows include data for electrical blocks with screw clamp terminal connections and various types (24, 120, 230).

Table with 4 columns: Description, Application, Catalog Number, Price. Rows include data for accessories for electrical blocks.

▲ t X 5 t , P h tt X 5 22 t t 17-34.

t t , t #9001 0001.

Glass-reinforced polyester insulated enclosures XAPA

t	- t
	: 4 5 ()
P t t t t t	t : t t t
tt t	t : -25 t +70 (-13 t +158) t : -40 t +70 (-40 t +158)
t t	IP65 t IE 529 IP657 t 20-010, 4, 4X, 12
E t h t t	II t IE 536 20-030
t	: 3, 20-455: 850 ; IE 92: 960 ; 94: ▼
h t	h t t , , t , t , t , ,
t	

Die Cast metal enclosures XAPG

t	(X P 1-X P4), (X P 5)
	: 4 5 (); 1, 2, 4, 12; t 1, 4, 4X, 12
P t t t t t	t : t t t : t t t
tt t	t : -25 t +70 (-13 t +158) t : -40 t +70 (-40 t +158)
t t	IP65 t IE 529 IP657 t 20-010, 4, 12
E t h t t	I t IE 536 20-030
h t	t t t t
t	t ()

Flush mount enclosures XAPE

t	t t.l t t t
P t t t t t	t : t t t
tt t	t : -25 t +70 (-13 t +158) t : -40 t +70 (-40 t +158)
t t	IP65 t IE 529 IP657 t 20-010, 1, 4, 4X, 12
E t h t t	I t IE 536 20-030
h t	h t t t , t , t , h , t , h t ,
t	h : - t t



E164353
(X P)



44087
3211 03



Undrilled Enclosures, Glass-Reinforced Polyester



XAPA1100

Type		H x W Dimensions		Catalog Number	Price
		IN	mm		
E 4, 4X, 13 h 3.27 .(83)	h h	3.34 5.75	85 146	X P 1100	\$55.00
		3.34 8.90	85 226	X P 2100	90.00
	h h	5.95 9.49	151 241	X P 3100	142.00
		5.95 9.49	151 241	X P 4100	189.00
P t	h t t h	X P 1100		X P 100	11.00
		X P 2100		X P 200	12.30
		X P 3100 4100		X P 300	16.00

Drilled Insulated Enclosures, Glass-Reinforced Polyester



XAPA1104

Type	Number of Knockouts 22 mm	Number of Rows		H x W Dimensions		Catalog Number	Price
		Vertical	Horizontal	IN	mm		
E 4, 4X, 13 h 3.27 .(83) 1.58 .(40) t h	1	1	1	3.35 X 5.75	85 X 146	X P 1110	\$57.00
	2	1	2	3.35 X 5.75	85 X 146	X P 1120	57.00
	4	2	2	3.35 X 5.75	85 X 146	X P 1104	57.00
	8	2	4	3.35 X 8.90	85 X 226	X P 2108	91.00
	16	4	4	5.94 X 9.49	151 X 241	X P 3116	195.00
P t	h t t h	X P 1110		X P 110		X P 110	11.00
		X P 1120		X P 120		X P 120	11.00
		X P 1104		X P 104		X P 104	11.00
		X P 2108		X P 208		X P 208	12.30
		X P 3116		X P 316		X P 316	16.00

t t , t #9001 0001.

Push Buttons and Operator Interface
22 mm Push Buttons XAP Enclosures

17 PUSH BUTTONS AND OPERATOR INTERFACE



XAPG39400



XAPG29703



XAPE302



XAPE303

Undrilled Die Cast Enclosures (Painted Gray RAL7032)

Table with 8 columns: Type, Material, Usable Depth (IN, mm), H x W x D Dimensions (IN, mm), Catalog Number, Price. Rows include enclosure types E 4, 13 and E 4, 13 (30) with various dimensions and prices.

Drilled Die Cast Enclosures (Painted Gray RAL7032)

Table with 8 columns: Type, Material, Usable Depth (IN, mm), Number of 22 mm knockouts, H x W x D Dimensions (IN, mm), Catalog Number, Price. Rows include enclosure types E 4, 13 (30) and E 4, 13 (40) with various dimensions and prices.

Drilled Flush Plates

Table with 6 columns: Type, Material, Number of 22 mm holes, H x W Dimensions (IN, mm), Catalog Number, Price. Rows include enclosure types E 4, 13 (30) and E 4, 13 (40) with various dimensions and prices.

Optional Back Box (for finger protection, if required)

Table with 5 columns: Type, Material, For Use With, Catalog Number, Price. Rows include enclosure types P t t and I t with various dimensions and prices.



**NEMA 1
Surface Mounting
Type BG201**



**NEMA 1
Flush Mounting
(w/o pullbox)
Type BF201**



**NEMA 4
Type BW243**



**NEMA 7 and 9
Type BR103**

Control Stations

Many items are stock or can be furnished as a quick ship using a "Universal" station plus accessories.

No. of Units	Nameplate Markings and Features	Contact Symbol See page 17-101	Surface Mounting NEMA 1 ♦		Stainless Steel Flush Plate (Pullbox not included) ♦		Watertight and Dusttight NEMA 4 ♦		For Hazardous Locations Class I, Div. I & II Groups B, C and D Class II Div. I & II Groups E, F and G NEMA 7 & 9 ♦	
			Type	Price	Type	Price	Type	Price	Type	Price
1	t t	1	101	\$57.	101	\$77.	146	\$180.	101	\$242.
	t	3	102	57.	102	77.	147	180.	...	...
	t (h tt)	3	103	66.	...	...	151	191.	103	252.
	t (h t)	3	104	86.	...	...	148	180.	104	242.
	(/ h l t)▲	16	107	55.	107	74.	159	179.	107	240.
	- (t th)	19	111	57.	111	77.	...	...	...	...
2	- - t (t th)	17	112	57.	112	77.	...	...	...	...
	t th (/ h l t)▲	19 17	114	55.	114	74.	...	...	...	...
	P t h t: 120 ▼ /	121	121	134.	121	152.	...	...	...	...
	P t h t: 120 ▼ /	121	122	134.	122	152.	...	...	...	...
	P t h t (/ h l) : 120 ▼ / ▲	121	123	126.	123	146.	...	...	...	...
	t t t	145	201	57.	201	77.	240	180.	204	242.
3	t t t	146	202	71.	202	90.	252	180.	202	242.
	t t t (h t)	145	203	66.	...	...	250	191.	203	252.
	t t t (h t t)	145	204	86.	...	...	241	180.	204	242.
	t t t (h t t t)	145	205	77.	...	...	246	200.	205	261.
	-	146	206	71.	206	90.	242	180.	206	242.
	-	146	207	71.	207	90.	244	180.	207	242.
	-	146	208	71.	208	90.	243	180.	208	242.
	- h	146	209	71.	209	90.	253	180.	209	242.
	-	145	210	57.	210	77.	245	180.	210	242.
	-	146	211	71.	211	90.	254	180.	211	242.
	(/ h l t)▲	25	214	52.	214	71.	260	176.	214	237.
	t t t (t t t)	10	215	86.	215	105.	255	209.	215	270.
	- (t t t)	10	216	86.	216	105.	256	209.	216	270.
	- t (t t t)	10	217	86.	217	105.	257	209.	217	270.
	t t t	10	...	...	...	...	...	...	219	294.
	(t h t , h t t t)	10	218	81.	218	99.	258	204.	218	266.
	(t t t t / h l t)▲	19 & 121	221	209.	221	228.	▲	h t t t t		
	- (t th), P t h t: 120 ▼ /	17 & 121	223	209.	223	228.	h t t t t			
- t (t th),	17 19 & 121	224	200.	224	207.	h t t t t	17-100			
P t h t: 120 ▼ /	17 & 1	225	86.	225	105.	h t t t t	2.0 2.13 h			
(/ h l t & / h l)▲	17 19 & 16	226	81.	226	99.	1_ 2_ t				
- - t (t th) & t (P h tt)						3_				
(/ h l t)▲										
3	t- - t	109	301	114.	301	138.	♦	h t t t t		
	- - t	109	302	114.	302	138.	h t t t t	17-101.		
	- t	109	303	114.	303	138.	h t t t t	(/		
	- h - t	109	304	114.	304	138.	h t t t t	)		
	h - t	109	305	114.	305	138.	h t t t t			
	t t - t	109	306	114.	306	138.	h t t t t	h t t t t		
	- - t (h t t)	109	316	114.	...	...	E 4			
	- - t (h t t)	109	322	143.	...	...	h t t t t	17-100.		
	h - t (h t t)	109	325	143.	...	...				
	(/ h l t)▲	109	326	143.	...	...				
		8	307	108.	307	132.				
	t t t t , P t h t: 120 ▼ /	145 & 121	308	209.	308	228.				
	P h tt (2) & P t h t: 120 ▼ /	25 & 121	309	198.	309	218.				
	(/ h l t & / h l)▲	10 & 121	310	228.	310	248.				
	t t t (t t t) &	10 & 121	311	228.	311	248.				
	P t h t: 120 ▼ /	10 & 121	312	228.	312	248.				
	- (t t t) & P t	10 & 121	313	218.	313	236.				
	h t: 120 ▼ /	17 & 145	314	114.	314	134.				
- t (t t t) &	17 19 & 25	315	108.	315	126.					
P t h t: 120 ▼ /										
P h tt (t t t) & P t										
h t: 120 ▼ / (/ h l t & / h l)▲										
- - t (t th) &										
t t t (P h tt)										
t th & 2 P h										
tt (/ h l t)▲										

17 PUSH BUTTONS AND OPERATOR INTERFACE

Push Buttons—Class 9001 Type B—Accessories

Standard Duty Control Stations



www.SquareD.com


For the most up-to-date information

17 PUSH BUTTONS AND OPERATOR INTERFACE




h t t t t h
t t
E : h tt
P, 9001 102. 301

Color	Type	Price
For NEMA 1 surface mounting stations		
	301	\$ 9.50
	302	11.00
For NEMA 4		
	303	9.50



t t E 1 t
t t , tt t .
h tt 2 3 t t th .
t t h h .

Type	Price
321	\$28.50



Pilot Light Lenses

Color	For NEMA 1 Surface Mounting	For NEMA 1 Flush Mounting	Price
	Type	Type	
	331	341	\$7.10
	332	342	

Interchangeable Push Button Legend Inserts

Marking	For NEMA 1 Surface Mounting Push Button & Mushroom Caps	For NEMA 1 Flush Mounting	For NEMA 4 and NEMA 7-9 Lever Type Square	For NEMA 4 Button Type Round	For NEMA 4 Mushroom Button Inserts	Price Each
	Type	Type	Type	Type	Type	
t t t t h h t - -	101	131	161	259	282	\$2.40
	102	132	162	260	283	
	103	133	163	...	...	
	104	134	164	...	...	
	105	135	165	255	278	
	106	136	166	256	279	
	107	137	167	263	286	
	108	138	168	264	287	
	109	139	169	261	284	
	110	140	170	262	285	
	111	141	171	253	276	
	112	142	172	254	277	
	113	143	173	...	...	
	114	144	174	...	...	
	115	145	175	257	280	
	116	146	176	258	281	
	117	147	177	265	288	
	118	148	178	266	289	
	119	149	179	...	...	
	129	159	189	251	251	
	129	159	189	252	252	
	t 10 .					



Replacement Covers for BF and BW

For Types	Types	Price
101 123	3040000311	\$61.70
201 226	3040000302	38.00
301 315	3110104301	61.70
146 147	108	11.90
148▲	109	23.70
149 159	108	11.90
240	219	11.90
241▲	220	23.70
242 260	219	11.90

▲ t h t t t .

Miscellaneous Accessories

Description	Type	Price
t th t & t th	9001 351	\$ 7.10
(120P)	2550105005	11.00
t h	124	57.00

Interchangeable Selector Switch Legend Plates

Marking	For NEMA 1 Surface Mounting	For NEMA 1 Flush Mounting	Price Each
	Type	Type	
- t - t - t - t - t - t - t - t - t - t - t - t	201	231	\$2.40
	202	232	
	203	233	
	204	234	
	205	235	
	206	236	
	207	237	
	208	238	
	209	239	
	210	240	
	211	241	
	212	242	
t 10 .			

Legend Insert Kits

(t h t t t .)

Where Used:	Type	Price
E 1 t	100 (l 1 h 101h 119)	\$45.20
	200 (l 1 h 201h 212)	28.50
E 1 h t	130 (l 1 h 131h 149)	45.20
	230 (l 1 h 231h 242)	28.50
E 4	160 (l 1 h 161h 179)	45.20
E 4	250 (l 1 h 253h 266)	33.30
E 4	300 (l 1 h 276h 289)	33.30


t t , t #9001 0001.



Type BGC214



Type BGB214



BOC361

Replacement Interiors For Type B Standard Duty Push Button Stations

For Control Station Types	Contact Symbol	Contact Block Assembly ▲ Type	Price	Terminal Block Wiring Receptacle Type	Price
101 107	16	107	\$26.10	107	\$28.50
111 114	19 17	114	26.10	114	28.50
121 123	121	123	98.00	123	28.50
201 214	25	214	23.70	214	28.50
215 218	10	218	52.00	214	28.50
221 224	7 19 & 121	224	156.00	224	42.80
225 226	17 19 & 16	226	38.00	226	42.80
301 307	8	214 & 107	23.70 26.10	214 & 107	28.50 28.50
308 309	25 & 121	214 & 123	23.70 98.00	214 & 123	28.50 28.50
310 313	10 & 121	218 & 123	52.00 98.00	214 & 123	28.50 28.50
314 315	17 19 & 25	214 & 114	23.70 26.10	214 & 114	28.50 28.50
101 107	16	107	26.10	107	28.50
111 114	17 19	114	26.10	114	28.50
121 123	121	123	98.00	123	28.50
201 214	25	214	23.70	214	28.50
215 218	10	218	52.00	214	28.50
221 224	17 19 & 121	224	156.00	224	42.80
225 226	17 19 & 16	226	38.00	226	42.80
301 307 316 326	8	307	26.10	307	57.00
308 309	25 & 121	309	141.00	309	57.00
310 313	10 & 121	313	161.00	309	57.00
314 315	17 19 & 25	315	49.80	315	57.00
101 107	16	107	26.10	107	28.50
202 214	25	214	23.70	214	28.50
215 219	10	218	52.00	214	28.50
101 107	16	107	26.10	107	28.50
202 214	25	214	23.70	214	28.50
215 218	10	218	52.00	214	28.50
146 159	16	360	84.00		
240 260	25	361	84.00		
255 258	10	362	84.00		

[illegible]


**“C” Shaped Mounting Bracket
for 9001BR Interior**

3110112001	Price
	\$4.80

Electrical Contact Ratings

AC—NEMA B600							DC—NEMA P600			
Volts	Inductive 35% Power Factor				Continuous Carrying Amperes	Resistive 75% Power Factor	Volts	Inductive and Resistive		
	Make		Break					Make, Break and Continuous Carrying Amperes	Make and Break Amperes	Continuous Carrying Amperes
	Amps	VA	Amps	VA						
120	30.5	3600	3.75	360	5	5	120	1.1	5	
240	15	3600	1.5	360	5	5			5	
480	7.5	3600	.75	360	5	5	240	.55	5	
600	6	3600	.6	360	5	5	600	.2	5	

Contact Symbols



t t t #9001 0001.

Push Buttons—Class 9001 Type KY and SKY—30 mm
Industrial Duty Enclosures

17 PUSH BUTTONS AND OPERATOR INTERFACE




Type KYAF9

Enclosures Only (For Customer Assembly)

No. of Units	UL Types 1, 3 and 13/NEMA 1, 3 and 13				UL Types 1, 3, 4 and 13 NEMA 1, 3, 4 and 13 ▲		UL Types 1, 3, 4, 4X and 13 NEMA 1, 3, 4, 4X and 13 ▲			
	Surface Mounting		Flush Mounting without Pullbox ◆ ★		Surface Mounting		Surface Mounting			
	Sheet Steel		Cast Zinc		Die Cast Aluminum ★		Stainless Steel (304) ▼		Polymeric (Plastic)	
	Type	Price	Type	Price	Type	Price	Type	Price	Type	Price
1	1	\$ 95.	11	\$ 57.	1	\$ 95.	1	\$ 171.	1	\$114.
2	2	105.	21■	57.	2■	105.	2	180.	2	134.
3	3	123.	31■	66.	3■	123.	3	248.	3	152.
4	4	152.	41■	95.	4■	152.	4	323.	4	179.
6	6	191.	6	134.	6	191.	6	476.	6	362.
9	9	248.	9	180.	t		9	588.	9	476.
12	12	333.	12	257.	12	333.	12	713.	12	546.
16	16	428.	16	351.	16	428.	16	941.	16	617.
20	20	531.	t		t		20	1044.	20	713.
25	25	654.	t		t		25	1329.	25	831.
30	30	783.	t		t		30	1566.	t	

Custom Built Control Stations are available. Consult Catalog #9001CT0001.



Type KYSS3

No. of Units	UL Types 1, 3 and 13/NEMA 1, 3 and 13				UL Types 1, 3, 4 and 13 NEMA 1, 3, 4 and 13 ▲		UL Types 1, 3, 4, 4X and 13 NEMA 1, 3, 4, 4X and 13 ▲			
	Surface Mounting		Flush Mounting without Pullbox ◆ ★		Surface Mounting		Surface Mounting			
	Sheet Steel		Cast Zinc		Die Cast Aluminum ★		Stainless Steel (304) ▼		Polymeric (Plastic)	
	Type	Price	Type	Price	Type	Price	Type	Price	Type	Price
1	100	\$ 95.	110	\$ 57.	10	\$ 95.	100	\$ 171.	100	\$114.
2	200	105.	210■	57.	20■	105.	200	180.	200	134.
3	300	123.	310■	66.	30■	123.	300	248.	300	152.
4	400	152.	410■	95.	40■	152.	400	323.	400	179.
6	600	191.	60	134.	60	191.	600	476.	600	362.
9	900	248.	90	180.	90	248.	900	588.	900	476.
12	1200	333.	120	257.	120	333.	1200	713.	1200	546.
16	1600	428.	160	351.	160	428.	1600	941.	1600	617.
20	2000	531.	t		t		2000	1044.	2000	713.
25	2500	654.	t		t		2500	1329.	2500	831.
30	3000	783.	t		t		3000	1566.	t	

▲ E 1, 3, 4, 6, 12, 13. h h t t E 1, 3, 12, 13. t t t ▲ 1, 3, 4, 6, 12 13/
■ 200 t t h t h h h t .
◆ h 1, 6 t t . P t t t t h
★ t t h 304 t t 316 t t (25%) 35
▼ t t .

Note: t , 17-83.



Type KY3



Type KZ31



Type KZ310



Type KYAF900



Type SKY2

t t , t #9001 0001.

[illegible]

Type KYK31

No of Units	Legend Plate Marking And Features	Type	Price	Consists of			
				Enclosure	Operators	Contact Blocks	Legend Plates
1	- - t (t th)	111	\$162.	1	43	1	260
	- - t (th) (h t t)	121 ■	228.	1	43	51	260
	- (t th)	18	162.	1	11	1	242
	- (th)	110	162.	1	11	1	244
	- (t th) (h t t)	122 ■	228.	1	11	51	244
	120 ▼ P t h t	120 ■	180.	1	P1 31	1	201
	t t	11	152.	1	1	1	201
	t t (h t t)	125 ■	219.	1	1	51	201
	t t (h tt)	12	180.	1	4	1	201
	t	13	152.	1	1	1	202
	t (h tt)	14	180.	1	4	1	202
	t (h t)	15	180.	1	3 , 4	1	202
	t (h t t t t t)	124 ■	248.	1	3 , 4	51	202
	t h (h t t t t t) t)	123 ■	276.	1	4 , 4	51	202
t	116	219.	1	15	1	799	
t (E)	117	219.	1 1	15	1	799 P	
2	- - (t t)	24	219.	2	1 , 1	1 , 1	206 , 207
	- t (t t)	224	248.	2	1 , 3 , 4	1 , 1	218 , 202
	- (h t t)	218	219.	2	1 , 3	1 , 1	203 , 204
	- (h t t t)	222 ■	351.	2	1 , 3	51 , 51	203 , 204
	- (h t t t)	221	219.	2	11	1	203 , 204
	-	26	219.	2	1 , 1	1 , 1	209 , 208
	t t - t	21	219.	2	1 , 3	1 , 1	201 , 202
	t t - t (h t t t)	223 ■	351.	2	1 , 3	51 , 51	201 , 202
	t t - t (t t t)	23	248.	2	1 , 3 , 4	1 , 1	201 , 202
	t t - t (t t t t)	27	219.	2	11	1	201 , 202
	t t - t (h t t t t t)	220 ■	285.	2	11	51	201 , 202
	t t - t (h t)	22	248.	2	1 , 4	1 , 1	201 , 202
	-	25	219.	2	1 , 1	1 , 1	211 , 210
	3	- - t t - t	35	305.	3	11 , 1 , 3	1 , 1 , 1
- - t		31	294.	3	1 , 1 , 3	1 , 1 , 1	206 , 207 , 202
- - t (t t t) t t		326	323.	3	1 , 1 , 3 , 4	1 , 1 , 1	206 , 207 , 202
t t - t (h t t)		322 ■	522.	3	1 , 1 , 3 , 4	51 , 51 , 51	206 , 207 , 202
h t - t		34	294.	3	1 , 1 , 3	1 , 1 , 1	214 , 215 , 202
/ - t t - t		36	305.	3	11 , 1 , 3	1 , 1 , 1	242 , 201 , 202
- - t		33	294.	3	1 , 1 , 3	1 , 1 , 1	209 , 208 , 202
- - t (t t t) t t		327	323.	3	1 , 1 , 3 , 4	1 , 1 , 1	209 , 208 , 202
t t		323 ■	522.	3	1 , 1 , 3 , 4	51 , 51 , 51	209 , 208 , 202
120 ▼ P t h t t t t t		317	314.	3	P1 31 , 1 , 3	2 , 3	200 , 201 , 202
120 ▼ P t h t t t t t		321 ■	456.	3	P1 31 , 1 , 3	51 , 51	200 , 201 , 202
(h t t)		324	323.	3	P38 31 , 1 , 3	1 , 1	200 , 201 , 202
120 ▼ / P t h t t t t t		32	294.	3	1 , 1 , 3	1 , 1 , 1	211 , 210 , 202
- - t		325	323.	3	1 , 1 , 3 , 4	1 , 1 , 1	211 , 210 , 202
- - t (t t t)	328 ■	522.	3	1 , 1 , 3 , 4	51 , 51 , 51	211 , 210 , 202	
- - t (t t)							

▲ t t t t t h t



Type KYSS300*



Type SKY201*

***See page 17-104 for selection and pricing.**

```

t          t  tt ..... 17-103 17-104
t          t  tt ..... 17-102
..... t 9001 0001

t          t . t #9001 0001.

```

Push Buttons—Class 9001 Type KY and SKY—30 mm

Control Stations for Types K and KY

Assembled Control Stations—UL Types 1, 3, 4, and 13/NEMA 1, 3, 4 and 13▲

No. of Units	Legend Plate Marking and Features	Type	Price	Consists of			
				Enclosure	Operators	Contact Blocks	Legend Plates
1		101	\$228.	1	1	1	101 P
		103	213.	1	1	3	102 P
		105	261.	1	3 h 5	3	102 P
		110	237.	1	11	1	144 P
		111	237.	1	43	1	160 P
2		201	281.	2	1, 3	1, 3	101 P, 102 P
		203	327.	2	1, 3 h 5	1, 3	101 P, 102 P
		205	294.	2	1, 1	1, 1	111 P, 110 P
		210	294.	2	11	1, 1	101 P, 102 P
3		301	404.	3	1, 1, 3	1, 1, 3	106 P, 107 P, 102 P
		302	404.	3	1, 1, 3	1, 1, 3	111 P, 110 P, 102 P
		303	404.	3	1, 1, 3	1, 1, 3	109 P, 108 P, 102 P
		304	404.	3	1, 1, 3	1, 1, 3	114 P, 115 P, 102 P
		308	452.	3	1, 1, 3 / 5	1, 1, 3	106 P, 107 P, 102 P
		309	452.	3	1, 1, 3 / 5	1, 1, 3	111 P, 110 P, 102 P
		310	452.	3	1, 1, 3 / 5	1, 1, 3	109 P, 108 P, 102 P
		311	452.	3	1, 1, 3 / 5	1, 1, 3	114 P, 115 P, 102 P

Assembled Control Stations—UL Types 1, 3, 4, 4X and 13/NEMA 1, 3, 4, 4X, and 13▲

No. of Units	Legend Plate Marking and Features	Type	Price	Consists of			
				Enclosure	Operators	Contact Blocks	Legend Plates
1		101	\$228.	1	1	1	101 P
		103	213.	1	3	3	102 P
		105	261.	1	3 h 5	3	102 P
		110	237.	1	11	1	144 P
		111	237.	1	43	1	160 P
2		201	281.	2	1, 3	1, 3	101 P, 102 P
		203	327.	2	1, 3 h 5	1, 3	101 P, 102 P
		205	294.	2	1, 1	1, 1	111 P, 110 P
		210	294.	2	11	1, 1	101 P, 102 P
3		301	404.	3	1, 1, 3	1, 1, 3	106 P, 107 P, 102 P
		302	404.	3	1, 1, 3	1, 1, 3	111 P, 110 P, 102 P
		303	404.	3	1, 1, 3	1, 1, 3	109 P, 108 P, 102 P
		304	404.	3	1, 1, 3	1, 1, 3	114 P, 115 P, 102 P
		308	452.	3	1, 1, 3 / 5	1, 1, 3	106 P, 107 P, 102 P
		309	452.	3	1, 1, 3 / 5	1, 1, 3	111 P, 110 P, 102 P
		310	452.	3	1, 1, 3 / 5	1, 1, 3	109 P, 108 P, 102 P
		311	452.	3	1, 1, 3 / 5	1, 1, 3	114 P, 115 P, 102 P

Assembled Control Stations—UL Types 1, 3, 4, 4X and 13/NEMA 1, 3, 4, 4X, and 13▲

No. of Units	Legend Plate Marking and Features	Type	Price	Consists of			
				Enclosure	Operators	Contact Blocks	Legend Plates
1		121 ■	\$249.	1	43	51	160 P
		111	180.	1	43	1	160 P
		107	171.	1	1	1	118 P
		108	180.	1	11	1	143 P
		122 ■	248.	1	11	51	144 P
		110	180.	1	11		
		101	171.	1	1	1	144 P
		125 ■	237.	1	1	51	101 P
		103	156.	1	3	3	102 P
		105	204.	1	3, 5	3	102 P
		124 ■	285.	1	3, 5	51	102 P
2		204	248.	2	1, 1	1, 1	106 P, 107 P
		222 ■	380.	2	1, 3	51, 51	103 P, 104 P
		206	248.	2	1, 1	1, 1	109 P, 108 P
		201	233.	2	1, 3	1, 3	101 P, 102 P
		203	281.	2	1, 1, 5	1, 3	101 P, 102 P
		220 ■	314.	2	11	51	101 P, 102 P
		223 ■	380.	2	1, 3	51, 51	101 P, 102 P
3		301	309.	3	1, 1, 3	1, 1, 3	106 P, 107 P, 102 P
		322 ■	522.	3	1, 1, 3	51, 51, 51	106 P, 107 P, 102 P
		304	309.	3	1, 1, 3	1, 1, 3	114 P, 115 P, 102 P
		303	309.	3	1, 1, 3	1, 1, 3	109 P, 108 P, 102 P
		323 ■	522.	3	1, 1, 3	51, 51, 51	109 P, 108 P, 102 P
		315	354.	3	P1 31, 1, 3	1, 3	101 P, 102 P
		305	309.	3	1, 1, 3	1, 1, 3	101 P, 118 P, 102 P
		302	309.	3	1, 1, 3	1, 1, 3	111 P, 110 P, 102 P
		328 ■	522.	3	1, 1, 3	51, 51, 51	111 P, 110 P, 102 P

▲ t t t t h h t t II 2 III.
■ t t t t h h t

Stainless Steel NEMA 1 Flush Plates



Two Unit



Type KY192



Type KZC299

UL Listed
File E42259
CNN NKCR
CSA Listed
File LR25490
Class 321103

h h t t , , X t t t h t 2" 3"
t t t t t t h , 3 1/2" h t h t t t t
t h t , t t h h t is not oiltight/watertight. h t h t t
t h t , t t h t t t t t

No. of Units	Description	Type	Price
1	1 t h t , , t	25	\$19.10
2	2 t h t , , t	26	28.50
3	3 t h t , , t	27	38.00
4	4 t h t , , t	28	57.00

▲ t t t t t 1 3/16"

General Purpose NEMA 1 Flush Mounting Control Station With Pull Box For Type K Control Units

Number of Units	Enclosure Only For Customer Assembly		Custom Built Factory Assembled Control Stations	
	Type	Price	Type	Price
1	P1	\$123.	P10	\$123.
2	P2	143.	P20	143.
3	P3	180.	P30	180.
4	P4	191.	P40	191.
5	P5	228.	P50	228.
6	P6	237.	P60	237.
7	P7	314.	P70	314.
8	P8	323.	P80	323.

Special Features			Price
Type 304 Stainless steel flush plate (Form Y242):			
1 4			Add
5 8			\$208.
			265.
Omit Pull Box (Form Y243):			
1 2			Deduct
3 4			57.
5 6			77.
7 8			95.
			114.

30 mm Security Control Stations

Description	Type of Cylinder	Cylinder Finish	Special Features	Cast Aluminum Enclosure		Satin Chrome Finish Flush Mounted with Box	
				Type	Price	Type	Price
t	t	h	t h ♦(6 P)	198	\$356.	198	\$452.
t	t	h	t h tt ★(6 P)	199	356.	199	452.
t	t	h	t h ♦(7 P)	197	498.	197	594.
t	t	h	t h tt ★(7 P)	196	428.	196	522.
t	t	h	t h tt ★(7 P)	195	498.	195	594.
t	t	h	t h tt ★(7 P)	194	428.	194	522.
t	t	h	t h tt ★(7 P)	193	356.	193	452.
t	t	h	t h tt ★(7 P)	192	594.	192	689.
t	t	h	t h ♦(6 P)	298	428.	298	522.
t	t	h	t h tt ★(6 P)	299	428.	299	522.
t	t	h	t h tt ★(6 P)	297	570.	297	665.
t	t	h	t h tt ★(7 P)	296	498.	296	594.
t	t	h	t h tt ★(7 P)	295	570.	295	665.
t	t	h	t h tt ★(7 P)	294	498.	294	594.
t	t	h	t h tt ★(7 P)	293	428.	293	522.
t	t	h	t h tt ★(7 P)	292	665.	292	759.

■ t E 3 t t t h t , t h t t t t t h
♦ h t t t h t , t h t t t t t h
★ h t t t h t , t h t t t t t h

Contact your nearest Square D/Schneider Electric sales office if:

- t
- t t t
- E t
- t t
- t
- t

Repair Parts

Replacement or duplicate keys:


t \$9.50 h 5 t t h t , h h t t
t t t t h t t t t t t t
h .P \$23.70 h 5 t t t t t t
t t t t t

Electrical Ratings

t : 9007 2 th h PE t th h
▲ E t . 19-37 t t h 9007 2.
t tt : 9001 1 t t h t h tt . 17-78 9001 1
t t . (Note: The KA1 contact block has a maximum voltage rating of 300 V (NEMA A300) when used in the Type KZC station.)
t t , t #9001 0001.



Push Buttons—Class 9001 Type O NEMA 13—XVL LED
Compact Pilot Light



Push Buttons and Operator Interface
XVB Illuminated Beacons and Indicating Banks
XVB Characteristics

17 PUSH BUTTONS AND OPERATOR INTERFACE



XVB L3



XVB L4B



XVB L6B
5 Joule



XVB L8B
10 Joule

Environment

Table with 2 columns: Specification, Value. Rows include UL, CE, and IP65 ratings.

Electrical Characteristics

Table with 2 columns: Specification, Value. Rows include voltage, power, and current ratings.

Illuminated Beacons with Steady Light (2.75 in./70 mm diameter)

Table with 5 columns: Description, Light Source and Voltage, Color, Catalog Number, Price. Rows list various catalog numbers and prices.

Illuminated Beacons with Flashing Light (2.75 in./70 mm diameter)

Table with 5 columns: Description, Light Source and Voltage, Color, Catalog Number, Price. Rows list various catalog numbers and prices.

Illuminated Beacons with 10 Joule Strobe (2.75 in./70 mm diameter)

Table with 5 columns: Description, Light Source and Voltage, Color, Catalog Number, Price. Rows list various catalog numbers and prices.

Note: h X L6, X L8 (\$190.00).

#9001 0001.



XVCB3*



XVCB4**



XVCB6**
5 Joule



XVCB8**
10 Joule



XVCB9*



XVBC21
(cover not shown)

Illuminated Lens Units with Steady Light (2.75 in./70 mm diameter)

Description	Light Source and Voltage	Color	Catalog Number	Price
I t t	(10) 250 ▼ /		X▼ 33	\$40.40
			X▼ 34	
			X▼ 35	
			X▼ 36	
			X▼ 37	
			X▼ 38	

Illuminated Lens Unit with Flashing Light (2.75 in./70 mm diameter)

Description	Light Source and Voltage	Color	Catalog Number	Price
I t t	(10) 24 ▼ 24 48 ▼		X▼ 4 3	\$94.00
			X▼ 4 4	
			X▼ 4 5	
			X▼ 4 6	
			X▼ 4 7	
			X▼ 4 8	
			X▼ 4 3	94.00
	(10) 48 230 ▼		X▼ 4 4	
			X▼ 4 5	
			X▼ 4 6	
			X▼ 4 7	
			X▼ 4 8	
			X▼ 4 8	

17-110.

Illuminated Lens Units with 10 Joule Strobe (2.75 in./70 mm diameter)

Description	Light Source and Voltage	Color	Catalog Number ▲	Price
I t t	(10) 24 ▼ /		X▼ 8 3	\$209.00
			X▼ 8 4	
			X▼ 8 5	
			X▼ 8 6	
			X▼ 8 7	
			X▼ 8 8	
	(10) 120 ▼		X▼ 8 3	209.00
			X▼ 8 4	
			X▼ 8 5	
			X▼ 8 6	
			X▼ 8 7	
			X▼ 8 8	
	(10) 230 ▼		X▼ 8 3	209.00
			X▼ 8 4	
			X▼ 8 5	
			X▼ 8 6	
			X▼ 8 7	
			X▼ 8 8	

▲ 5 t, X▼ 6**, t X▼ 8** (\$155.00).

Note: h t X▼ t h X▼ t .

Audible Sounder Units (2.75 in./70 mm diameter)

Description	Supply Voltage	Catalog Number	Price
90 t t	12 48 ▼ /	X▼ 9	\$145.00
t t 75 90 t t tt t	120 230 ▼	X▼ 9	228.00


Base Units + Cover (for direct or tube mounting, 2.75 in./70 mm diameter)

Description	For use with	Type	Catalog Number	Price
tt t+ t		t	X▼ 21	\$40.40


t t , t #9001 0001.




XVBC02



XVBC020



XVBC11



XVBC12

Accessories Common to Beacon and Indicating Banks


Description	Characteristics		Catalog Number	Price
	IN	mm		
tt	3.94	100	XV 02	\$12.20
	15.75	400	XV 03	23.00
	31.50	800	XV 04	33.70
tt t	3.94	100	XV 020	7.80
	15.75	400	XV 030	23.00
	31.50	800	XV 040	41.40
t t h t	t t XV 0		XV 11	16.10
t t	XV 11+t	t XV 0 t h t	XV 12	32.30
l tt t 15 , 10	12 V /		L1 L	5.40
	24 V /		L1 L	
	48 V /		L1 LE	
	120 V /		L1 L	
	230 V /		L1 L	
l tt t 15 , 7	12 V /		L1 E	5.40
	24 V /		L1 E	
	48 V /		L1 EE	
	120 V /		L1 E	
	230 V /		L1 E	
LE (tt) 15	24 V /	h t	L1 1	72.00
			L1 3	
			L1 4	
			L1 6	
		-	L1 8	
	120 V	h t	L1 1	72.00
			L1 3	
			L1 4	
			L1 6	
		-	L1 8	
t t h h t	h 12 (13.5) 0.4 t 0.55 (10 t 14) t		XV 14	5.20
t t	1/2" P (t t)		XV 00	2.10

Accessories Specific to Indicating Banks


Description	Characteristics	Catalog Number	Price
t	6	XV 22	\$2.10
t 5 h	l t t t t	XV 23	8.30
h t 85 h (XV 23)	l t t t t	XV 1	3.10
h t 52	l t t t t	XV 2	3.10

Wiring Diagrams, Base Units

Screw terminals
Torque to 4.4 in-lb (0.5 N•m)



2 x #16 AWG (1.5 mm²)
1 x #14 AWG (2.5 mm²)



t t , t #9001 0001.



XVDLS

h X V L t t h t t t .

Environment

	t E164353 44087 3211 03	E164353 44087 3211-03
t t	CE	IE /E 60947-5-1, 508, 22.2 .14
t t	50, 22.2 .94 IE 529 20-010	IP40 ¹
		1 #16 (1.5 ²) t
	t 4.4 - (0.5) t	

Note: h X V L t t 5 .

Illuminated Beacons with Steady Light (1.75 in./45 mm diameter)

Description	Light Source	Color	Catalog Number	Price
1 t t, : 1 t(t t)	l t (5) ▲ 250 ▼		X V L 33	\$33.10
			X V L 34	
			X V L 35	
			X V L 36	
			X V L 37	
			X V L 38	

▲ t h t : 15 tt , t 5 .

Illuminated Beacons with 0.5 Joule Strobe (1.75 in./45 mm diameter)

Description	Light Source	Color	Catalog Number	Price
1 t t, : 1 t(t t)	t 24 ▼ /		X V L 6 3	\$83.00
			X V L 6 4	
			X V L 6 5	
			X V L 6 6	
			X V L 6 7	
			X V L 6 8	
	t 120 ▼		X V L 6 3	83.00
			X V L 6 4	
			X V L 6 5	
			X V L 6 6	
			X V L 6 7	
			X V L 6 8	
	t 230 ▼		X V L 6 3	83.00
			X V L 6 4	
			X V L 6 5	
			X V L 6 6	
			X V L 6 7	
			X V L 6 8	

Accessories

Description	Supply Voltage	Color	Catalog Number	Price
l t t 15 (t t 10)	24 ▼ / , 4 tt	...	L1 E	\$ 4.10
	120 ▼ / , 5 tt	...	L1 E	
	230 ▼ / , 5 tt	...	L1 E	
L1 E t t 15 (t t)	24 ▼ /	h t	L1 1	72.00
			L1 3	
			L1 4	
			L1 6	
			L1 8	
		-	L1 8	
	120 ▼	h t	L1 1	72.00
			L1 3	
			L1 4	
			L1 6	
			L1 8	
		-	L1 8	

t t , t #9001 0001.



XVR1

Environment

Table with 3 columns: Environment, t, and IP65. It lists various environmental conditions and their corresponding IP65 ratings.

Rotating Mirror Beacon (6.5 in./165 mm diameter)

Table with 5 columns: Light Source, Supply Voltage, Color, Catalog Number, and Price. It lists various rotating mirror beacon models and their specifications.

Accessories and Spare Parts

Table with 4 columns: Description, Characteristics, Catalog Number, and Price. It lists various accessories and spare parts for the rotating mirror beacon.

t t , t #9001 0001.

Environment

	UL E164353	SE 44087 3211 03	RA E164353 2
t t	CE	IE /E 60947-5-1, 508	
P t t t t			
t t	IE 60529 50 20-010 22.2 .94	IP65 1, 12 13	

Electrical Characteristics

t	IE t	24 V / : < 60 ; 120 230 V : < 20
	t t 7	24 V / : < 300 ; 120 230 V : 65 35
	h	24 V 24 V : < 250 ; 120 230 V : < 30
	t h t (t)	24 V : 0.3 , 40 ; 120 V : 0.6 , 20 ; 230 V : 0.6 , 11
	t	24 V , 12 ; 120 V , 15 ; 230 V , 15
		2 #16 (1.5 2) h
	t	t t : 4.4 - (0.5)

Components

Base Units with Cover (for direct or tube mounting)

Description	Color	For use with Indicating Banks	Catalog Number	Price
50 t		50 t	XVP 21	\$32.
50 t		50 t	XVP 21	
50 t h -t t t	-h t	50 t	XVP 21	

Illuminated Lens Units

Description	Ring Color	Light Source and Voltage	Lens Color	Catalog Number	Price
Steady or Flashing					
50 t t (IE t h 17-114 t) t		t (7) 250 V		XVP 33 XVP 34 XVP 35 XVP 36 XVP 37 XVP 38	\$29.
	-h t	t (7) 250 V		XVP 33 XVP 34 XVP 35 XVP 36 XVP 37 XVP 38	29.

Strobe

50 t t		t 24 V 0.3		XVP 6 3 XVP 6 4 XVP 6 5 XVP 6 6 XVP 6 7 XVP 6 8	124.
		t 120 V 0.6		XVP 6 3 XVP 6 4 XVP 6 5 XVP 6 6 XVP 6 7 XVP 6 8	
	-h t	t 24 V 0.3		XVP 6 3 XVP 6 4 XVP 6 5 XVP 6 6 XVP 6 7 XVP 6 8	
		t 120 V 0.6		XVP 6 3 XVP 6 4 XVP 6 5 XVP 6 6 XVP 6 7 XVP 6 8	

Audible Sounder Units

Description	Ring Color	Supply Voltage	Catalog Number	Price
50 (IP40 E 1) t		24 V 120 V 230 V	XVP 09 XVP 09 XVP 09	\$104.
t t t , 75 85 t1	-h t	24 V 120 V 230 V	XVP 09 XVP 09 XVP 09	



XVPC21



Lens Unit
with Black Ring



XVPC09B

t t , t #9001 0001.

Push Buttons and Operator Interface

XVP 50 mm Illuminated Indicating Banks

Accessories



DL1BEJ



DL18DB1



XVPC12



XVPC02



XVPC03T
(With Base and Lenses)

LEDs

Description	Voltage	Color	Catalog Number	Price
t - LE Protected LED	24 ▽ /	h t /	1 1 3 3 4 4 6 6 8 8	\$72.
	120 ▽	h t /	1 1 3 3 4 4 6 6 8 8	
	230 ▽	h t /	1 1 3 3 4 4 6 6 8 8	
h LE Protected LED	24 ▽ /	h t /	1 1 3 3 4 4 6 6 8 8	93.
	120 ▽	h t /	1 1 3 3 4 4 6 6 8 8	
	230 ▽	h t /	1 1 3 3 4 4 6 6 8 8	

Incandescent Bulbs


Description	Voltage	Catalog Number	Price
t t 15 , 7	12 ▽ / 24 ▽ / 48 ▽ / 120 ▽ / 230 ▽ /	1 E 1 EE 1 EE 1 EE 1 EE	\$5.40

Accessories

Description	Color	Characteristics		Catalog Number	Price
		IN	mm		
h t h t		4	100	XVP 02	\$21.70
		10	250	XVP 03	26.90
		16	400	XVP 04	32.00
h t		4	100	XVP 02	21.70
		10	250	XVP 03	26.90
		16	400	XVP 04	32.00
	- h t	4	100	XVP 02	21.70
	- h t	10	250	XVP 03	26.90
	- h t	16	400	XVP 04	32.00
t t	- h t	...		XVP 12	10.40
	- h t	...		XVP 12	
t t	...	...		XVP X13	5.20

Wiring Diagram

Cable Connections, Supply line maximum: 1.5 mm² (#16 AWG)



t t , t #9001 0001.



h 9001 70 80 t t t h t t , h t
t tt . h h t h 1/2 h t t tt t t h
h t . t t h . h t t t E 1,3,3,4 4X. h
h t t t t t (1 . /1 . .) h tt h t . h
t t t t

No. of Units	Description	Legend Insert Markings	Mechanical Interlock	Enclosure Color			Price	Contact Symbol	Replacement Interior		
				Yellow	Black	Red			9001 Type	Contact Symbol	Price
2		-		72	72	72	\$84.	146	368	146	\$60.
		- ▲		73	73	73	84.	146	368	146	60.
		t t t		74	74	74	113.	10	358	147	60.
		t t t ▲		75	75	75	84.	145	359	25	60.
		t t t ▲		76	76	76	113.	10	358	147	60.
		-		77	77	77	84.	146	359	25	60.
		-		79	79	79	84.	145	359	25	60.
		-		78	78	...	84.	100	...	...	...
		h t ▲ t		70	70	70	80.	147	366	25	60.
		h t ▲ t		71	71	71	80.	25	359	25	60.
		h t ▲ t		74	74	74	108.	147	358	147	60.
		h t ▲ t		80	80	80	123.	150	367	150	105.
		-		82	82	82	128.	150	367	150	105.

Interchangeable Push Button Legend Inserts

Contact Symbol

Marking	For NEMA 4X Type BW70s and BW80s	Mushroom Button Inserts for NEMA 4X Type BW70s and BW80s	Marking	For NEMA 4X Type BW70s and BW80s	Mushroom Button Inserts for NEMA 4X Type BW70s and BW80s	Price Each
Type	Type	Type	Type	Type	Type	
t t	259	282		257	280	
t	260	283		258	281	
	255	278		265	288	
	256	279		266	289	
	263	286	t			\$2.40
	264	287		251	251	
	261	284	-			
	262	285		252	252	
▲	253	276	-			
	254	277				

Legend Insert Kit—Kit includes one each of standard legend inserts as indicated.

Where Used:	Type	Price
E 4X P h tt	250 (l ' 1 h 253h 266)	\$33.30
70 h	300 (l ' 1 h 276h 289)	33.30
80 tt		

Hanger Bracket

Form	Price
236	\$7.00

t t E t h t(t h 9001 P P t
t t). h h t t .
..... t 9001 0001

Pendant Stations, XAC Standard Duty
Pistol Grips, Enclosures, Contact Blocks



XACA06



XACA03



ZB2BE10•



XENG37•1

Specifications

Table with 2 columns: Specifications and Certifications. Includes UL, CSA, and CE marks.

Pistol Grip Stations

Table with 5 columns: Description, Speeds, Function, Catalog Number, Price. Lists various pistol grip models and their specifications.

Additional technical specifications and notes for the pistol grip stations.

General Purpose Pendants

Table with 3 columns: Enclosures, Catalog Number, Price. Lists general purpose pendant models and their prices.

Additional technical specifications and notes for the general purpose pendants.





ZB2BE10●



XENG37●1



XENG1191



XACS10●



Booted Push Button



Mushroom Head



Selector Switch



Selector Switch
(key operated)



Wobble Stick

Contact Blocks for Operators in Cover

Description	Wiring Diagram	Catalog Number	Price
1 . / t /1	...	2 E101	\$8.20
1 . / t /1	...	2 E102	8.20
1 . . & 1 . . & 1 . / t /2	1	XE 1191	24.50
1 . . & 2 . / t /1	2	XE 1491	24.50
1 . . & 1 . . th /1 / t	3	XE 3781	24.50
1 . . & 1 . . th /1 / t	4	XE 3791	24.50

For Operators in Base of Enclosure ▲

1 . /1	X 101	\$14.30
1 . /1	X 102	14.30
2 . /1	X 103	19.10
2 . /1	X 104	19.10
1 . . & 1 . /1	X 105	19.10

▲ t h XACA03 t.

Wiring Diagrams




Figure 1




Figure 2



Figure 3



Figure 4

Operators ■

Description	Color	Catalog Number	Price
t h tt	h t	X 9411	\$4.10
		X 9412	
		X 9413	
		X 9414	
		X 9415	
		X 9416	
		X 9419	

Description		Mushroom Size	Color	Catalog Number	Price
h h , t	30		2 24	\$18.40	
			2 44		
h h , t	40		2 2	18.40	
			2 4		
h h , h t t /t -t -	30		2 44	39.30	
	40		2 54	39.30	
(t h h t)♦ , h t t /t -t -	30		2 834	56.00	
	40		2 844	56.00	
h h , h t t / t -t -	30		2 74	56.00	
	40		2 14	56.00	
(t h h t)♦ , h t t / t -t -	40		2 944	56.00	

Description					Color	Catalog Number	Price
t	th	/2	t	★		2 2	\$15.00
t	th	/3	t	★		2 3	15.00
t	★	th	/2	t	t	2 4	56.00
t	★	th	/3	t	t	2 5	56.00
t (tt t)						2 2	51.00
						2 4	

Pilot light components

Description	Color	Catalog Number	Price
t / h t (6 t 120 ▼ t)(/)	...	2 ▼006	\$12.30
t / h 130 ▼ (220 240 ▼ t)(/)	...	2 ▼007	26.00
P t h t t t		2 ▼03	4.80
		2 ▼04	
		2 ▼05	
		2 ▼06	
		2 ▼07	
P t h t t t E		2 ▼033	4.80
		2 ▼043	
		2 ▼053	


■ t h tt t . h t t t t t t t
◆ t h h t h t t t t t t t
★ t h XE t t t t t t t t

t t t #9001 0001.


Pendant Stations, XAC Standard Duty Operators

SQUARE D
www.SquareD.com
For the most up-to-date information


17 PUSH BUTTONS AND OPERATOR INTERFACE




XACB961




XACA971




XACA982



XACA983



DL1CE0**
(Incandescent)



DL1CJUS***
(LED)

Enclosure Accessories

Description	Catalog Number	Price
h	2 3	\$6.80
h t (t t)	X 009	4.10
t - t	X 961	3.40
t t	X 971	9.60
P t t tt t h h	X 982	9.60
P t t tt t t th th	X 983	13.70

Lamps

Type	Voltage	Watts	Catalog Number	Price
(9) t	6 ▼ /	1.2	1 006	\$5.50
	12 ▼ /	2.0	1 E012	
	24 ▼ /	2.0	1 E024	
	48 ▼ /	2.4	1 E048	
	130 ▼ /	2.6	1 E130	
(h t h t)	120 ▼ /	...	E51 120▼	7.60
	220 ▼ /	...	E51 220▼	
	380 ▼ /	...	E51 380▼	

Type	Color	Voltage	Catalog Number	Price
1E , 9 t		6 ▼ /	1 0063	\$12.50
		6 ▼ /	1 0064	
		6 ▼ /	1 0065	
		12 ▼ /	1 0123	
		12 ▼ /	1 0124	
		12 ▼ /	1 0125	
		24 ▼ /	1 0243	
		24 ▼ /	1 0244	
		24 ▼ /	1 0245	
		120 ▼ /	1 1203	
		120 ▼ /	1 1204	
		120 ▼ /	1 1205	


PVC Standard Legend Plates 30 x 40 mm

Text▲	Catalog Number	Price	Text▲	Catalog Number	Price
	2 2343	\$2.10		2 2312	\$2.10
	2 2344			2 2311	
	2 2314			2 2367	
	2 2308			2 2313	
E t	2 2330			2 2376	
t	2 2328		- -	2 2388	
	2 2305		t	2 2339	
	2 23		P	2 2326	
- -	2 2384			2 2335	
t	2 2387		t▲	2 2323	
h	2 2338			2 2306	
h 1	2 2369		h t	2 2309	
t	2 2342			2 2334	
t	2 2341			2 2327	
l	2 2503		t t	2 2303	
l h	2 2321		t	2 2304	
	2 2381		t t t	2 2366	
	2 2380		h t	2 2345	
	2 2365		1 t	2 2346	
1 t	2 2310			2 2307	
1	2 2336			2 2370	
1	2 2337		- -	2 2389	
t	2 2372				

▲ t t h h h t t t t t 2. E t t h h h h t t t

Type	Description	Catalog Number	Price
P▼	30 40	2 2101	\$2.10
	h t 30 40	2 4101	
P▼ t	■ , h t tt 30 40	2 2002	8.90
	■ , h t tt 30 40	2 2004	
	■ h t , tt 30 40	2 4001	
	■ , tt 30 40	2 4005	

■ P tt h . h 11 h t () h . t t , t #9001 0001.






Multispeed
9001SKRU2
SKRU3
SKRU4
SKRU5

Diagram illustrating the wiring for the 2868-D30 module, showing connections for Terminals 1, 2, and 3 to the module's internal components (CO, 1, 2) and the module's output terminals (C, 1, 2).

Terminals	2	1	Off	1	2	Terminals
CO	X	X		X	X	C
1	X	X		X	X	1
2	X				X	2

2868-D30



Push Buttons—Class 9001 Type SKYP Pendant Stations

Size	Conduit Entrance Size	Enclosure Only ■	Enclosure For Assembled Station ▲	Price
		Type	Type	
2 tt	3/4" 14 P	P2	P20	\$126.
4 tt	3/4" 14 P	P4	P40	159.
6 tt	1" 11 1/2 P	P6	P60	191.
8 tt	1 1/4" 11 1/2 P	P8	P80	237.
10 tt	1 1/4" 11 1/2 P	P10	P100	285.

Push Button Units★

Number of Buttons Per Unit	Description	Contact Symbol— See Below	Type ♦	Price
2	t l t	7	1	\$86.
2	t l t -l t	5	10	71.
2	t l t	10	11	99.
2	t l t	87	2	180.
2	t l t	88	3	213.
2	t l t	89	4	227.
2	t l t	90	5	237.

♦		1, 10	11		t t	.		2h	5	t		t t
★		t	17-86.									

	Where Used	Marking	Type	Price
	h h 1 11	- t - : E t t : : h - h : : E t t : h - h t t t t t P : -	200☆ 201 202 203 204 205 206 207 208 209 210 211 299	\$5.70 5.70 5.70 5.70 5.70 5.70 5.70 5.70 5.70 5.70 5.70 5.70 24.80
	h th ▼ E	- -	500□ 544□ 545□ 599□	8.60 8.60 8.60 18.00
	h t P t h t Δ E	E . t P -	100◇ 103 104 105 124 138 144 199◇	2.90 2.90 2.90 2.90 2.90 2.90 2.90 12.30

▼				9001	1 t	\$35.60		t	E	4X	t	
△		9001			17-68	17-86.						
□	l		t	,		t t		h t		th	.	
◇	-	t		th								
☆	19 h	t	h	.								

	Type	Price
	52	\$9.50



E42259



▲ 25490
321103



t t t # 9001 0001.


P1	
----	--

h t

Type A
Class 9002



Heavy Duty Industrial Foot Switches—Oiltight, Watertight, Dusttight and Driptight Enclosure, NEMA 2, 4 and 13



Foot Switch Selection

t th t t , h H t h t t . h t
t th t h t t h H t t , t t
H , t t t , t . l t H t th t
H t h t t th t t H h .
H t h h t th () . h t t t h h ; H , H
l t t . h t t t t P t h t .
l t , h , t t t t h t - - t t h t th
t t . h H t h H t H t t H h t
t H . h h t th t t t . H H t th t t t
t H t - - t t t .
E h . h h . t t - - t t t H h t th . h t H :

Type AW Fully Shielded Foot Switch with Oversized Pedal Shield, Side Shields and Safety Door. h t t h h



Type AW Foot Switch with Top Pedal Shield and Side Shields



Type AW with Oversized Pedal Shield and Side Shields



Type AW Foot Switch without Pedal Shield

Description	Features	Fully Shielded with Oversized Pedal Shield, Side Shields and Safety Door		With Oversized Pedal Shield and Side Shields		With Pedal Shield and Side Shields		UNSHIELDED (See warning note▼)	
		Type	Price	Type	Price	Type	Price	Type	Price
P h ■	h t h th	117 ...	\$500. ...	132 ...	\$500. ...	2 7	\$242. 351.	1 ...	\$264. ...
P h ■	h t h th	124 ▲ ...	602. ...	133 ...	602. ...	14 15	351. 461.	13 ...	383. ...
(t P) E h 1	h t h th 1 t t	119 ...	620. ...	134 ...	620. ...	6 9	362. 470.	5 ...	393. ...
(t P) E h 2	h t h th 2 t	...	...	...	...	10	470.	...	...
P h	t t t P h /P h	123	863.	...	...	22	608.	21	663.
t	t t t P h /P h	...	...	...	...	12	352.	11	383.
t	...	5	242.	7	242.	8★	93.	1	102.

Replacement Parts:

9002 :
t
. 65013-010-31


[illegible]

E42259




▲ 25490
184 13.1


Approximate Dimensions



Types AW1, AW5, AW11, AW13 and AW21



Types AW117, AW119, AW123, AW124
Types AW132, AW133 and AW134 (without safety door)



Types AW2, AW6, AW12, AW14 and AW22

Dual Dimensions: **INCHES**
Millimeters

Maximum Current Ratings For Control Circuit Contacts

Type	Volts	AC Amperes			Volts	DC Amperes		
		Inductive 35% Power Factor		Resistive 75% Power Factor		Inductive and Resistive		Con- tinuous
		Make	Break	Make, Break and Continuous		Single Throw	Double Throw	
1h, 117, 132	120 240 480 600	40 20 10 8	15 10 6 5	15 10 6 5	125 250 600	2.0 0.5 0.1	0.5 0.2 0.02	15 15 15
13, 14, 15, 133	120 240 480 600	30 15 7.5 6	3 1.5 0.75 0.6	3 1.5 0.75 0.6	125 250 600 ...	1.0 0.3 0.1 ...	0.2 0.1 ...	10 10 10 ...
11, 12	115 230	36 18	6 3	...	125 250	2.2 1.1	...	...
21, 22, 123	120 240 480 600	15.0 7.5 3.75 3.0	1.5 0.75 0.375 0.3	10 10 10 10	...	...	...	...
124	120 240 480 600	60 30 15 12	6 3 1.5 1.2	10 10 10 10	120 240 600	1.1 0.55 0.2	...	10 10 10

Note: 1h = 1h, 117, 132; th = 11, 12; t = 21, 22, 123; 250 = 250V

TABLE 1
Contact Symbol—Two Stage

Snap Switch		Pedal		
Unit	Circuit	Up	Half Down	Full Down
1	1	0	1	1
	1	1	0	0
2	2	1	1	0
	2	0	0	1

0 = 1 =

TABLE 2
Contact Symbol—Four Stage

Snap Switch		Pedal Position			
Unit	Circuit	Up → Down			
1	1 1	0	0	1	1
	1 1	1	1	0	0
	2 1	0	1	1	1
	2 1	1	0	0	0
2	1 2	1	1	1	0
	1 2	0	0	0	1
	2 2	1	1	1	0
	2 2	0	0	0	1

Rotary Cam Switches K10 Miniature, K2 Custom, K30–K150 Power Switching

A New Extended Offer, Three Ranges: Your Solution

17

PUSH BUTTONS AND
 OPERATOR INTERFACE



- K10 Miniature
- E , 300, 300 ▼, 10
 - t , , h
 - 16 22 t
 - 30 30 t t
 - t h h



- K2 Custom Cam Switches
- E , 300, 300 ▼, 10
 - t , , h
 - t 22 4h
 - t t th
 - X 4 t h



- K30–K150 Power Switching
- 32 t 150 (40h @ 480 ▼)
 - t t ,
 - t 48 48 64 64
 - t t 64 64 88 88
 - t t
 - t h h

t , t #9001 0001.