

# DATA SHEET

## GLV9\_C63631 Series

Part of the simpleLED® Program

## simpleLED GLV9\_C63631 SERIES

The light engine series consist of 9 high power LUXEON Rebel LEDs. It is engineered to provide customers with the flexibility to select the optimal light source for their applications. Customers also have the option of modifying their light engine by selecting their preferred LUXEON Rebel LED, optic and/or connector that best suits the application.

## FEATURES & BENEFITS


- 3 year manufacture (GL-Lighting) warranty
- High-reliability LED sources
- Wide operational temperature range
- Multiple configurable options
- Multiple optic options
- Wide range of drive current
- Multiple CCT's available
- 9 LEDs in series
- Short lead time
- CE certified, UL recognized



GLV91C63631

## TYPICAL APPLICATIONS

- Directional lighting
- Track lighting
- Accent lighting
- Display lighting
- Recessed down lighting



GLV92C63631

Note: All specifications are subject to change without notice.

## simpleLED GLV9\_C63631 WARM WHITE SERIES

PARAMETER		CONDITIONS
PCB		FR4 / MCPCB
Finish		White
Size		Dia 63mm
Source Type		LUXEON Rebel LXM8-PW30
Connector	00	Solder Pad
	20	20cm UL1007 20Awg
	CN	TYCO 2008563-1
Thermal Resistance (p-n junction to Tp)		Rth= 21 K/W (FR4) Rth= 14 K/W (MCPCB)
Rated Lumen Tp=25°C @350mA		>=720lm
CCT		3045k
CRI		Min. 80
Tp Maximum Temperature		80 °C

## ELECTRICAL CHARACTERISTICS

PARAMETER	MIN	TYPICAL	MAX
Forward Voltage (V) @350mA & Tp=25°C	22.5	27	29.25
Power Consumption @350mA (W)	7.9	9.45	10.24
Efficacy (lm/Watt) @350mA, Tp=25°C	>=70	>=76	>=91

Driving Current	100mA	350mA	700mA
-----------------	-------	-------	-------

## ENVIRONMENTAL CHARACTERISTICS

PARAMETER	MIN	MAX
Storage Temperature (°C)	-40	+85
Tp Temperature (°C)	-40	+80

Note: All specifications are subject to change without notice.

## simpleLED GLV9\_C63631 NEUTRAL WHITE SERIES

PARAMETER		CONDITIONS
PCB		FR4 / MCPCB
Finish		White
Size		Dia 63 mm
Source Type		LUXEON Rebel LXML-PWN2
Connector	00	Solder Pad
	20	20cm UL1007 20Awg
	CN	TYCO 2008563-1
Thermal Resistance (p-n junction to Tp)		Rth= 17 K/W (FR4) Rth= 10 K/W (MCPCB)
Rated Lumen Tp=25°C @700mA		>=1800lm
CCT		4100k
CRI		Min. 60
Tp Maximum Temperature		80 °C

## ELECTRICAL CHARACTERISTICS

PARAMETER	MIN	TYPICAL	MAX
Forward Voltage (V) @700mA & Tp=25°C	22.5	27	31.5
Power Consumption @700mA (W)	15.75	18.9	22.05
Efficacy (lm/Watt) @700mA, Tp=25°C	>=81	>=95	>=114
Driving Current	100mA	700mA	1000mA

## ENVIRONMENTAL CHARACTERISTICS

PARAMETER	MIN	MAX
Storage Temperature (°C)	-40	+85
Tp Temperature (°C)	-40	+80

Note: All specifications are subject to change without notice.

## simpleLED GLV9\_C63631 COOL WHITE SERIES

PARAMETER		CONDITIONS
PCB		FR4 / MCPCB
Finish		White
Size		Dia 63 mm
Source Type		LUXEON Rebel LXML-PWC2
Connector	00	Solder Pad
	20	20cm UL1007 20Awg
	CN	TYCO 2008563-1
Thermal Resistance (p-n junction to Tp)		Rth= 17 K/W (FR4) Rth= 10 K/W (MCPCB)
Rated Lumen Tp=25°C @700mA		>=1800lm
CCT		5650k
CRI		Min. 60
Tp Maximum Temperature		80 °C

## ELECTRICAL CHARACTERISTICS

PARAMETER	MIN	TYPICAL	MAX
Forward Voltage (V) @700mA & Tp=25°C	22.5	27	31.5
Power Consumption @700mA (W)	15.75	18.9	22.05
Efficacy (lm/Watt) @700mA, Tp=25°C	>=81	>=95	>=114
Driving Current	100mA	700mA	1000mA

## ENVIRONMENTAL CHARACTERISTICS


PARAMETER	MIN	MAX
Storage Temperature (°C)	-40	+85
Tp Temperature (°C)	-40	+80

Note: All specifications are subject to change without notice.

## MECHANICAL DRAWINGS (GLV91C63631 / FR4)

2D drawing with dimensions:

( Unit: mm)




Note: All specifications are subject to change without notice.

## MECHANICAL DRAWINGS (GLV92C63631 / MCPCB)

2D drawing with dimensions:

( Unit: mm)



Note: All specifications are subject to change without notice.

## PART NUMBERING & ORDERING INFORMATION

### 1. PRODUCT SERIES

GLV91C63631

Circular FR4 with 9 LEDs in series

GLV92C63631

Circular MCPCB with 9 LEDs in series

### 2. CONNECTOR TYPE

00 – Solder Pad

20 – 20cm UL1007 20Awg

CN – TYCO 2008563-1

### 3. LED TYPE

LL - LXML LUXEON REBEL

LB - LXM8 LUXEON REBEL

LG - LXML LUXEON REBEL ES

### 4. NUMBER OF LED

09 - 9 LEDs

### 5. CCT

S30 – 3000K ANSI

D40 – 4000K

S40 – 4000K ANSI

W00 – 5600K

S50 – 5000K ANSI

### 6. FLUX BIN

L – Min 80lm@350mA

N – Min 100lm@350mA

R – Min 160 Lumens@700mA

S – Min 180 Lumens@700mA

T – Min 200 Lumens@700mA

### 7. OPTICS

OBS – 15/22 Degree, single lens

OBN – 27 Degree, single lens

OBF – 38/43 Degree, single lens

Part Number :

GLV9\*C63631 / AA – BB CC DDD E FFF

1                      2            3            4            5            6            7

Note: All specifications are subject to change without notice.



## ACCESSORIES FOR LENS

•Single Lens

No.	BRAND	MANUFACTURER PART #	SIZE	LUXEON REBEL	LUXEON REBEL ES	HOLDER
1	GL	GLVA1BS01Y	Ø13.5x7.3mm	15°	22°	Yes
2		GLVA1BN01Y	Ø13.5x7.3mm	27°	27°	Yes
3		GLVA1BF01Y	Ø13.5x7.3mm	38°	43°	Yes

Part Number :

GLVA1    BS    01    Y  
|            |            |            |  
1           2           3           4

1. ACCESSORIES CATEGORY NUMBER

GLVA1

Optics Number

3. LENS NUMBER

01 – Exclude DF, 1 Lens, With Holder

2. OPTICS ANGLE

BS – 15/22 Degree Lens

BN – 27 Degree Lens

BF – 38/43 Degree Lens



4. RING / HOLDER

Y – With Holder Only


Note: All specifications are subject to change without notice.

## PACKAGING INFORMATION

INNER PACKING	SIZE	TRAY	QTY
TYPE	345*295*11mm	1	12



INNER PACKING	SIZE	TRAY	QTY
TYPE 1	350*300*30mm	1	12
TYPE 2	350*300*250mm	18	216



Note: All specifications are subject to change without notice.

## COMPANY INFORMATION

### About Future Lighting Solutions

Future Lighting Solutions ([www.futurelightingsolutions.com](http://www.futurelightingsolutions.com)) is a leading provider of LED lighting components and support services for solid-state lighting products and installations, including engineering expertise, concept development, full system solutions and online tools that accelerate quality application development. The company is a division of Future Electronics.

### About simpleLED®

Future Lighting Solutions simpleLED program has over 500 combinations of LUXEON® LED & Optic configurations, enabling you to select the right Light Engine for your application, eliminate prototyping delays and accelerating time to market. Additional benefits include UL recognized quality and a 3 year warranty. Visit our website and start innovating.

## CONTACT DETAILS

### In North America:

1-888-LUXEON2

[Americas@futurelightingsolutions.com](mailto:Americas@futurelightingsolutions.com)

### In Europe:

00-800-44FUTURE

[Europe@futurelightingsolutions.com](mailto:Europe@futurelightingsolutions.com)

### In Asia:

+800-LUMILEDS

[Asia@futurelightingsolutions.com](mailto:Asia@futurelightingsolutions.com)

### In Japan:

+81-0120-667-013

[Japan@futurelightingsolutions.com](mailto:Japan@futurelightingsolutions.com)

Note: All specifications are subject to change without notice. Warranty provided by the manufacturer, GL-Lighting.