






2		1				
LOC	DIST	REVISIONS				
HB		P	LTR	DESCRIPTION	DATE	APVD
			C	1.UPDATE TE LOGO 2.ADD LINE IDENTIFICATION 3.TERMINALS TOLERANCE CLARIFICATION4. VENT HOLE CHANGE	ECO-12-005726	09-APR-12
			D	CHANGE THE VENT HOLE SHAPE FROM RECTANGLE TO CIRCLE ONE	ECO-13-015347	16-DEC-13
					D.L	BH.Y
					XL,Y	B,F



		DWN	N.FUNAYAMA		TE Connectivity					
		CHK	T.FUKAYA							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± ± ± ± ± ±	APVD	MJ.HO		NAME				
mm										
										
			PRODUCT SPEC	—						
		APPLICATION SPEC	—		OZ CUSTOMER DRAWING					
MATERIAL		FINISH	WEIGHT	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
—		—				A3	00779	©= 1649399	—	
CUSTOMER DRAWING						SCALE	4 : 1		SHEET 1 OF 2	REV D

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

HB

DIST

REVISIONS

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

NOTES:

1.LOT NO. SYSTEM AS FOLLOWING:

0825

WEEK

YEAR

2.GENERAL TOLERANCE AS FOLLOWING:

TOLERANCE	
0~0.99mm	±0.1
1mm~2.99mm	±0.2
3mm MIN.	±0.3

3.TERMINAL DIMENSION IS NOT INCLUDING SOLDER TIP.


4.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKNESS AND DIAMETER.
+0.5mm FOR LENGTH.

(A1)	3-1649399-0	OZ-SH-148D1	48V	OZ-SH-148D1
(A1)	2-1649399-9	OZ-SH-124D1	24V	OZ-SH-124D1
(A1)	2-1649399-8	OZ-SH-118D1	18V	OZ-SH-118D1
(A1)	2-1649399-7	OZ-SH-112D1	12V	OZ-SH-112D1
(A1)	2-1649399-6	OZ-SH-109D1	9V	OZ-SH-109D1
(A1)	2-1649399-5	OZ-SH-106D1	6V	OZ-SH-106D1
(A1)	2-1649399-4	OZ-SH-105D1	5V	OZ-SH-105D1
(A1)	2-1649399-3	OZ-SS-148D1	48V	OZ-SS-148D1
(A1)	2-1649399-2	OZ-SS-124D1	24V	OZ-SS-124D1
(A1)	2-1649399-1	OZ-SS-118D1	18V	OZ-SS-118D1
(A1)	2-1649399-0	OZ-SS-112D1	12V	OZ-SS-112D1
(A1)	1-1649399-9	OZ-SS-109D1	9V	OZ-SS-109D1
(A1)	1-1649399-8	OZ-SS-106D1	6V	OZ-SS-106D1
(A1)	1-1649399-7	OZ-SS-105D1	5V	OZ-SS-105D1
	1-1649399-6	OZ-SH-148L1	48V	OZ-SH-148L1
	1-1649399-5	OZ-SH-136L1	36V	OZ-SH-136L1
	1-1649399-4	OZ-SH-124L1	24V	OZ-SH-124L1
	1-1649399-3	OZ-SH-118L1	18V	OZ-SH-118L1
	1-1649399-2	OZ-SH-112L1	12V	OZ-SH-112L1
	1-1649399-1	OZ-SH-109L1	9V	OZ-SH-109L1
	1-1649399-0	OZ-SH-106L1	6V	OZ-SH-106L1
	1649399-9	OZ-SH-105L1	5V	OZ-SH-105L1
	1649399-8	OZ-SS-148L1	48V	OZ-SS-148L1
	1649399-7	OZ-SS-136L1	36V	OZ-SS-136L1
	1649399-6	OZ-SS-124L1	24V	OZ-SS-124L1
	1649399-5	OZ-SS-118L1	18V	OZ-SS-118L1
	1649399-4	OZ-SS-112L1	12V	OZ-SS-112L1
	1649399-3	OZ-SS-109L1	9V	OZ-SS-109L1
	1649399-2	OZ-SS-106L1	6V	OZ-SS-106L1
	1649399-1	OZ-SS-105L1	5V	OZ-SS-105L1
	PART NO	EC TYPE NAME	PART B	PART A

RELAY TYPE

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

MATERIAL

—

FINISH

—

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

OZ CUSTOMER DRAWING

SIZE

A3

CAGE CODE

00779

DRAWING NO

1649399

RESTRICTED TO

—

SCALE

4:1

SHEET

2 OF 2

REV

D

UV RESIN

UV SEAL

17

EPOXY RESIN

SEAL

16

Cu ALLOY

HINGE SPRING

15

UL94 V-0

PBT

CASE

14

POLYURETHANE COPPER WIRE

MAGNETIC WIRE

13

UL94 V-0

PET

BASE

12

UL94 V-0

PBT

BOBBIN

11

SOLDER DIP

HCP WIRE

COIL TERMINAL

10

UL94 V-0

PPS

CARD

9

Ag ALLOY

MOVABLE CONTACT

8

Ag ALLOY

STATIONARY CONTACT

7

SOLDER DIP

Cu ALLOY

NC TERMINAL

6

SOLDER DIP

Cu ALLOY

MOVABLE SPRING

5

SOLDER DIP

Cu ALLOY

NO TERMINAL

4

Ni PLATED

STEEL

CORE

3

Ni PLATED

STEEL

ARMATURE

2

Ni PLATED

STEEL

YOKE

1

INCOMBUSTIBILITY

TREATMENT

MATERIAL

DESCRIPTION

ITEM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[OZ-SS-105L1,200](#)