





LOC	DIST	REVISIONS				
		REV	DESCRIPTION	DATE	OWN	APVD
CM	0	AP2	REVISED PER ECO-11-004587	11MAR11	RK	HMR

NOTES:

1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
2. SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
3. DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
4. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
5. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
6. TRADEMARK LOCATION (AMP OR TE CONNECTIVITY).
7. MANUFACTURING LOCATION ID (OPTIONAL).
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



DETAIL A
OPTIONAL CONSTRUCTION


27.43	1.080
26.67	1.050
14.73	.580
11.68	.460
7.62	.300
0.38	.015
0.25	.010
0.13	.005
MM	IN
CONVERSION TABLE	


3-DIMENSIONAL MODEL
NTS

		BLACK	1-480702-9
8	OBSOLETE	GRAY	1-480702-8
		BLUE	1-480702-6
		GREEN	1-480702-5
		YELLOW	1-480702-4
8 SUPERSEDED BY 1-480700-0		ORANGE	1-480702-3
8	OBSOLETE	RED	1-480702-2
		BROWN	1-480702-1
		NATURAL	1-480702-0
		COLOR	PART NUMBER

8 SUPERSEDED BY 1-480700-0





8 OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 08FEB95	 TE Connectivity						
		CHK R. SWING 08FEB95							
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 3. PLC ± - 4. PLC ± - ANGLES ± 0°30'	APVD D. SELF 08FEB95	NAME	PLUG, 4 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)					
		PRODUCT SPEC							
	FINISH -	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
		WEIGHT	-	-	A1		00779	C=480702	-
MATERIAL NYLON, UL 94V-2		CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 2	REV.	AP




LOC	DIST	REVISIONS				
		REV	DATE	BY	APP'D	DESCRIPTION
CM	0					SEE SHEET 1

- NOTES:
1. STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE).
 2. CHARACTERS TO BE POSITIONED ON HOUSING TO BE READ FROM WIRE END ONLY.
 3. VIOLET, BLACK, BROWN AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



6.73	.265	—	—
5.97	.235	—	—
3.18	.125	27.43	1.080
0.38	.015	26.67	1.050
0.25	.010	14.73	.580
0.13	.005	7.62	.300
MM	IN	MM	IN
CONVERSION TABLE			



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL	08FEB95	 TE Connectivity	
DIMENSIONS: mm		CHK R. SWING	08FEB95	NAME	
		AP'D D. SELF	08FEB95	PLUG, 4 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± .010 1. PLC ± .010 2. PLC ± 0.13 3. PLC ± .010 4. PLC ± .010 ANGLES ± .030° FINISH		PRODUCT SPEC		RESTRICTED TO	
MATERIAL NYLON, UL 94V-2		APPLICATION SPEC		SIZE	
—		WEIGHT —		CAGE CODE	
		CUSTOMER DRAWING		DRAWING NO.	
				A1 00779	
				C=480702	
				SCALE 4:1	
				SHEET 2 OF 2	
				REV. AP	