

3-Phase Switched PDU, 11 kW, 24 220/230V outlets (21 C13, 3 C19) IEC-309 380/400V Red 16A Input, 3m cord, 0U vertical mount

MODEL NUMBER: **PDU3XVSR10G16**



Description

Tripp Lite 3 phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption per-phase or per-receptacle. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper start-up of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps per-phase or per-receptacle can be displayed locally via visual meter or remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

Features

- 11kW 3 phase 380/400V input, 220/230V output Switched Power Distribution Unit / PDU with built-in web/network interface
- Attached IEC-309 Red 16A (3P+N+E) 380/400V 3 phase input; 3m line cord
- 0U / 178cm vertical form factor supports installation in 2 or 4 post equipment racks
- 24 switched 220/230V outlets (21 C13, 3 C19) in 3 breakered single-phase load banks
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage, per-outlet and per-phase load levels
- Digital display with scroll-buttons supports per-outlet or per-phase load levels, IP-address self-identification and 180 degree display rotation
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH

Highlights

- Switched 11kW 3 Phase 380/400V input, 220/230V output PDU; 178cm 0U vertical rackmount
- Reports voltage, frequency & load per-outlet or phase via ethernet interface
- Visual current meter; Toolless button-mount installation
- IEC-309 Red 16A (3P+N+E) 380/400V 3 phase input; 3m line cord
- 21 C13 & 3 C19 single phase switched 220/230V outlets with cord retention brackets
- Temperature, humidity and contact closure monitoring options

Applications

- Ideal for 3 phase network configurations in datacenters and heavily configured equipment racks

Package Includes

- Switched rackmount PDU with pre-installed mounting buttons
- Cord retention brackets
- Spare installation buttons (29 mm / 46 mm)
- Rack mounting brackets
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is not powered on
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)
- TAA Compliant Version Available - Order Tripp Lite PDU3XVSR10G1TAA

Specifications

General Info	
Product Group	PDUS
OVERVIEW	
PDU Type	Switched
OUTPUT	
Output Capacity Details	11.5kVA (415V), 11kVA (400V), 10.5kVA (380V); 16A maximum output per phase
Frequency Compatibility	50 Hz; 60 Hz
Output Nominal Voltage	Single phase 240V (415V), 230V (400V), 220V (380V)
Outlet Quantity / Type	24 total - 21 C13 (7 per phase), 3 C19 (1 per phase)
Outlet Type	IEC-C13, IEC-C19
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface
INPUT	
PDU Input Voltage	380; 400
Maximum Input Amps	16
PDU Plug Type	IEC-309 16A RED (3P+N+E)
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Phase	3-Phase
LEDS ALARMS & SWITCHES	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Switches	Pushbutton scroll switch enables local power consumption display of each phase or outlet separately, display rotate and display IP address functions
Front Panel LEDs	2 digit current meter display reports output amps per phase and IP address self identification
PHYSICAL	
Shipping Dimensions (hwd / in.)	75.4 x 6.6 x 9.3
Shipping Dimensions (hwd / cm)	191.5 x 16.8 x 23.6
Shipping Weight (lbs.)	20.45
Shipping Weight (kg)	9.3
Unit Dimensions (hwd / in.)	70 x 2.19 x 3.26
Unit Dimensions (hwd / cm)	177.8 x 5.6 x 8.3
Unit Weight (lbs.)	13.2
Unit Weight (kg)	6
Material of Construction	Steel
Style	Vertical rackmount
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
COMMUNICATIONS	
SNMP Compatibility	Yes, pre-installed SNMPWEBCARD provides remote monitoring via web, telnet, SSH and SNMP management systems
CERTIFICATIONS	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDU3XVSR10G1TAA
Certifications	Tested to CE (EN 60950-1), Class A (Emissions), RoHS (Hazardous Substances)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.