

Absolute Maximum Ratings (Ta = 25°C)


Item	Symbol	Rating	Unit	Measurement conditions
Input	LED forward current	I_F	50	mA
	Repetitive peak LED forward current	I_{FP}	1	A
	LED forward current reduction rate	$\Delta I_F/^\circ\text{C}$	-0.5	mA/°C
	LED reverse voltage	V_R	5	V
	Connection temperature	T_J	125	°C
Output	Load voltage (AC peak/DC)	V_{OFF}	400	V
	Continuous load current	I_O	120	mA
	ON current reduction rate	$\Delta I_{ON}/^\circ\text{C}$	-1.2	mA/°C
	Connection temperature	T_J	125	°C
Dielectric strength between input and output (See note 1.)		V_{I-O}	2,500	V_{rms}
Operating temperature		T_a	-40 to +85	°C
Storage temperature		T_{stg}	-55 to +125	°C
Soldering temperature (10 s)		---	260	°C

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
Input	LED forward voltage	V_F	1.0	1.15	1.3	V
	Reverse current	I_R	---	---	10	μA
	Capacity between terminals	C_T	---	30	---	pF
	Trigger LED forward current	I_{FT}	---	1	3	mA
Output	Maximum resistance with output ON	R_{ON}	---	18	35	Ω
	Current leakage when the relay is open	I_{LEAK}	---	0.0008	1.0	μA
	Capacity between terminals	C_{OFF}	---	40	---	pF
Capacity between I/O terminals		C_{I-O}	---	0.8	---	pF
Insulation resistance		R_{I-O}	1,000	---	---	M Ω
Turn-ON time		t_{ON}	---	0.4	1.0	ms
Turn-OFF time		t_{OFF}	---	0.09	1.0	ms

Note: 2. Turn-ON and Turn-OFF Times



Recommended Operating Conditions


Use the G3VM under the following conditions so that the Relay will operate properly.

Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	320	V
Operating LED forward current	I_F	5	7.5	25	mA
Continuous load current (AC peak/DC)	I_O	---	---	100	mA
Operating temperature	T_a	-20	---	65	°C

Engineering Data


LED forward current vs.
Ambient temperature

$I_F - T_a$




Continuous load current vs.
Ambient temperature

$I_O - T_a$




LED forward current vs.
LED forward voltage

$I_F - V_F$




Continuous load current vs.
On-state voltage

$I_O - V_{ON}$




On-state resistance vs.
Ambient temperature

$R_{ON} - T_a$




Trigger LED forward current vs.
Ambient temperature

$I_{FT} - T_a$




Turn ON, Turn OFF time vs.
LED forward current

$t_{ON}, t_{OFF} - I_F$




Turn ON, Turn OFF time vs.
Ambient temperature

$t_{ON}, t_{OFF} - T_a$



Current leakage vs.
Ambient temperature

$I_{LEAK} - T_a$



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X302-E-1

12/10

Specifications subject to change without notice

Printed in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

[G3VM-402F\(TR\)](#) [G3VM-402C](#) [G3VM-402F](#)