

NOTES:
1.MATERIALS AND FINISHES:
BODY - PHOSPHOR BRONZE, NICKEL PLATING
CONTACT - BeCu, GOLD PLATING
FERRULE & SHELL - BRASS, NICKEL PLATING
INSULATOR - PTFE

2.ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 4 GHz
C. VSWR(RETURN LOSS): 1.3 MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.

3.MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C

4.FERRULE TO BE CRIMPED WITH A .178 HEX DIE.
A. CONTACT TO BE CRIMPED WITH A .042 SQUARE DIE
OR A 8 PT CRIMPER AMPHENOL NUMBER 227-TI200


5.SHOWS CABLE ENTRY DIMENSIONS.

6.PACKAGING: BULK PACK PER TABLE.


THIRD ANGLE PROJ.

REVISIONS


REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	12-Sep-06	45950	SX
B	SEE SHEET 2	8/6/07	46681	TC
C	INSIDE SPRING WAS CHANGED\RD-DM09090201K NOTE 4:227-TI200 WAS CTL-TI200\RD-DM-110704011 STAMP WAS CHANGED\RD-DA110823011 DANBURY: 0.48 WAS 0.53;2.77 WAS 2.57 UPDATED DRAWING FORMAT	26-Aug-11	48649	SCOTT






AFTER ASSEMBLY DIMENSIONS



RECOMMENDED
CABLE STRIPPING DIMENSIONS



SCALE 1.500



STAMP: APH 31-80101-XXX WWYY

DATE CODE

PART NUMBER	QTY
31-80101-BIC	100
31-80101-B2C	200
31-80101-B5C	500
31-80101-B1M	1000

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

SEE NOTE

REFERENCE

EAR # 1674
GEN # 611X-4252

FINISH

DRAWN

I. XU

ENGINEER

G. ANTONINI

APPROVED

S. HSIEH

CAD FILE

I:\BNC\31-80101-XXX

DATE

11-Aug-11

DATE

03-Mar-05

DATE

11-Aug-11

TITLE

75 OHM BNC PLUG
FOR AT&T 734A CABLE
BULK PACK

SCALE: 5.0:1.0 SHEET 2 OF 2

DWG SIZE

B

REV

C

Amphenol RF

Danbury CT USA, Tainan, Taiwan, Shenzhen, China
www.amphenolrf.com

DRAWING NO. 31-80101-XXX

ITEM NO. 31-80101-XXX

PART NO. 31-80101-XXX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[31-80101-B1C](#)