


SC Chip type, Standard Series


- Chip type higher capacitance in larger case sizes
- Designed for surface mounting on high density PC board
- Applicable to automatic insertion machine using carrier tape
- Complied to the RoHS directive



Item	Characteristics														
Operating temperature range	-40 ~ +85℃														
Leakage current max.	WV ≤ 100 I = 0.01CV or 3μA whichever is greater (after 2 minutes) WV ≥ 160 I = 0.04CV + 100μA(after 1 minutes)														
Capacitance tolerance	±20% at 120Hz, 20℃														
Dissipation factor max. (at 120Hz, 20℃)	WV	4	6.3	10	16	25	35	50	63	100	160	200	250	400	450
	tanδ	0.40	0.35	0.24	0.20	0.16	0.15	0.12	0.12	0.12	0.20	0.20	0.20	0.25	0.25
Low temperature characteristics (Impedance ratio at 120Hz)	WV			4	6.3	10	16	25	35 ~ 100	160 ~ 250	400 ~ 450				
	Z-25℃/Z+20℃			6	5	4	3	2	2	3	6				
	Z-40℃/Z+20℃			12	10	8	6	4	3	6	10				
Load life (after application of the rated voltage for 2000 hours at 85℃)	Leakage current						Less than specified value								
	Capacitance change						Within ±20% of initial value (Small size : ±25%)								
	tanδ						Less than 200% of the specified value								
Shelf life (at 85℃)	After 1000 hours no load test, leakage current, capacitance and tanδ are same as load life value. The measurement shall be performed at 20℃ by the KS C IEC 60384 - 4														
Resistance to soldering heat	The following specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them at 250℃ for 10 seconds.														
	Leakage current						Less than specified value								
	Capacitance change						Within ±10% of initial value								
	tanδ						Less than specified value								

● DRAWING -Series code of SC is "V"

Unit : mm



SURFACE MOUNT ALUMINUM ELECTROLYTIC CAPACITORS

SC series

● DIMENSIONS & MAXIMUM PERMISSIBLE RIPPLE CURRENT

μF \ WV	4		6.3		10		16		25		35		50	
1.0													4×5.3	10
2.2											4×5.3	11	4×5.3	15
3.3									4×5.3	15	4×5.3	16	4×5.3	18
4.7							4×5.3	16	4×5.3	18	4×5.3	19	4×5.3	24
													5×5.3	25
10	4×5.3	16	4×5.3	19	4×5.3	21	4×5.3	21	4×5.3	24	4×5.3	27	5×5.3	41
									5×5.3	30	5×5.3	32	6.3×5.3	43
22	4×5.3	24	4×5.3	29	4×5.3	28	4×5.3	30	5×5.3	41	6.3×5.3	53	6.3×5.3	71
					5×5.3	36	5×5.3	41	6.3×5.3	53			6.3×5.8	73
33	4×5.3	29	4×5.3	30	4×5.3	34	5×5.3	43	5×5.3	50	6.3×5.3	65	6.3×7.7	94
			5×5.3	41	5×5.3	44	6.3×5.3	58	6.3×5.3	64	6.3×5.8	67	8×6.2	95
47	4×5.3	35	4×5.3	36	5×5.3	47	5×5.3	52	6.3×5.3	70	6.3×7.7	94	6.3×7.7	105
			5×5.3	48	6.3×5.3	62	6.3×5.3	69	6.3×5.8	72	8×6.2	105	8×10	140
100	5×5.3	54	5×5.3	60	6.3×5.3	80	6.3×5.3	88	8×6.2	145	6.3×7.7	132	8×10	181
	6.3×5.3	68	6.3×5.3	82	6.3×5.8	82	6.3×5.8	91			8×10	175	10×10	195
220	6.3×5.3	93	6.3×5.8	91	6.3×7.7	173	6.3×7.7	162	8×10	232	10×10	265	10×10	320
					8×6.2	175	8×10	215	10×10	250				
330			6.3×7.7	188	8×10	240	8×10	270	10×10	305	10×10	360	12.5×13.5	600
			8×6.2	190										
470			8×10	265	8×10	290	8×10	307	10×10	400	12.5×13.5	600		
							10×10	330						
1000			8×10	370	10×10	454	12.5×13.5	710	12.5×13.5	820				
			10×10	400										
1500			10×10	480	12.5×13.5	850	12.5×13.5	870						
2200			12.5×13.5	890	12.5×13.5	960								

↑ ↑
Ripple current (mA rms) at 85°C, 120Hz
Case size $\varnothing D \times L$ (mm)

μF \ WV	63		100		160		200		250		400		450	
2.2													10×10	85
3.3			6.3×5.8	29							10×10	90	10×10	100
			6.3×5.8	35										
4.7	6.3×5.8	31	8×6.2	40			10×10	100	10×10	100	12.5×13.5	115	12.5×13.5	115
10	6.3×5.8	46	8×10	77	10×10	100	12.5×13.5	150	12.5×13.5	150				
22	8×6.2	96	8×10	100	12.5×13.5	240	12.5×13.5	260						
33	8×10	117	10×10	130	12.5×13.5	260								
47	10×10	140	10×10	155										
68	10×10	160	12.5×13.5	350										
100	12.5×13.5	370	12.5×13.5	420										
220	12.5×13.5	550												

↑ ↑
Ripple current (mA rms) at 85°C, 120Hz
Case size $\varnothing D \times L$ (mm)

● FREQUENCY COEFFICIENT OF PERMISSIBLE RIPPLE CURRENT

Frequency	50Hz	120Hz	300Hz	1kHz	10kHz $\leq$
Coefficient	0.70	1.00	1.17	1.36	1.50