

LM2901, MC3302, LM139 Series —Quad Voltage Comparator

GENERAL DESCRIPTION

The LM 139 series consists of four independent precision voltage comparators with an offset voltage specification as low as 2.0mV max for each comparator which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage. These comparators also have a unique characteristic in that the input common mode voltage range includes ground, even though operated from a single power supply voltage.

The LM139 series was designed to directly interface with TTL and CMOS. When operated from both plus and minus power supplies, the LM 139 series will directly interface with MOS logic where their low power drain is a distinct advantage over standard comparators.


FEATURES

- Wide single supply voltage range 2.0Vdc to 36Vdc or dual supplies ± 1.0 Vdc to ± 18 Vdc
- Very low supply current drain (0.8mA) independent of supply voltage (1.0mW/comparator at 5.0Vdc)
- Low input biasing current 25nA
- Low input offset current ± 5 nA and offset voltage ± 3 mV
- Input common-mode voltage range includes ground
- Differential input voltage range equal to the power supply voltage
- Low output 250mV at 4mA saturation voltage
- Output voltage compatible with TTL, DTL, ECL, MOS and CMOS logic systems

APPLICATIONS

- A/D converters
- Wide range VCO
- MOS clock generator
- High voltage logic gate
- Multivibrators

CONNECTION DIAGRAM



MAXIMUM RATINGS

PARAMETER	RATING	UNIT
V _{CC} supply voltage	36 or ± 18	Vdc
Differential input voltage	36	Vdc
Input voltage	-0.3 to +36	Vdc
Power dissipation		
Molded DIP	570	mW
CERDIP	900	mW
Output short circuit to ground	Continuous	
Input current (V _{IN} < 0.3Vdc)	50	mA
Operating temperature range		
LM139/139A	-55 to +125	°C
LM339/339A	0 to +70	°C
LM2901/MC3302	-40 to +85	°C
Storage temperature range	-65 to +150	°C
Lead temperature (soldering 10sec)	300	°C

REFERENCE TABLE


TYPE NO.	STOCK NO.	OUTLINE DRWG. NO.
LM139F	55997A	1
LM139AF	55998X	1
LM339N	55999H	1
LM339AN	56000H	1
MC3302N	56001F	1
LM2901N	56002D	1

PLEASE QUOTE STOCK NO.
AND MANUFACTURERS PART NO. WHEN ORDERING

ITT GEMINI


Outline Drawings






PLEASE QUOTE STOCK NO.
AND MANUFACTURERS PART NO. WHEN ORDERING


ITT GEMINI




16



17




19




PLEASE QUOTE STOCK NO.
AND MANUFACTURERS PART NO. WHEN ORDERING

TTT GEMINI


20



21



22



23

