CRYSTEK MICROWAVE
A DIVISION OF CRYSTEK CORPORATION

Voltage Controlled Oscillator-VCO
CVCO55BE-3430-3480

PERFORMANCE SPECIFICATION	MIN	TYP	MAX	UNITS
Lower Frequency:			3430	MHz
Upper Frequency:	3480			MHz
Tuning Voltage:	0.5		4.5	VDC
Supply Voltage:	4.75	5.0	5.25	VDC
Output Power:	0	+2.5	+5.0	dBm
Supply Current:			22	mA
Harmonic Suppression (2nd Harmonic):		-30		dBc
Pushing:			5.0	MHz/V
Pulling, all Phases:			18.0	MHz pk-pk
Tuning Sensitivity:		48		MHz/V
Phase Noise @ 10kHz offset:		-97	-93	dBc/Hz
Phase Noise @ 100kHz offset:		-119	-115	dBc/Hz
Load Impedance:		50		Ω
Input Capacitance:			10	pF
Operating Temperature Range:	-40		+85	°C
Storage Temperature Range:	-45		+90	°C

RoHS Compliant

Phase Noise (1 Hz BW, Typical)



Tuning Curve (Typical)



CRYSTEK CORPORATION
12730 COMMONWEALTH DRIVE • FORT MYERS, FLORIDA 33913
PHONE: 239-561-3311 • 800-237-3061
FAX: 239-561-1025 • WWW.CRYSTEK.COM

Voltage Controlled Oscillator-VCO
CVCO55BE-3430-3480







Pad	Connection
2	Vt
10	RF-OUTPUT
14	Vcc
Others	GROUND

- Unless otherwise specified, Dimensions are in: IN / (mm)
- Pad Location Dimensions are in: Inches

TAPE AND REEL



Drawing not to scale

Product Control:			
Crystek Part Number:	CVCO55BE-3430-3480	Release Date:	12-March-08
Revision Level:	D	Responsible:	C. Vales

Specification is subject to change without notice

CRYSTEK CORPORATION
12730 Commonwealth Drive • Fort Myers, Florida 33913
Phone: 239-561-3311 • 800-237-3061
Fax: 239-561-1025 • www.crystek.com