

M61084FP

PREAMPLIFIER WITH PHOTODETECTOR FOR OPTICAL PICKUP

DESCRIPTION

The M61084FP is a semiconductor integrated circuit developed for DVD and CD-ROM (8 times speed) players. The IC is housed in a 12-pin clear molded plastic package and contains 8 preamplifiers with divided photodetectors.

FEATURES

- 8 amplifiers with divided photodetectors
- Using small package (5.0X4.0X1.5 mm)
- For differential push-pull technique and single beam phase difference technique
- High Band preamplifier circuit (DC-20MHz)
- For red reys laser diode (ex. $\lambda = 635 \text{ nm}$)

APPLICATION


DVD , CD-ROM etc.

RECOMMENDED OPERATING CONDITIONS

Supply voltage 4.5V to 5.5V


Rated supply voltage 5.0V

PIN CONFIGURATION



Outline 12C2E

BLOCK DIAGRAM



MITSUBISHI
ELECTRIC

(1 / 5)


M61084FP

PREAMPLIFIER WITH PHOTODETECTOR FOR OPTICAL PICKUP


ABSOLUTE MAXIMUM RATINGS ($T_a=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Rating	Unit
Vcc	Supply voltage	6.0	V
Pd	Power dissipation ($T_a \leq 25^{\circ}\text{C}$)	250	mW
Topr	Operating temperature	-20 to +70	$^{\circ}\text{C}$
Tstg	Storage temperature	-40 to +100	$^{\circ}\text{C}$

TEST CIRCUIT

Units Resistance : Ω

Capacitance : F

THERMAL DERATING
(MAXIMUM RATINGS)

*Please set the condenser connected to Vcc and Vc near the pin. (Within 10mm)

MITSUBISHI
ELECTRIC

(2 / 5)

M61084FP

PREAMPLIFIER WITH PHOTODETECTOR FOR OPTICAL PICKUP

ELECTRICAL CHARACTERISTICS (VCC=5.0V, Ta=25°C, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
I _{CC}	Circuit current	In the dark	3.5	5.0	6.5	mA
V _O	Output voltage	P _O =10μW λ=635nm Output A to D without offset voltage	210	270	330	mV
		P _O =10μW λ=635nm Output E to H without offset voltage	400	500	600	mV
V _{OFF}	Output offset voltage	In the dark Output A to H	-15	0	+15	mV
ΔV _{OFF}	Delta output offset voltage	In the dark (A+B) - (C+D)	-15	0	+15	mV
		In the dark (A+D) - (B+C)	-15	0	+15	
		In the dark E - F	-15	0	+15	
		In the dark G - H	-15	0	+15	
V _{OMAX}	Maximum Output voltage	Output A to H maximum voltage at V _{CC} =5.0 v	3.5	-	-	V
f _c	Frequency characteristic	P _O =10μW/cell λ=635nm 30%modulation 3 dB down Output A to D	15	20	-	MHz
		P _O =10μW/cell λ=635nm 30%modulation 3 dBdown Output E to H	1.0	1.5	-	
V _{NO}	Output noise voltage	Output A to D (at f=5MHz)	-	-80	-74	dBm
R	Optical sensitivity on SPD	λ=635nm Output A to H	-	0.3	-	A/W





MITSUBISHI<LINEAR ICS>

M61084FP

PREAMPLIFIER WITH PHOTODETECTOR FOR OPTICAL PICKUP

PD SIZE (TYPICAL)



Note) A public difference from the SPD center and the flame
..... $\pm 0.2\text{mm}$

A public difference from the center of the flame of molded package
..... $\pm 0.2\text{mm}$

A public difference from the center of SPD and the center of molded package
..... $\pm 0.4\text{mm}$

The rotation deviation of SPD toward the flame
..... ± 3 degree



MITSUBISHI
ELECTRIC

(4 / 5)