


**DIMENSIONS (mm)****ELECTRICAL DATA**

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Lamp rated wattage	(W) :	6.0	5.2	6.8
Lamp operating voltage (rms)	(V) :	42	36	48
Lamp current	(mA) :	160		
Preheat current	(mA) :			

OPERATING CONDITIONS:

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Ballast impedance - single lamp 50Hz	:	4/6/8W 700ohm 127V FS22 Starter		
Ballast impedance - twin series 50Hz	:	13W 1070ohm 220V FS22 Starter		
High Frequency Operation	:			
Cap Rim temperature	(°C) :			80
Lamp Ambient Temperature	(°C) :	25	-15	50
Operating Position	:	Any		

LAMP LIFE ¹

Average life (50% failure)	(h) :	10000
----------------------------	-------	-------

PHOTOMETRIC DATA:

			<u>Luminous Flux ²</u>	<u>CRI</u>	<u>Colour</u>	<u>ILCOS</u>	
	<u>colour</u>		<u>nominal value</u>	<u>(Class)</u>	<u>Temp.</u>	<u>Code</u>	
	<u>no.</u>		<u>(lm)</u>		<u>(K)</u>		
Warm White	WW	129	290	3	3100		
Cool White	CW	133	290	3	4200		
White	W	135	290	3	3500		
Daylight	D	154	240	3	6500		
		840	320	1b	4000		

ATTENTION:

The product must be used with suitable operating equipment and in accordance with the specified data. This product is in accordance with relevant IEC standards.

¹ Life test according to EN 60 081.

² Measured according to EN 60 081, at 50 Hz, lamp aged 100h.

Issued by : SHIPLEY
Date : 22.03.1989
Revision date : 28.02.2000

DATA SHEET

Number : 6102
Supersedes :
Page : 1 of 1

SYLVANIA reserves the right to change data and specifications without notice.
Data for guidance only.

SYLVANIA