

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

ALL INTERNATIONAL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN

LOC
A1

DIST
—

REVISIONS
ÄNDERUNGEN

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	C4	REVISION PER EG00-2081-00 (TEXT TO ENGLISH TRANSLATED)	06-SEP-00	R.S	G.F
	D1	966899-1 and 966899-2 OBSOLETE - PER PCN EG00-0641-04	03-JUN-04	STOLZ	G.F
	D2	REVISED PER ECR-09-018681	20AUG09	VKH	RRP

STRIP FORM ON MIDDLE REEL (CARDBOARD REEL, DIA. ABOUT 450mm)
BANDWARE AUF MITTELSPULE (PAPPSPULE, Ø CA. 450mm)

4

ORDER NO. BESTELL-NR.	CROSS SECTION QUERSCHNITT		STRIP LENGTH ABISOLIER-LÄNGE /mm	TYPE AUSFÜHRUNG	COLOUR FARBE	L ₁ /mm	L ₂ /mm	d ₁ /mm	s ₁ /mm	d ₂ /mm	COLOUR TYPE FARBREIHE	PACKING UNIT VERPACKUNGSEINHEIT PARTS/STÜCK REEL/SPULE	
	mm ²	AWG											
966 899-1	0.25/0.34	23/22	10	NORMAL	GREEN GRÜN	12 ±1.5	8 ±0.4	0.8 ^{+0.14}	0.15 ±0.05	2.0 ±0.2	1	10000	OBSOLETE
966 899-2	0.25/0.34	23/22	10	NORMAL	TORQUISE TÜRKIS	12 ±1.5	8 ±0.4	0.8 ^{+0.14}	0.15 ±0.05	2.0 ±0.2	2	10000	OBSOLETE
966 900-1	0.50	20	10	NORMAL	ORANGE	14 ±1.5	8 ±0.4	1.0 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	2	10000	
966 900-2	0.50	20	10	NORMAL	WHITE WEIß	14 ±1.5	8 ±0.4	1.0 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	DIN/1	10000	
966 901-1	0.75	18	10	NORMAL	LIGHT-BLUE HELLBLAU	14 ±1.5	8 ±0.4	1.2 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	1	10000	
966 901-2	0.75	18	10	NORMAL	WHITE WEIß	14 ±1.5	8 ±0.4	1.2 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	2	10000	
966 901-3	0.75	18	10	NORMAL	GREY GRAU	14 ±1.5	8 ±0.4	1.2 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	DIN	10000	
966 902-1	1.00	17	10	NORMAL	YELLOW GELB	14 ±1.5	8 ±0.4	1.4 ^{+0.14}	0.15 ±0.05	3.3 ±0.2	2	7500	
966 902-2	1.00	17	10	NORMAL	RED ROT	14 ±1.5	8 ±0.4	1.4 ^{+0.14}	0.15 ±0.05	3.3 ±0.2	DIN/1	7500	
966 903-1	1.50	16	10	NORMAL	RED ROT	14 ±1.5	8 ±0.4	1.7 ^{+0.25}	0.15 ±0.05	3.3 ±0.2	2	7500	OBSOLETE
966 903-2	1.50	16	10	NORMAL	BLACK SCHWARZ	14 ±1.5	8 ±0.4	1.7 ^{+0.25}	0.15 ±0.05	3.5 ±0.2	DIN/1	7500	
966 903-3	1.50	16	10	NORMAL	BLACK SCHWARZ	14 ±1.5	8 ±0.4	1.7 ^{+0.25}	0.15 ±0.05	3.5 ±0.2	DIN/1	7500	SUPERSEDED BY -2
966 904-1	2.50	14	10	NORMAL	GREY GRAU	14 ±1.5	8 ±0.4	2.2 ^{+0.25}	0.15 ±0.05	4.2 ±0.2	1	5000	
966 904-2	2.50	14	10	NORMAL	BLUE BLAU	14 ±1.5	8 ±0.4	2.2 ^{+0.25}	0.15 ±0.05	4.2 ±0.2	DIN/2	5000	

1

THE AWG CROSS-SECTION CAN SLIGHT DEVIATING OF THE DIN-STANDARD CROSS-SECTION VALUES

2

RECOMMENDED STRIP LENGTH

3

MAX. INSULATION-DIA. OF WIRE: d₂ MIN.— 0.1

4

COLOUR TYPE 1: COLOUR PER TELEMECANIQUE STANDARD
COLOUR TYPE 2: COLOUR PER WEIDMÜLLER STANDARD
DIN COLOUR TYPE: COLOUR PER DIN 46228 PART 4


5

TUBULAR END-SLEEVE WITH PLASTIC SLEEVE ACCORDING TO DIN 46228 PART 4

PLASTIC SLEEVE
KUNSTSTOFFHÜLSE

COPPER SLEEVE
KUPFERHÜLSE

3




NOMINAL SIZE
NENNGRÖßE
/mm

R
/mm


0.25/0.34	2.7
0.5 — 0.75	3.6
1 — 1.5	4.2
2.5	5.0

R ±0.4



THIS DRAWING IS A CONTROLLED DOCUMENT.
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.

DIMENSIONS:
MASSENGHEITEN:
mm



MATERIAL
PP/E-Cu

TOLERANCES UNLESS OTHERWISE SPECIFIED:
n. ISO 8015
n. ISO 2768 — mH —E
n. DIN 16901 — 140

TOLERANCES UNLESS OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES /WINKEL ± —

FINISH/OBERFLÄCHE/FARBE
Sn (SEE TABLE)

DWN
E.WERNER
29-APR-96

CHK
R.SCHMIDT
29-APR-96

APVD
G.FELDMER
12-SEP-00

PRODUCT SPEC
PRODUKTSPEZ.
—

APPLICATION SPEC
VERARBEITUNGSSPEZ.
—

WEIGHT
GEWICHT
—

Tyco
Electronics

Tyco Electronics AMP GmbH
D — 64625 Bensheim

TUBULAR END-SLEEVE WITH PLASTIC SLEEVE, STRIP FORM, MIDDLE REEL
ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE, BANDWARE, MITTELSPULE

5

SIZE
A3

CAGE CODE
00779

DRAWING NO
ZEICHNUNGS-NR.
C-966899

RESTRICTED TO
NUR FÜR
—

CUSTOMER DRAWING/KUNDENZEICHNUNG

SCALE
MASSSTAB
—

SHEET
BLATT
1 OF
VON 1

REV
D2

1470-19 (1/08)