

14.2mm (0.56") THREE DIGIT NUMERIC DISPLAY




SUNLED

Email : sales@us.sunled.com

Web Site : www.sunled.com

XDUY14C3-B



Notes:


1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25 (0.01)$ unless otherwise noted.

Absolute maximum ratings (T _A =25°C)		UY (GaAsP/GaP)	Unit
Reverse voltage	V _R	5	V
Forward current	I _F	30	mA
Forward current (peak) 1/10Duty cycle 0.1ms pulse width	i _{FS}	140	mA
Power dissipation	P _T	105	mW
Operating temperature	T _A	-40 ~ +85	°C
Storage temperature	T _{stg}		
Lead solder temperature [2mm below package base]	260°C For 5 Seconds		

Operating Characteristics (T _A =25°C)		UY (GaAsP/GaP)	Unit
Forward voltage (typ.) (I _F =10mA)	V _F	1.95	V
Forward voltage (max.) (I _F =10mA)	V _F	2.5	V
Reverse current (V _R =5V)	I _R	10	uA
Wavelength at peak emission (I _F =10mA)	λ_{peak}	590	nm
Wavelength at Dominate emission (I _F =10mA)	λ_D	588	nm
Spectral Line half-width (I _F =10mA)	$\Delta\lambda$	35	nm
Capacitance (V _r =0V, f=1MHz)	C	20	pF

Part Number	Emitting Color	Emitting Material	Luminous Intensity (I _F =10mA) ucd min. typ.	Wave- length nm λ_P	Description
XDUY14C3-B	Yellow	GaAsP/GaP	1900 4690	590	Common Cathode,Rt.Hand Decimal.

XDUY14C3-B



◆UY

