


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680						
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
1281	A	RELEASED	HYO	11/27/01	JWM	11/27/01	DJC	11/27/01	



SPC TYPE NO.	WATTS (W)	MOD MAX.	MOL MAX.	BASE	APPROX. LUMENS	APPROX. COLOR TEMPERATURE (K)	AVG. LIFE (HOURS)	COLOR RENDERING INDEX (CRI)	LIGHT
F4T5/CW	4	16	152	G5	135	4150	6000	62	COOL WHITE
F4T5/D	4	16	152	G5	115	6250	6000	75	DAYLIGHT
F6T5/CW	6	16	229	G5	295	4150	7500	62	COOL WHITE
F6T5/D	6	16	229	G5	230	6250	7500	75	DAYLIGHT
F8T5/CW	8	16	305	G5	400	4150	7500	62	COOL WHITE
F8T5/D	8	16	305	G5	330	6250	7500	75	DAYLIGHT
F13T5/CW	13	16	533	G5	850	4150	7500	62	COOL WHITE
F15T8/CW	15	26	457	G13	825	4150	7500	62	COOL WHITE
F15T8/D	15	26	457	G13	700	6250	7500	75	DAYLIGHT

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
HISHAM ODISH	11/27/01
CHECKED BY:	DATE:
JEFF MCVICKER	11/27/01
APPROVED BY:	DATE:
DANIEL CAREY	11/27/01

DRAWING TITLE: PREHEAT FLUORESCENT LAMPS			
SIZE A	DWG. NO. TA-456	ELECTRONIC FILE TA-456.DWG	REV A
SCALE: NTS	U.O.M.: MILLIMETERS	SHEET: 1 OF 1	