



THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

MECHANICAL DIMENSIONS:



REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Specifications	01-24-08	DP

ELECTRICAL SCHEMATIC:



NOTES:

ELECTRICAL CHARACTERISTICS:

RATED CURRENT:

UL/CSA @ 250VAC.....10/6 AMP
SEMKO @250VAC.....10 AMP

DPST POWER SWITCH:

UL / CSA / SEMKO @ 250 VAC.....6 AMP

DOUBLE 5x20mm OR 6.3x32mm FUSEHOLDER

SOLDER TAB TERMINALS

FLAMMABILITY CLASS UL94V-0

PLASTIC CASE

SCREW MOUNT TYPE

= VOLTAGE SELECTOR 110-120 VAC
220-240 VAC

APPROVALS: UL, CSA, SEMKO

RoHS COMPLIANT

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION		
		Part Number: 763-00/001	RoHS Compliant	
0-1	0.15	Description: MULTI-FUNCTION MODULE		
1-6	0.20			
6-18	0.30		UNIT: mm	REV.C
18-50	0.50			
50-120	0.70			
120-250	0.90			
250-500	1.20			
		Drawn / Date	Checked / Date	Approved / Date
		B.ZHANG 06-29-05	06-29-05	JJH / 06-29-05