

10987654321

F

E

D

C

B

A

FORMAT: Eng-lega-master-lb-prod-B
REVISION: E1
DATE: 2021/05/01

DOCUMENT STATUS P1 RELEASE DATE 2023/01/27 16:26:29

9

8

7

6



5

4





3

2

1



- SPECIFICATIONS:
- MATERIAL:
 - (A). BODY: PA66 (UL94-V0)
 - (B). PIN MATERIAL: BRASS
 - PIN FINISH:
 - TIN - 3 µm (118 µin) MIN MATTE TIN
 - OVER 2 µm (79 µin) MIN NICKEL
 - GOLD - 0.76 µm (30 µin) MIN GOLD IN CONTACT AREA, 3 µm (118 µin) MIN MATTE TIN IN SOLDER AREA.
 - 2 µm (79 µin) MIN NICKEL UNDERPLATE
 - ELECTRICAL RATING: 300V, 18A (PER UL)
 - OPERATING TEMPERATURE: -40°C to +115°C.
 - INSULATION RESISTANCE: DC 500V, 500MΩ.
 - DIELECTRIC WITHSTAND: AC 2500V FOR 1 MINUTE.
 - BREAKDOWN VOLTAGE : 4000V.



TOLERANCES			
MM	TOL	INCH	TOL
0-6	±0.25	0-.24	±.010
>6-30	±0.40	.24-1.18	±.016
>30-120	±0.50	1.18-4.76	±.020
>120	±0.80	>4.76	±.031

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: MODIFIED SPECIFICATIONS					molex 5.08MM, EURO HEADER, VERTICAL							
	MM/INCH		4:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
= 0					EC NO: 735568 DRWN: ABENJAMINLW 2023/01/06 CHK'D: DACHAMMER 2023/01/17 APPR: JFMURPHY 2023/01/27					PRODUCT CUSTOMER DRAWING							
= 0					INITIAL REVISION: DRWN: LROTHAUS 2006/01/09 APPR: JPAWLICK 2006/01/10					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION			
				SD-39531-002						PSD	001	A3					
DIVISIONAL SYMBOLS	4 PLACES		±	---	±	---	THIRD ANGLE PROJECTION					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
	3 PLACES		±	---	±	SEE CHART						SEE SHEET-2		GENERAL MARKET		1 OF 2	
	2 PLACES		±	SEE CHART	±	SEE CHART											
	1 PLACE		±	SEE CHART	±	---											
0 PLACES		±	---	±	---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											
ANGULAR TOL		±	---														

