

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

REV	DATE	BY	APP'D
03	16DEC08	PER	MS

LOT NO.

2

1992.

APRIL

MONTH

D

YEAR

1992.

APRIL

6.20±0.51

[.244±.020]

1.00

[.039]

1.76

[.069]

DIM.

W/TAPE

1.27

[.050]

TYP

0.35

[.014]

TYP

1.20

[.047]

1.58

[.062]

0.56

[.022]

1.71

[.067]

MAX.

W/O TAPE

1.27

[.050]

TYP

0.76

[.030]

TYP

6.34

[.250]

MAX

7.60

[.299]

REF

8.89

[.350]

MIN

1.27

[.050]

TYP

3.81

[.150]

0.76

[.030]

TYP

1.27

[.050]

REF

TYP

6.34

[.250]

MAX

7.60

[.299]

REF

8.89

[.350]

MIN

RECOMMENDED PAD LAYOUT

TOLERANCE ±.002 UNLESS OTHERWISE NOTED

6.19±0.30

[.244±.012]

0.15

[.006]

0.79

[.031]

STROKE

0.10

[.004]

0.57

[.022]

8X

1.07

[.042]

8X

8.12±0.50

[.320±.020]

1

SUPPLIED WITH TAPE SEAL STANDARD

2

SWITCH IS TO HAVE OVERALL HEIGHT AS SHOWN

3

ITEM TO BE PACKAGED IN TUBES, QUANTITY PER TUBE=70

4

SWITCH SHALL BE MARKED AS SHOWN

5

ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

6

TAPE AND REEL PACKAGING PER EIA-481

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWNS

CHK

APVD

01MAR05

M.S.SARVER

01MAR05

M.S.SARVER

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.25[.010]

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL

-

FINISH

-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SCALE 10:1

SHEET 1 OF 1

REV 03

NAME

LOW PROFILE DIP SWITCH

MGDH04

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

100779

1825140

4805 (1/08)