

# DATA SHEET

For a complete data sheet, please also download:

- The IC06 74HC/HCT/HCU/HCMOS Logic Family Specifications
- The IC06 74HC/HCT/HCU/HCMOS Logic Package Information
- The IC06 74HC/HCT/HCU/HCMOS Logic Package Outlines

## **74HC/HCT147** 10-to-4 line priority encoder

Product specification  
File under Integrated Circuits, IC06

December 1990

## 10-to-4 line priority encoder

## 74HC/HCT147

## FEATURES

- Encodes 10-line decimal to 4-line BCD
- Useful for 10-position switch encoding
- Used in code converters and generators
- Output capability: standard
- $I_{CC}$  category: MSI

## GENERAL DESCRIPTION

The 74HC/HCT147 are high-speed Si-gate CMOS devices and are pin compatible with low power Schottky TTL (LSTTL). They are specified in compliance with JEDEC standard no. 7A.

The 74HC/HCT147 9-input priority encoders accept data from nine active LOW inputs ( $\bar{A}_0$  to  $\bar{A}_8$ ) and provide a binary representation on the four active LOW outputs ( $\bar{Y}_0$  to  $\bar{Y}_3$ ). A priority is assigned to each input so that when two or more inputs are simultaneously active, the input with the highest priority is represented on the output, with input line  $\bar{A}_8$  having the highest priority.

The devices provide the 10-line to 4-line priority encoding function by use of the implied decimal "zero". The "zero" is encoded when all nine data inputs are HIGH, forcing all four outputs HIGH.

## QUICK REFERENCE DATA

GND = 0 V;  $T_{amb} = 25\text{ }^{\circ}\text{C}$ ;  $t_r = t_f = 6\text{ ns}$

| SYMBOL            | PARAMETER                                    | CONDITIONS                                   | TYPICAL |     | UNIT |
|-------------------|----------------------------------------------|----------------------------------------------|---------|-----|------|
|                   |                                              |                                              | HC      | HCT |      |
| $t_{PHL}/t_{PLH}$ | propagation delay $\bar{A}_n$ to $\bar{Y}_n$ | $C_L = 15\text{ pF}$ ; $V_{CC} = 5\text{ V}$ | 15      | 17  | ns   |
| $C_I$             | input capacitance                            |                                              | 3.5     | 3.5 | pF   |
| $C_{PD}$          | power dissipation capacitance per package    | notes 1 and 2                                | 30      | 33  | pF   |

## Notes

1.  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu\text{W}$ ):

$$P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum (C_L \times V_{CC}^2 \times f_o) \text{ where:}$$

$f_i$  = input frequency in MHz

$f_o$  = output frequency in MHz

$\sum (C_L \times V_{CC}^2 \times f_o)$  = sum of outputs

$C_L$  = output load capacitance in pF

$V_{CC}$  = supply voltage in V

2. For HC the condition is  $V_I = \text{GND to } V_{CC}$   
For HCT the condition is  $V_I = \text{GND to } V_{CC} - 1.5\text{ V}$

## ORDERING INFORMATION




See "74HC/HCT/HCU/HCMOS Logic Package Information".

10-to-4 line priority encoder

74HC/HCT147

PIN DESCRIPTION

| PIN NO.                       | SYMBOL                               | NAME AND FUNCTION                |
|-------------------------------|--------------------------------------|----------------------------------|
| 8                             | GND                                  | ground (0 V)                     |
| 9, 7, 6, 14                   | $\overline{Y}_0$ to $\overline{Y}_3$ | BCD address outputs (active LOW) |
| 11, 12, 13, 1, 2, 3, 4, 5, 10 | $\overline{A}_0$ to $\overline{A}_8$ | decimal data inputs (active LOW) |
| 15                            | n.c.                                 | not connected                    |
| 16                            | V <sub>CC</sub>                      | positive supply voltage          |



10-to-4 line priority encoder

74HC/HCT147




Fig.4 Functional diagram.

FUNCTION TABLE

| INPUTS         |                |                |                |                |                |                |                |                | OUTPUTS        |                |                |                |
|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| A <sub>0</sub> | A <sub>1</sub> | A <sub>2</sub> | A <sub>3</sub> | A <sub>4</sub> | A <sub>5</sub> | A <sub>6</sub> | A <sub>7</sub> | A <sub>8</sub> | Y <sub>3</sub> | Y <sub>2</sub> | Y <sub>1</sub> | Y <sub>0</sub> |
| H              | H              | H              | H              | H              | H              | H              | H              | H              | H              | H              | H              | H              |
| X              | X              | X              | X              | X              | X              | X              | X              | L              | L              | H              | H              | L              |
| X              | X              | X              | X              | X              | X              | X              | L              | H              | L              | H              | H              | H              |
| X              | X              | X              | X              | X              | X              | L              | H              | H              | H              | L              | L              | L              |
| X              | X              | X              | X              | X              | L              | H              | H              | H              | H              | L              | L              | H              |
| X              | X              | X              | X              | L              | H              | H              | H              | H              | H              | L              | H              | L              |
| X              | X              | X              | L              | H              | H              | H              | H              | H              | H              | L              | H              | H              |
| X              | X              | L              | H              | H              | H              | H              | H              | H              | H              | H              | L              | L              |
| X              | L              | H              | H              | H              | H              | H              | H              | H              | H              | H              | L              | H              |
| L              | H              | H              | H              | H              | H              | H              | H              | H              | H              | H              | H              | L              |

Notes

1.
- H = HIGH voltage level
- L = LOW voltage level
- X = don't care

10-to-4 line priority encoder

74HC/HCT147




Fig.5 Logic diagram.

## 10-to-4 line priority encoder

## 74HC/HCT147

**DC CHARACTERISTICS FOR 74HC**

For the DC characteristics see *"74HC/HCT/HCU/HCMOS Logic Family Specifications"*.

Output capability: standard

I<sub>CC</sub> category: MSI

**AC CHARACTERISTICS FOR 74HC**

GND = 0 V; t<sub>r</sub> = t<sub>f</sub> = 6 ns; C<sub>L</sub> = 50 pF

| SYMBOL                              | PARAMETER                                             | T <sub>amb</sub> (°C) |                |                 |            |                 |             |                 | UNIT | TEST CONDITIONS        |           |
|-------------------------------------|-------------------------------------------------------|-----------------------|----------------|-----------------|------------|-----------------|-------------|-----------------|------|------------------------|-----------|
|                                     |                                                       | 74HC                  |                |                 |            |                 |             |                 |      | V <sub>CC</sub><br>(V) | WAVEFORMS |
|                                     |                                                       | +25                   |                |                 | −40 to +85 |                 | −40 to +125 |                 |      |                        |           |
|                                     |                                                       | min.                  | typ.           | max.            | min.       | max.            | min.        | max.            |      |                        |           |
| t <sub>PHL</sub> / t <sub>PLH</sub> | propagation delay<br>A <sub>n</sub> to Y <sub>n</sub> |                       | 50<br>18<br>14 | 160<br>32<br>27 |            | 200<br>40<br>34 |             | 240<br>48<br>41 | ns   | 2.0<br>4.5<br>6.0      | Fig.6     |
| t <sub>THL</sub> / t <sub>TLH</sub> | output transition<br>time                             |                       | 19<br>7<br>6   | 75<br>15<br>6   |            | 95<br>19<br>16  |             | 110<br>22<br>19 | ns   | 2.0<br>4.5<br>6.0      | Fig.6     |

10-to-4 line priority encoder

74HC/HCT147

DC CHARACTERISTICS FOR 74HCT

For the DC characteristics see *“74HC/HCT/HCU/HCMOS Logic Family Specifications”*.

Output capability: standard  
I<sub>CC</sub> category: MSI

Note to HCT types

The value of additional quiescent supply current (ΔI<sub>CC</sub>) for a unit load of 1 is given in the family specifications. To determine ΔI<sub>CC</sub> per input, multiply this value by the unit load coefficient shown in the table below.


| INPUT                                                                            | UNIT LOAD COEFFICIENT |
|----------------------------------------------------------------------------------|-----------------------|
| $\overline{A}_3, \overline{A}_4, \overline{A}_7, \overline{A}_8$                 | 1.50                  |
| $\overline{A}_5, \overline{A}_6, \overline{A}_0, \overline{A}_1, \overline{A}_2$ | 1.10                  |

AC CHARACTERISTICS FOR 74HCT

GND = 0 V; t<sub>r</sub> = t<sub>f</sub> = 6 ns; C<sub>L</sub> = 50 pF

| SYMBOL                              | PARAMETER                                                 | T <sub>amb</sub> (°C) |      |      |            |      |             |      | UNIT | TEST CONDITIONS        |           |
|-------------------------------------|-----------------------------------------------------------|-----------------------|------|------|------------|------|-------------|------|------|------------------------|-----------|
|                                     |                                                           | 74HCT                 |      |      |            |      |             |      |      | V <sub>CC</sub><br>(V) | WAVEFORMS |
|                                     |                                                           | +25                   |      |      | −40 to +85 |      | −40 to +125 |      |      |                        |           |
|                                     |                                                           | min.                  | typ. | max. | min.       | max. | min.        | max. |      |                        |           |
| t <sub>PHL</sub> / t <sub>PLH</sub> | propagation delay<br>$\overline{A}_n$ to $\overline{Y}_n$ |                       | 20   | 35   |            | 44   |             | 53   | ns   | 4.5                    | Fig.6     |
| t <sub>THL</sub> / t <sub>TLH</sub> | output transition<br>time                                 |                       | 7    | 15   |            | 19   |             | 22   | ns   | 4.5                    | Fig.6     |

AC WAVEFORMS



PACKAGE OUTLINES

See *“74HC/HCT/HCU/HCMOS Logic Package Outlines”*.