

REV. Status

ISSUE 1
4/28/92 YNISSUE 2
REFORMATTED
TEMECULA
WAS CARSON
9/13/95 DS

1. Electrical specifications

- 1.1 Input voltage: AC 120V $\pm 10\%$ 60 Hz ± 0.5 Hz
1.2 Output voltage and current: AC 20V at 1000mA

Vin	1000mA Load	100mA Load
108	16.6 VAC MIN	—
120	18.7–20.9 VAC	23.3 VAC MAX
132	—	25.8 VAC MAX

NOTE: Specification applies after 10 minutes warm-up with 1000mA load and at any operating temperature

- 1.3 Operating temperature: 0 ° C to +40 ° C
1.4 Storage temperature: -20 ° C to +85 ° C
1.5 Operating and Storage Humidity: 0 to 95% without condensation
1.6 Withstand voltage: AC 1500Vrms 1 minute @ input to output
1.7 Input earth prong is connected to output "G" terminal


2. Typical performance data test condition: Ta = +25° C, measured after 10 minute warm-up with input at 120V 60Hz

3. Safety agencies

UL File No. E82180
CSA File No. LR38236



4. Nameplate: See drawing P-N1-11159 for detail

UL AND CSA RATING



5. Mechanical Specifications;

All dimensions shown are nominal unless otherwise specified



PREPARED BY:

K. Georgeson

ENGINEER:

D. Suzuki

QUALITY CONTROL:

V. Casey

APPROVED:

V. Casey

DWG CONTROL NO.
P-A7-10677
ACAD\PS\A7106771.DWG

REV
A

UL/CSA AC 20V 1000mA
POWER SUPPLY

TAMURA CORPORATION OF AMERICA

43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

830A0065-03

MODEL SPECIFICATION

DIM: mm(In) SCL: NONE SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.