


REV	DOCUMENT	CHANGED BY	CHECK
3	0038113	PRS 12JUN08	BLR



RELEASE NO.	PR - 19882
REPLACES	X94370 - SM

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± - ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± - ANGLES ± - THIRD ANGLE PROJECTION 				DRAWN	VK	30 OCT 07		Honeywell					
OPERATING FORCE - - - - 9 OZ MAX		CONTACT ARRANGEMENT S P D T								CHECK	RJ	30 OCT 07							
RELEASE FORCE - - - - 2 OZ MIN		APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4 		BRAND L190			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC							
DIFFERENTIAL TRAVEL - - - .020 MAX				UL, CSA	11A 1/4 HP 125 250 VAC 5A 30 VDC  														
OVERTRAVEL - - - - .013 MIN									INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME			REV		
											RASTER			B	I	141SM28-H58			3
									SCALE -			WEIGHT .006 LB MAX		SHEET 1 OF 1					