


Preferred Connector Products

Technology to Inspire Innovation

JAE



JAE Electronics, Inc.

For Additional Information Visit www.jae-connector.com

Japan Aviation Electronics Industry, Ltd. (JAE) is an international manufacturer and supplier of electronic components and systems. For over four decades, JAE has provided the electronics industry with solutions to complex design requirements. Since its founding, the Company has strived to contribute to society through market-driven, technology-based global business operations under the philosophy: "Technology to Inspire Innovation."

With worldwide and world-class manufacturing certified to ISO 9001 and QS 9000, JAE has made the commitment to meet the global requirements of our customer. In addition to a network of state of the art manufacturing facilities, JAE has technical service offices located around the world, staffed with experts in connector design and application.

This catalog contains a select overview of JAE Connector Products. For in-depth information on our complete product line, and information on new developments, visit JAE's online catalog at www.jae-connector.com.

Innovative design, quality oriented manufacturing, commitment to our customers and sensitivity to the environment assures JAE's leadership position in the 21st century.

Table of Contents

Product Series	Contact Spacing	Pages
SOCKETS/MEMORY PRODUCTS		
PCMCIA		
JC22.....	1.27mm (.050")	5
COMPACT FLASH		
JC26C2.....	1.27mm (.050")	6 - 7
JC26E.....	1.27mm (.050")	8
JC26F.....	1.27mm (.050")	9
PCI EXPRESS MINI CARD		
MM60.....	0.8mm (.031")	10
EXPRESSCARD		
PX10/11	1.0mm (.039")	11 - 12
PX20/22	1.0mm (.039") / 0.635mm (.025").....	13 - 14
SMART/SIM CARD		
SF2.....	2.54mm (.100")	15
SF3.....	2.54mm (.100")	16
SF6.....	2.54mm (.100")	17
SF7.....	2.54mm (.100")	18
SF7 (Slim).....	2.54mm (.100")	19
SF9.....	2.54mm (.100")	20
SECURE DIGITAL CARD		
SG5.....	2.50mm (.098")	21
MINI SECURE DIGITAL CARD (SD)		
ST4.....	1.1mm (.043")	22
SC1.....	2.50mm (.098")	23
MICRO SD/TRANSFLASH™		
ST1.....	1.1mm (.043")	24
ST2.....	1.1mm (.043")	25

BOARD-TO-BOARD CONNECTOR PRODUCTS

BOARD-TO-BOARD		
AA03.....	0.40mm (.020")	26
WA6.....	0.40mm (.020")	27
WH1.....	0.40mm (.020")	28
AA01A	0.50mm (.020")	29
IL-312.....	0.50mm (.020")	30
WR.....	0.50mm (.020")	31 - 32
WB3.....	0.50mm (.020")	33
IL-WX	0.80mm (.031")	34
KX14/15	0.80mm (.031")	35 - 36
PM1	0.80mm (.031")	37
WM1.....	1.00mm (.039")	38
WM2.....	1.00mm (.039")	39
TX24/TX25.....	1.27mm (.050")	40

Table of Contents

Product Series	Contact Spacing	Pages
BOARD-TO-BOARD CONNECTOR PRODUCTS		
WIRE-TO-BOARD		
PCB-TO-FPC/FFC		
FB3.....	0.30mm (.012")	41
FB5.....	0.30mm (.012")	42
FB6.....	0.30mm (.012")	43
FF02.....	0.30mm (.012")	44
FF02S.....	0.30mm (.012")	45
FB8.....	0.30mm (.012")	46
FA5.....	0.50mm (.020")	47
FF03.....	0.50mm (.020")	48
IL-FPR.....	0.50mm (.020")	49
PCB-TO-CABLE/FPC		
FI-J.....	0.40mm (.016")	50 - 51
FI-R.....	0.50mm (.020")	52 - 53
FI-X.....	1.00mm (.039")	54 - 55
FI.....	1.25mm (.049")	56 - 58
PCB-TO-CABLE		
DX2/3.....	0.80mm (.031")	59
FI-E.....	1.00mm (.039")	60 - 61
CN10.....		62 - 63
CV10.....		64
IL-Z.....	1.25mm (.049")	65 - 66
IL-S.....	2.00mm (.079")	67 - 68
LY.....	2.00mm (.079")	69
KD10/20.....	2.00mm (.079")	70
IL-G.....	2.50mm (.098")	71
INPUT/OUTPUT CONNECTOR PRODUCTS		
PCB-TO-CABLE		
DD1.....	0.50mm (.020")	72 - 73
DD2.....	0.50mm (.020")	74 - 75
DG1.....	0.50mm (.020")	76
RA1.....	0.50mm (.020")	77
RC1.....	0.50mm (.020")	78
DA1.....	0.60mm (.024")	79
DE1.....	1.27mm (.050")	80
TX20A.....	1.27mm (.050")	81
DV2.....	1.905mm (.075")	82 - 84
CIRCULAR		
JN1.....		85 - 86
JN2.....		87 - 88
JB5.....		89

Table of Contents

Product Series

Contact Spacing

Pages

INPUT/OUTPUT CONNECTOR PRODUCTS

CIRCULAR

JL04V	90 - 91
JL05	92 - 93
JB1	94 - 95
SRCN	96 - 97
N/MS	98 - 99

FIBER OPTIC PRODUCTS

FO-FC	100
FO-EX	101

AUTOMOTIVE CONNECTOR PRODUCTS

PCB-TO-CABLE

MX34	1.1mm (.043")	102
MX7	2.30mm (.091")	103
IL-AG7	2.50mm (.098")	104
MX17	2.50mm (.098")	105 - 106
MX23A	2.50mm (.098")	107 - 108
MX10	2.50mm (.098")	109
MX5	3.00mm (.118")	110

PCB-TO-CABLE/CABLE-TO-CABLE

IL-AG5	2.50mm (.098")	111
IL-AG6	2.50mm (.098")	112
MX9	3.50mm (.138")	113
MX25	6.7mm (2.64")	114
MX36	2.50mm (.098")	115

CABLE-TO-CABLE

IL-AG9	2.50mm (.098")	116 - 118
MX19	2.50mm (.098")	119

- All JAE connector products shown in this catalog are lead free.
- We reserve the right to modify designs in order to improve quality, keep pace with technological advancements or meet particular requirements in production.
- Products shown in this catalog are made for the applications specified. However, if the above-mentioned products are to be used in aerospace devices, marine cable-connection devices, atomic power control systems, medical equipment for life-support systems, or any other specific application requiring extremely high reliability, please contact JAE for further information. Recommended Applications: Computers, Office Machines, Measuring Devices, Telecommunications Devices (Terminals, Mobile Devices) AV Devices, Household Applications, FA Devices, etc.
- Refer to end of catalog for alphabetical index of products.

Waterproof, Wire Soldering Type, Circular Connectors



- Certified by European safety standards and UL standards

Certification Organization	Standards
TÜV	DIN VDE 0627
UL	UI-498(E67741)




/ Rheinland



- First-to-make, last-to-break grounding contacts incorporated that connect with metallic shell to create protective earth circuit

Connector Profile (Ref.)



- IP67 class waterproof and dust-proof structure when mated
- Right angle, straight and straight without endbell (for use with conduit) plug types available
- Various contact arrangements
- Intermatable with MS connectors
(Please consult JAE for details.)

.....

JL04V Series are highly reliable circular connectors (wire soldering type) approved by TÜV as connectors satisfying European safety standards and by United States UL standards. They feature IP67 class water and dust proof (in the mated condition) structure, and a protective earth circuit with first-to-make, last-to-break grounding contacts. They are ideal for use in machine tools, servomotors, robots, and other industrial machines.

Number of Contacts	3, 4, 6, 7, 8, 9, 22 (See Note 1)						
Current Rating (Per contact)	Contact Size	Current Rating					
	#4	80 Amp max. per contact					
	#8	46 Amp max. per contact					
	#12	23 Amp max. per contact					
	#16	13 Amp max. per contact					
Dielectric Withstanding Voltage	2000 VAC r.m.s. (for one minute) with the rated current of 500 VAC: 3000 VAC r.m.s (for one minute)						
Insulation Resistance	1000 megohms min. (5,000 megohms min. for 28-11)						
Contact Resistance (Steady Level initial)	Contact Size	Applicable Wire AWG No.	Test Current Amps.	Contact Resistance milliohms max. (Initial)			
	#4	#4	80	1			
		#6	60	1			
		#8	46	1			
	#8	#10	46	2			
		#12	32	2			
	#12	#12	23	2			
		#14	17	3			
		#16	13	4			
	#16	#16	13	4			
		#18	10	7			
		#20	7.5	8			
		#22	5	15			
		#24	3	15			
Operating Temperature	-55°C to +125°C						
Applicable Wire Size and Cross Section	#4 2.2mm ² max. #8 5.5mm ² max. #12 3.5mm ² max. #16 1.25mm ² max. (0.5mm ² max. for 2E10SL-3P)						
Waterproof (mated condition)	IP67 Class						
Air Tightness (Receptacle)	2.9 x 10 ⁴ Pa (0.3 kg/cm ²), one minute						
Durability	500 Cycles						

Description	Materials/Finishes
Shell	Aluminum Alloy/Zinc plating (black)
Insulator	Synthetic Resin/Black (see Note)
Contact	Copper Alloy/Silver plating
Gasket	Synthetic Rubber
Retaining Ring	Copper Alloy/Zinc plating (OD chromate)
Endbell Fixing Screw	Steel/Zinc plating
Ground Pin/Screw (Screw: 24-10 (G) only)	Copper Alloy/Nickel plating

Note: Front part of receptacle is silicone rubber.
Synthetic resin for contact arrangement 28-11 only.

JL04V SERIES CONNECTORS

Waterproof, Wire Soldering Type, Circular Connectors

ORDERING INFORMATION

(Receptacle)	JL04V	-	2	*	**	-	**	*	E	*	-	B	-	R
(Plug)	JL04V	-	*	A	**	-	**	*	E	*	-		-	EB-R
Series														
Connector Type														
2 – Receptacle														
6 – Straight Plug														
8 – Right Angle Plug														
Waterproof														
E – Waterproof														
A – Waterproof During Mating Only														
Shell Size														
10 SL, 18, 20, 22, 24, 28, 32														
Contact Arrangement														
(Ref. page xxx-xxx)														
Contact Type														
P – Pin Contact														
S – Socket Contact														
With Protective Grounding Contact														
Alternate Insert Position														
W, X, Y, Z														
Outer Shell Color														
B – Black														
Endbell														
EB – With Endbell														
EB-R – With Right Angle Endbell														

Technology to Inspire Innovation



***"Building Technologies
to Connect Your World"***



Japan Aviation Electronics Industry, Limited

1-19, Aobadai 3-chome, Meguro-ku
Tokyo 153-8539, Japan
Telephone: 03-3780-2736
Fax: 03-3780-2883

JAE Electronics, Inc.

142 Technology Drive, Suite 100
Irvine, California 92618-2430, U.S.A.
Telephone: 949-753-2600
Fax: 949-753-2699
800-523-7278 Toll free in the U.S.A.

JAE Europe

Coliseum Business Centre
Riverside Way, Camberley
Surrey, GU15 3YL, England
Telephone: 44-1276-404000
Fax: 44-1276-404010

JAE Taiwan, Ltd.

4F-1, No. 88, Chung Hsiao E. Rd.
Sec. 2, Taipei, Taiwan, R.O.C.
Telephone: 886-2-2396-7676
Fax: 886-2-2392-5929

JAE Hong Kong, Ltd.

Suites 1407-11, 14/F, Tower 2, The Gateway,
25 Canton Road, Tsimshatsui, Kowloon, Hong Kong
Telephone: 852-2723-7782
Fax: 852-2723-9028

JAE Korea, Inc.

1602, Korea City Air Tower
159-9 Samsung-Dong, Kangnam-ku
Seoul, 135-973, Korea
Telephone: 82-2-551-8959
Fax: 82-2-551-8958

JAE Philippines, Inc.

PEZA Zone, Gateway Business Park, Javalera
General Trias, 4107 Cavite, Philippines
Telephone: 63-46-433-0285
Fax: 63-46-433-0287

JAE Singapore Pte., Ltd.

33 Tannery Lane, #02-01 Hoesteel
Industrial Building
Singapore 347789
Telephone: 65-6748-1332
Fax: 65-6748-2920

JAE Shanghai Co., Ltd.

RM 1407, Shanghai Mart 2299 Yanan Rd.
West Shanghai 200336 P.R.C.
Telephone: 86-21-6236-0322
Fax: 86-21-6236-1292

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[JL04-22EBL-R](#) [JL04V-6A22-J1PE-R](#) [JL04V-6A22J1SE-R](#) [JL04V-2A28-11PE-R](#)