







FEP16AT - FEP16JT

Features

- Low forward voltage drop.
- High surge current capacity.
- High current capability.
- High reliability.



Fast Rectifiers (Glass Passivated)

Absolute Maximum Ratings*

$T_A = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Value								Units
		16AT	16BT	16CT	16DT	16FT	16GT	16HT	16JT	
V_{RRM}	Maximum Repetitive Reverse Voltage	50	100	150	200	300	400	500	600	V
$I_{F(AV)}$	Average Rectified Forward Current, .375 " lead length @ $T_A = 100^\circ\text{C}$	16								A
I_{FSM}	Non-repetitive Peak Forward Surge Current 8.3 ms Single Half-Sine-Wave	200								A
T_{stg}	Storage Temperature Range	-55 to +150								$^\circ\text{C}$
T_J	Operating Junction Temperature	-55 to +150								$^\circ\text{C}$

*These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

Thermal Characteristics

Symbol	Parameter	Value	Units
P_D	Power Dissipation	8.33	W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	15	$^\circ\text{C/W}$
$R_{\theta JL}$	Thermal Resistance, Junction to Lead	2.2	$^\circ\text{C/W}$

Electrical Characteristics

$T_A = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Device								Units
		16AT	16BT	16CT	16DT	16FT	16GT	16HT	16JT	
V _F	Forward Voltage @ 8.0A	0.95				1.3		1.5		V
t _{rr}	Reverse Recovery Time I _F = 0.5 A, I _R = 1.0 A, I _{RR} = 0.25 A	35				50				ns
I _R	Reverse Current @ rated V _R T _A = 25°C T _A = 100°C	10 500								μA μA
C _T	Total Capacitance V _R = 4.0. f = 1.0 MHz	85						60		pF

Typical Characteristics




Figure 1. Forward Current Derating Curve



Figure 2. Non-Repetitive Surge Current Reverse Characteristics




Figure 3. Forward Voltage Characteristics



Figure 4. Reverse Current vs Reverse Voltage






Figure 5. Total Capacitance



Reverse Recovery Time Characteristic and Test Circuit Diagram

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[FEPB16FT/31](#) [FEP16BT/45](#) [FEP16FT/45](#) [FEP16HT-E3/45](#) [FEP16JT/45](#) [FEP16JT-E3/45](#) [FEPB16AT/31](#)
[FEPB16AT-E3/81](#) [FEPB16BT/31](#) [FEPB16BT-E3/81](#) [FEPB16CT/31](#) [FEPB16CT-E3/81](#) [FEPB16DT/31](#) [FEPB16DT-](#)
[E3/81](#) [FEPB16FT-E3/81](#) [FEPB16GT/45](#) [FEPB16GT-E3/81](#) [FEPB16JT/45](#) [FEPB16JT-E3/81](#) [FEPF16AT-E3/45](#)
[FEPF16BT-E3/45](#) [FEPF16CT-E3/45](#) [FEPF16DT-E3/45](#) [FEPF16FT-E3/45](#) [FEPF16GT-E3/45](#) [FEPF16HT-E3/45](#)
[FEPF16JT-E3/45](#) [FEP16AT/45](#)