



American Opto Plus LED Corp.
0.56" SMD Type LED Display
SMA562LR G/W
SMC562LR G/W

● **FEATURES**

- 0.56 inch (14.2 mm) Digit Height.
- SMD type.
- Low current operation.
- Gray face, White segment.
- RoHS compliant, Pb Free.

● **DESCRIPTION**

The SMA562LR G/W & SMC562LR G/W are 0.56 inch (14.2mm) height Dual 7-segment displays.

This device utilizes Super Red LED chip which are made from AlGaInP On a transparent GaAs, substrate.

The display has Gray face, White segment.

● **DEVICE**

PART NO	DESCRIPTION
SMA562LR G/W	Common Anode
SMC562LR G/W	Common Cathode

RoHS Compliance



Pb free.





Technical drawing of a mechanical part, likely a bracket or support, showing dimensions in millimeters (mm). The drawing includes a top view and a side view.

Top View Dimensions:

- Overall width: 8.05
- Overall height: 14.20
- Distance from top edge to centerline: 1.50
- Distance from centerline to bottom edge: 6.36
- Distance from left edge to centerline: 4.70
- Angle between top edge and centerline: 10°
- Radius of the bottom corner: $R0.50$

Side View Dimensions:

- Overall height: 14.20
- Distance from top edge to centerline: 1.50
- Distance from centerline to bottom edge: 6.36
- Distance from left edge to centerline: 4.70
- Angle between top edge and centerline: 10°
- Radius of the bottom corner: $R0.50$

Other Dimensions:

- Distance from centerline to bottom edge: 6.36
- Radius of the bottom corner: $R0.50$
- Radius of the bottom corner: $R0.50$



American Opto Plus LED Corp.





0.56" SMD Type LED Display

SMA562LR G/W


SMC562LR G/W

● TYPICAL INTERNAL EQUIVALENT CIRCUIT

Recommended
Soldering Pattern



(Common Anode)



(Common Cathode)



American Opto Plus LED Corp.

0.56" SMD Type LED Display

SMA562LR G/W

SMC562LR G/W

● SUPER RED (AlGaInP/GaAs)

ABSOLUTE MAXIMUM RATING AT Ta=25°C

Parameter	Symbol	Maximum Rating	Unit
Power dissipation	P _{AD}	75	mW
Derating liner from 25°C	-	0.3	mA / °C
Continuous forward current	I _{AF}	30	mA
Peak current (duty cycle 1/10, 1kHz)	I _{PF}	100	mA
Reverse voltage	V _R	5	V
Operating temperature	T _{OPR}	-40 to +105	°C
Storage temperature	T _{STG}	-40 to +105	°C

ELECTRICAL - OPTICAL CHARACTERISTICS AT Ta=25°C

Characteristic	Symbol	Condition	Min.	Type.	Max.	Unit
Forward Voltage, (Per Dice)	V _F	I _F = 20mA	-	2.0	2.6	V
Reverse Current, (Per Dice)	I _R	V _R = 5V	-	-	10	μA
Peak Wavelength	λ _P	I _F = 20mA	-	650	-	nm
Dominant Wavelength	λ _D	I _F = 20mA	-	640	-	nm
Luminous Intensity	I _V	I _F = 20mA	-	4	-	mcd
Spectral radiation bandwidth	Δλ	I _F = 20mA	-	20	-	nm



American Opto Plus LED Corp.

0.56" SMD Type LED Display

SMA562LR G/W

SMC562LR G/W

● SUPER RED (AlGaInP/GaAs) CURVE

Typical Electro-optical Characteristic Curves
(25 °C Free Air Temperature Unless Otherwise Specified)




Fig.1 FORWARD CURRENT VS. FORWARD VOLTAGE




Fig.2 RELATIVE INTENSITY VS. FORWARD CURRENT




Fig.3 FORWARD VOLTAGE VS. TEMPERATURE




Fig.4 RELATIVE INTENSITY VS. TEMPERATURE




Fig.5 RELATIVE INTENSITY VS. WAVELENGTH




Fig.6 MAX. ALLOWABLE DC CURRENT VS. AMBIENT TEMPERATURE




American Opto Plus LED Corp.
0.56" SMD Type LED Display
SMA562LR G/W
SMC562LR G/W

● **RECOMMEND SOLDERING PROFILE**

SMT Soldering Profile

Pb free reflow soldering Profile



● **SOLDERING IRON**

Basic specification : ≤ 4 seconds when 260°C, If temperature is higher, time should be shorter (+10°C → 1 sec). Power dissipation of iron should be smaller than 15W, and temperature should be controllable. Surface temperature of the device should be under 230°C.

● **REWORK**

Customer must finish rework within ≤ 3 sec under 350°C.