


Dimensions: (In.)

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Contact resistance: 100m Ω max.
- Insulation resistance: 100M Ω min. @ 500VDC
- Dielectric strength: 250VAC for 1 minute
- Life: 500,000 cycles

Mechanical Specifications:

- Type: SPST
- Operating force: 160 $\pm$ 50gf
- Stroke: .25mm +.2mm -.1mm
- Operating temperature: -25 $^{\circ}$ ~+70 $^{\circ}$ C

Soldering Process:

- Wave soldering temperature: 260 $^{\circ}$ C(500 $^{\circ}$ F) max. for 5 seconds with 1.6mm thick PCB
- Hand soldering temperature: 320 $^{\circ}$ C(608 $^{\circ}$ F) max. for 2 seconds using a 30W soldering iron

Material:

- Button color: brown

Tactile Switch (Thru-Hole)
101-0661

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0661](#)