

Terminal Blocks - Single Row

Series A4000 & Series B4000

Single Row Terminal Blocks

SPECIFICATIONS

Rating: See table.

Center Spacing: 0.562" or 9/16" (14.28mm)

Wire Range: See rating table.

Screw Size: #8-32 or #10-32 zinc-plated slotted screws

Torque Rating: #8 screw size 16 lb-in.; #10 screw size 20 lb-in.

Distance Between Barriers: 0.47" (11.9mm)

Operating Temperature: 105°C (221°F) max., -40°C

(-40°F) min.

Molded Material: Black, UL Rated 94V0 Thermoplastic

Hardware: Bottom studs supplied with nuts assembled. Cup washers are optional on bottom studs but are not recommended with ring terminals.

Extended Hex Nuts: Optional extended, slotted hex nuts enable easier installation and removal with hex wrench or screwdriver. Available in bulk for the #10-32 studs on Series A4953 blocks. Specify part number F582 and quantity.

Breakdown Voltage: 6100V

Agency Information: UL File E62622, CSA File 47235; CE Certified

RATING TABLE

Part Number	Terminal Top	Terminal Bottom	Wire* Range CU	Rated* Volts/Amps
A4003XX	# 8 Screw	#8 Stud	8-16 AWG	150V/50A
A4011XX	# 8 Screw	Solder	10-16 AWG	600V/35A
A4013XX	# 8 Screw	Solder	10-16 AWG	600V/35A
A4021XX	# 8 Screw	0.250 QC	10-16 AWG	600V/35A
A4035XX	# 8 Screw	Closed	8-16 AWG	600V/50A
A4041XX	#10 Screw	Solder	10-16 AWG	600V/35A
A4043XX	#10 Screw	Solder	10-16 AWG	600V/35A
A4051XX	#10 Screw	0.250 QC	10-16 AWG	600V/35A
A4803XX	#10 Screw	#8 Stud	8-16 AWG	150V/50A
A4813XX	#10 Screw	SolderTurret	10-16 AWG	600V/35A
A4843XX	#10 Screw	#8 Screw	8-16 AWG	150V/50A
A4953XX	#10 Stud	#10 Stud	8-16 AWG	150V/50A
B4843XX	#10 Screw	#8 Screw	8-16 AWG	600V/50A


* All models 30A Max. with 10 AWG;

35-50A ratings with 8 AWG using ring or fork type terminals.

Note: 50A rating achieved with #8 copper wire crimped to ring terminal.




A4000 Series Dimensions - in (mm)




Optional Cup Washers Assembled

Available on A4003, A4803, A4843, A4953 & B4843.



Reference Panel Cutout for 6 Position Block




* Dimensions in inches. To convert to millimeters, multiply by 25.4.

Part Numbering System

Series	Terminal Style	Base/End	Poles	Screw Options	Options
A4 B4					
A4 - standard B4 - barrier (only available in 84 terminal style)	00 - screw top; stud bottom 01 - screw top; solder bottom 02 - #8 screw top; 0.250 QC bottom 03 - screw top only 04 - #10 screw top; solder term. b. 05 - #10 screw top; 0.250 QC bottom 80 - screw top; stud bottom #10-32 top, #8-32 bottom insulated base 81 - screw top; solder turret bottom #10-32 84 - screw top; screw bottom #10-32 95 - stud top; stud bottom #10-32	*1 - flat base/ mount end 3 - insulator base- (not available in 03 terminal style) /mount end 5 - closed base/ mount end (available in 03 terminal only)	02 to 18	Blank - std. screw 00 - screws shipped bulk 04 - brass nickel-plated 07 - steel SEMS zinc plated (not available with hardware options; not available on A4003, A4803, A4813, A4843, B4843)	A1 to A9 - 0.250 QC †CW - cup washer (pg 20) J301 - flat slip-on jumper (2 position only) L1 to L6 marking options (pg 22) S1 & S2 - solder lugs/flat
*Available in 01, 02, 04 & 05 terminal style only.				† Available only on A4003, A4803, A4843, A4953 & B4843.	

Terminal Styles


Inches (Millimeters)




Hardware Options (Bulk ordering part numbers are in parentheses.)

Inches (Millimeters)


Solder Lugs



Jumpers



Quick Connects Blade Width A = 0.250". (For other orientations, contact factory.)



*Not available for A4843

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cooper Bussmann:

[A400303](#) [B484306](#) [A400302](#) [A400303CW](#) [A400305](#) [A400306](#) [A400308](#) [A401102](#) [A40110207](#) [A401103](#)
[A40110304](#) [A40110307](#) [A401104](#) [A40110400](#) [A401106](#) [A40110707](#) [A401108](#) [A401110](#) [A40111404](#) [A401116](#)
[A40111600](#) [A401302](#) [A40130204](#) [A401303](#) [A40130304](#) [A40130307](#) [A401304](#) [A40130407](#) [A40131404](#) [A403503](#)
[A403504](#) [A403504A1A2A3](#) [A403505](#) [A40411004](#) [A40430404](#) [A480302](#) [A480303CW](#) [A480304CW](#) [A480305](#)
[A480306](#) [A48030604](#) [A480308](#) [A481302](#) [A48130404](#) [A481305](#) [A48130604](#) [A48130704](#) [A481308](#) [A48130800](#)
[A48130804](#) [A48131004](#) [A48131204](#) [A481314](#) [A48131404](#) [A481316](#) [A48131600](#) [A48131604](#) [A48430200](#) [A484303](#)
[A48430304](#) [A484303L1](#) [A484304](#) [A48430400](#) [A48430404](#) [A484305](#) [A484306](#) [A48430604](#) [A484308](#) [A48430804](#)
[A48430904](#) [A484310](#) [A48431004](#) [A484312](#) [A495302](#) [A495303](#) [A495304](#) [A495305](#) [A495305CW](#) [A495306](#)
[A495310](#) [A495310CW](#) [A495312](#) [A495315CW](#) [B484302](#) [B484304](#) [B48430404](#) [B484305](#) [B48430604](#) [B484307](#)
[B484308](#) [B484308CW](#) [B484310](#) [B484312](#) [B48431200](#) [B48431204](#) [B484318](#)