



Rating		20A 12VDC 10A 24VDC	Mounting Hole  <table><tr><th>Thickness(mm)</th><th>X(mm)</th><th>Y(mm)</th></tr><tr><td>0.75~1.25</td><td rowspan="3">21.2+0.1</td><td>36.6^{+0.2}₋₀</td></tr><tr><td>1.25~2.0</td><td>36.8^{+0.2}₋₀</td></tr><tr><td>2.0~3.0</td><td>37.0^{+0.2}₋₀</td></tr></table>			Thickness(mm)	X(mm)	Y(mm)	0.75~1.25	21.2+0.1	36.6 ^{+0.2} ₋₀	1.25~2.0	36.8 ^{+0.2} ₋₀	2.0~3.0	37.0 ^{+0.2} ₋₀	Circuit Diagram 	
Thickness(mm)	X(mm)	Y(mm)															
0.75~1.25	21.2+0.1	36.6 ^{+0.2} ₋₀															
1.25~2.0		36.8 ^{+0.2} ₋₀															
2.0~3.0		37.0 ^{+0.2} ₋₀															
Configured For		12VDC 14V															
Contact Resistance		50m ohm Max.															
Insulation Resistance		DC 500V 100M ohm Min.															
Dielectric Strength		AC 1500V 1 minute															
Operation Temperature		-20°~85°															
Switch Function		4P SPDT ON-ON Lamp Dependent															
Lamp Type	Bulb 12VDC 14V																

*** MATERIAL:**




Frame: Nylon#66, Black

Actuator: Nylon#66 with 33%GF, Black

Lens 1: PC, Red

Lens 2: PC, Green

Water proof and dust proof to fit IP-56



RoHS Compliant

2	Added Dependent to switch function & Lamp Type. 12/09/2011.
1	Removed AC Rating marks and added DC Rating marks.8/23/10

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/19/10

Rev. 2

Unit: mm

Checked By: *G. Gold*

Title:
ROCKER SWITCH

CW P/N:
GRB260C501BBRG1