


MATERIALS	
BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE
COUPLING NUT	BRASS NICKEL PLATED



SPECIFICATIONS

FREQUENCY RANGE: DC TO 18 GHz
 ATTENUATION: 1 dB
 IMPEDANCE: 50 OHMS
 ACCURACY: ± 0.3 dB

DC - 4 GHz 1.15:1 MAX
 4 GHz - 8 GHz 1.20:1 MAX
 8 GHz - 12.4 GHz 1.25:1 MAX
 12.4 GHz - 18 GHz 1.35:1 MAX
 AVG. POWER HANDLING CAPABILITY: 2 WATTS



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7004-1

DES. N ATTENUATOR, MALE TO FEMALE, 1 dB
 FREQUENCY RANGE: DC TO 18 GHz

REV. A

FSCM NO. 53919

CAD FILE 030408

SCALE N/A

SIZE A

147

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.