

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16DEC2014	HMR	CW
	B	ECR-15-013292	16SEP2015	DL	CW
	BI	ECR-16-009730	06JUL2016	BS	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PBT
RATED VOLTAGE: 50 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 0.8 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X10XX000)

注释:

1. 技术参数:
绝缘材料: PBT
额定电压: 50V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 0.8 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接

2. 端子需要单独订购.
(订货号参考图面: T20200X10XX000)

T2020082101-001	HD-008-M HD-008公插(不锈钢螺丝)
T2020082101-000	HD-008-M HD-008公插
PART NUMBER 料号	DESCRIPTION 描述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16DEC2014 RAGHAVENDRA H M	TE TE Connectivity		
		CHK 16DEC2014 CHRIS WANG			
		APVD 16DEC2014 XU XIANG			
		PRODUCT SPEC 108-137042			
		APPLICATION SPEC 114-137042	NAME HD-008-M		
		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO T2020082101000
CUSTOMER DRAWING		SCALE 2:1	SHEET 1	OF 1	REV BI

