
















SANS CPA WITHOUT CPA		AVEC CPA WITH CPA		COULEUR COLOR	TOLERANCE POUR DETROMPAGE: ±0.05 KEYING TOLERANCE
REF TE NO	INDICE DE REVISION REVISION NUMBER	REF TE NO	INDICE DE REVISION REVISION NUMBER		
1801178-1	E	1-1801178-1	F	NOIR BLACK	 ECHELLE 3:2
1801178-2	E	1-1801178-2	F	BLEU BLUE	 ECHELLE 3:2
1801178-3	E	1-1801178-3	F	GRIS GREY	 ECHELLE 3:2
1801178-4	E	1-1801178-4	F	JAUNE YELLOW	 ECHELLE 3:2
1801178-5	E	1-1801178-5	F	VERT GREEN	 ECHELLE 3:2
1801178-6	E	1-1801178-6	F	MARRON BROWN	 ECHELLE 3:2
1801178-7	E	1-1801178-7	F	BLANC WHITE	 ECHELLE 3:2
1801178-8	E	1-1801178-8	F	ROUGE RED	 ECHELLE 3:2
1801178-9	E	1-1801178-9	F	ORANGE ORANGE	 ECHELLE 3:2

- NOTES/NOTES:
- 1- 1-1801178-1 REPRESENTE (COD. NOIR) / AS SHOWN (COD. BLACK)
- 2 REPERE ALVEOLES / CAVITY MARKING
- 3 LOGO TE / TE LOGO
- 4 DATE D'ASSEMBLAGE / ASSEMBLY DATE
- 5 CODE DU LIEU D'ASSEMBLAGE / ASSEMBLY LOCATION DATE
- E = EUROPE / EUROPE
- C = CHINE / CHINA
- M = MERCOSUR / MERCOSUR
- H A = AFRICA / AFRIQUE
- 6 NUMERO DE LA MACHINE D'ASSEMBLAGE / NUMBER ASSEMBLY LINE
- 7 REF TE DE L'ASSEMBLAGE (RACINE) / TE ASSEMBLY NO (RACINE)
- 8 REF TE DE L'ASSEMBLAGE (SUFFIXE) / TE ASSEMBLY NO (SUFFIX)
- 9 INDICE DE REVISION PRODUIT / PRODUCT REVISION NUMBER
- 10- PIECES A UTILISER AVEC VOIR TABLEAU "COMPOSANTS ASSOCIES" / MATED WITH : SEE TABLE "ASSOCIATED PARTS"




LOC
F

DIST
00

REVISONS

P	LYR	DESCRIPTION	DATE	DWN	APVD
E		INCREASE IN THE LENGTH OF THE EXTERNAL WALL ABOVE THE LOCKING LATCH	01DEC2009	FJ	XR
F		MODIFIED CPA TO DECREASE ACTIVATION AND DESACTIVATION FORCE	12JUL2010	FJ	XR
G		ADDED NUMBER ASSY LINE ON THE PART	21NOV2011	FJ	XR
H		UPDATED NOTE 5 WITH NEW PLANT CODE	15NOV2018	ASB	XR



CPA ONLY FOR REF. 1-1801178-X
CPA seulement pour la réf. 1-1801178-X

ECHELLE 2:1

2x 3.33 = 6.66

3.33

0.7

E

34

33

0.25

C B

12.25

19.65

0.9±0.1

32

1.7±0.15

30

0.3

C B A

31

E

SECTION CABLE ADMISSIBLE PAR CONTACT
ACCEPTABLE CABLE SECTIONS PER CONTACT

La section des câbles utilisés doit être comprise entre 0,35 et 2mm² avec un diamètre d'isolant compris entre 1,40mm mini et 2,80mm Maxi.
The cross-section of the cables used must be between 0,35 and 2mm² (with insulator diameter included between 1,40mm mini and 2,80mm Maxi)

CAPOT FIXE 3 VOIES - SORTIE GAUCHE/DROITE FIXED COVER 3 WAYS - LEFT/RIGHT EXIT	POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm	1801467-1
CAPOT FIXE 3 VOIES - SORTIE HAUT/BAS FIXED COVER 3 WAYS - UP/DOWN EXIT <td>POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm</td> <td>1-1801467-1</td>	POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm	1-1801467-1
CAPOT FIXE 3 VOIES - SORTIE AXIALE FIXED COVER 3 WAYS - EXIT IN LINE <td>POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm</td> <td>1801467-2</td>	POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm	1801467-2
CAPOT ROTATIF 90 DEG. 3 VOIES ROTATIVE COVER 90 DEG. 3 WAYS	POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm	1-1801467-2
CAPOT (*) COVER	POUR GAINÉ ANNELÉE DE 6mm FOR CORRUGATED TUBE OF 6mm	1801468-1
SUPPORT (*) ADAPTER	POUR GAINÉ ANNELÉE DE 4.5mm FOR CORRUGATED TUBE OF 4.5mm	1-1801468-1
CLIP 1.5 SENSOR II DORE Section 1.4 à 2mm ² RECEPTACLE 1.5 SENSOR II GOLD PLATED Section 1.4 to 2mm ²		1801468-1
CLIP 1.5 SENSOR II DORE Section 0.75 à 1mm ² RECEPTACLE 1.5 SENSOR II GOLD PLATED Section 0.75 to 1mm ²		1801359-1
CLIP 1.5 SENSOR II DORE Section 0.35 à 0.5mm ² RECEPTACLE 1.5 SENSOR II GOLD PLATED Section 0.35 to 0.5mm ²		1670328-1
OBTURATEUR "MINI-ETANCHE" PLUGGING PIN PORTE-LANGUETTES 3 VOIES HP 3 WAYS TAB CONNECTOR HP		1670326-1
		1564724-1
		1801177-X

DESCRIPTION
TITLE

COMPOSANTS ASSOCIES
ASSOCIATED PARTS

(*) : POUR LE CAPOT ROTATIF, PRENDRE : SUPPORT + CAPOT
FOR THE ROTATIVE COVER, TAKE: ADAPTER + COVER

COULEUR COLOR	MATIERE MATERIAL	DESCRIPTION TITLE	REP. ITEM
ORANGE ORANGE	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	CPA	6
VERT GREEN	SILICONE LUBRIFIE A 5% ; DURETE 30 SHORE A LUBRICATED SILICON TO 5% ; HARNESS 30 SH. A	JOINT GROMMET GROMMET SEAL	5
NOIR BLACK	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	GRILLE ARRIERE REAR GRID	4
VERT GREEN	SILICONE LUBRIFIE A 4% ; DURETE 50 SHORE A LUBRICATED SILICON TO 4% ; HARNESS 50 SH. A	JOINT INTERFACIAL INTERFACE SEAL	3
VOIR TABLEAU DES REF. SEE TABLE OF PART NO	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	DOUBLE VERROUILLAGE CODAGE (VOIR TABLEAU DES REFS) SECONDARY LOCKING CODING (SEE TABLE OF PART NO)	2
NOIR BLACK	PBT-GF15 (MATIERE: HB) (HB MATERIAL)	BOITIER PORTE-CLIPS RECEPTACLE HOUSING	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
A. BARLEMON
23NOV2007

CHK
J. DAHER
23NOV2007

APVD
J. DAHER
23NOV2007

PRODUCT SPEC

108-15378

APPLICATION SPEC

411-15712

WEIGHT
7.1g / 7.4g with CPA

CUSTOMER DRAWING

SCALE
3:1

SHEET
1 OF 1

REV
H

TE Connectivity

NAME
3 WAYS RECEPTACLE CONNECTOR HP
PORTE-CLIPS 3 VOIES HP

SIZE
-

CAGE CODE
-

DRAWING NO
A100779

DRAWING NO
C=1801178

RESTRICTED TO
-