

## Type 1 Mild Steel Splitter Box CSB Series

Hinged Door with Screw



### Application

- The splitter boxes are designed for indoor distribution of up to 600 V (max) service using either 3 or 4 wires.

### Standards

- CSA Type 1
- Complies with
  - IEC 60529, IP20

### Construction

- Formed and spot welded from 14 or 16 gauge steel.
- Factory installed splitter blocks.
- Series of knockouts on each side.
- Padlocking hasp.

### Finish


- Enclosure and cover are finished in ANSI 61 gray powder coating.

### Accessories


**Splitter Blocks**

**Grounding Kits**






### Front View



### Side View



### Bottom View

NOTE: KNOCKOUTS TYPICAL ON OPPOSITE SIDES

Part No.			CU/AL	Dimensions			Ship Wt.
3 Wire	4 Wire	Less Blocks	Amps	H	W	D	Ibs
<b>CSB73</b>	<b>CSB74</b>	<b>CSB70</b>	70/70	12.00	10.00	4.00	9
<b>CSB103</b>	<b>CSB104</b>	<b>CSB100</b>	125/120	15.00	10.00	4.00	10
<b>CSB203</b>	<b>CSB204</b>	<b>CSB200</b>	225/225	18.00	12.00	5.00	16
<b>CSB403</b>	<b>CSB404</b>	<b>CSB400</b>	400/340	24.00	17.00	6.00	37
<b>CSB603*</b>	<b>CSB604*</b>	<b>CSB600*</b>	600/574	30.00	24.00	7.00	63

\* 14 gauge steel

*Data subject to change without notice*

© 2014. Hammond Manufacturing Ltd. All rights reserved.