




NOTES:

1. MATERIALS:
HOUSING - LIQUID CRYSTAL POLYMER (LCP),
GLASS-FILLED, UL 94V-0, COLOR: BLACK
SIGNAL PIN - COPPER ALLOY
2. FINISHES:
CONTACT AREA: SELECTIVE GOLD (Au)
PCB TAILS: SELECTIVE MATTE TIN (Sn)
NICKEL (Ni) OVERALL.
3. THIS PART CONFORMS TO MOLEX PRODUCT
SPECIFICATION PS-74031-999
4. FOR MIXED CONTACT LENGTHS CONSULT
MOLEX FOR AVAILABILITY
5. FOR SPECIFIC MATERIAL NUMBERS & MATING
INFORMATION REFER TO SHEET 2
6. PACKAGE PER PK-74058-003
7. MARK PART WITH PART NUMBER & DATE
CODE APPROXIMATELY WHERE SHOWN
8. MAPS (MOLEX ADVANCED PLATING SYSTEM).

THE PRIMARY CARTON WITH A LABEL STATING
"ELV AND RoHS COMPLAINT" IS LEAD FREE.
CARTONS WITHOUT THIS LABEL MAY CONTAIN LEAD.


LEAD FREE CONVERSION EC NO: UCP2013-0687 2012/08/22 2012/11/26 2012/12/14 DRWNGES CHKD:MMOLFE APPR:SMILLER	DESCRIPTION REV G	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 		
					DRAWN BY JMELTON		DATE 2010/05/19	TITLE VHDM LITE 6 ROW SHIELD END BACKPLANE SALES ASSEMBLY			
					CHECKED BY SDANNELLEY		DATE 2010/05/19	molex			
					APPROVED BY SMILLER		DATE 2010/07/14				
					MATERIAL NO.		DOCUMENT NO.				
			ANGULAR ±1/2°		SEE SHEET 2		SD-75196-001				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

M/N 75196-()	---0*	---1*	---2*	---3*	---4*	---5*	---6*	---7*	---8*
KEYING PIN ORIENTATION									

75196 - * * * *

CONTACT LOAD
(PIN HEIGHT)
1 & 6 = 4.75
2 & 7 = 6.25
3 & 8 = 4.25
4 & 9 = 5.15

NUMBER OF COLUMNS/PLATING
10 = 10 COLUMN MATTE TIN (FORMERLY TIN/LEAD)
25 = 25 COLUMN MATTE TIN (FORMERLY TIN/LEAD)
60 = 10 COLUMN MATTE TIN (MAPS)
75 = 25 COLUMN MATTE TIN (MAPS)
90 = 10 COLUMN MATTE TIN
85 = 25 COLUMN MATTE TIN



PART NUMBER	COLUMN	NUMBER OF SIGNAL PIN	NUMBER OF SHIELD	A	B	M	GOLD THICKNESS MICROMETER	TIN THICKNESS MICROMETER
75196-60*1	10	60	0	27.00	18.00	4.75	0.25 MAPS	0.76-152
75196-*0*1							0.76	
75196-75*1	25	150	0	57.00	48.00	6.25	0.25 MAPS	
75196-*5*1							0.76	
75196-60*2	10	60	0	27.00	18.00	4.25	0.25 MAPS	
75196-*0*2							0.76	
75196-75*2	25	150	0	57.00	48.00	5.15	0.25 MAPS	
75196-*5*2							0.76	
75196-60*3	10	60	0	27.00	18.00	4.75	0.25 MAPS	
75196-*0*3							0.76	
75196-75*3	25	150	0	57.00	48.00	6.25	0.25 MAPS	
75196-*5*3							0.76	
75196-60*4	10	60	0	27.00	18.00	5.15	0.25 MAPS	
75196-*0*4							0.76	
75196-75*4	25	150	0	57.00	48.00	4.75	0.25 MAPS	
75196-*5*4							0.76	

SEE SHEET 1 EC NO: UCP2013-0687 DRAWINGS 2012/08/22 CHKD:MMOLFE 2012/11/26 APPR:SMILLER 2012/12/14	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY DATE JMELTON 2010/05/19 CHECKED BY DATE SDANNELLEY 2010/05/19 APPROVED BY DATE SMILLER 2010/07/14	SCALE 2.5:1 TITLE VHDM LITE 6 ROW SHIELD END BACKPLANE SALES ASSEMBLY DOCUMENT NO. SD-75196-001	DESIGN UNITS METRIC THIRD ANGLE PROJECTION	SHEET NO. 2 OF 2