



MGV252012S2R2M-10

PHYSICAL DIMENSIONS:


A 2.50 \pm 0.20
B 2.00 \pm 0.20
C 1.20 Max.
D 0.60 \pm 0.30



LAND PATTERNS FOR REFLOW SOLDERING



RoHS



ELECTRICAL SPECIFICATION @ 25°C

	Min	Norm	Max
INDUCTANCE (uH) L @ 1MHz/1mA $\pm 20\%$	1.76	2.20	2.64
DCR (Ω)		0.074	0.089
Saturation Current Isat (A)		3.50	3.20
Heating Current Irms (A)		2.50	2.20

NOTES:

1. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
2. TERMINATION FINISH IS 100% TIN.
3. OPERATING TEMPERATURE RANGE: $-40^\circ\text{C} \sim +125^\circ\text{C}$.
4. STORAGE TEMPERATURE RANGE: $-50^\circ\text{C} \sim +125^\circ\text{C}$.
5. Isat MEANS THAT MAX DC CURRENT WILL CAUSE A PROXIMATELY 30% INDUCTANCE REDUCTION FROM INITIAL VALUE.
6. Irms MEANS THAT MAX DC CURRENT WILL CAUSE PROXIMATELY 40°C TEMPERATURE RISE FROM $25 \pm 5^\circ\text{C}$ AMBIENT.

DIMENSIONS ARE IN mm.			This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird		
PROJECT/PART NUMBER:	REV	PART TYPE:	DRAWN BY:				
MGV252012S2R2M-10	A	POWER INDUCTOR	QIU				
DATE: 06/08/17	SCALE: NTS	SHEET: 1 of 1					
A ORIGINAL DRAFT 06/08/17 QIU	CAD #	TOOL #					
REV	DESCRIPTION	DATE	INT	MGV252012S2R2M-10-A			