


TL-241 Draw Catch




Characteristic


A fastener utilizing the characteristic of resin.
Having this simple mechanism, its appearance is compact and it suits for devices with polished appearances.
Suitable for devices that excellent performance on waterproof or salt damage resistance is required.

Application

Measuring instruments / Medical devices



Operational Instruction
Hang the latch on the keeper and press it until it becomes flat on the plane.



Model No.	Allowable Load N (kgf)	Net Weight (g)	Code No.
TL-241-1	49.1 (5)	9.1	1591
TL-241-2	29.4 (3)	3.0	1592

Parts List

No.	Part Name	Material	Finish	Quantity
1	Latch	PP	Black	1
2	Keeper			1

Size List

Model No.	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q
TL-241-1	29.8	54.3	7.7	21.5	31	2.5	4.7	16.7	14	9.2	9.9	18.6	(10)	6.5	3.2
TL-241-2	17.2	43	6	12.5	25	2	3.8	12.7	11.3	6.2	6.5	12.9	(8.5)	5.6	2.7

TL-253 Adjustable Pull Down Catch




Characteristic

The arm④ shall move to adjust the catch by turning the stopper shaft⑦ with screwdriver from the lever① side. It suits for an application using with packing.

Application

Distribution boards / General industrial machines / Machine tools / Various types of metallic boxes



Model No.	Allowable Load N (kgf)	Net Weight (g)	Code No.
TL-253-1	120 (12.2)	71	1711

Parts List

No.	Part Name	Material	Finish	Quantity
1	Lever	SPCC	Zn	1
2	Base			1
3	Shaft (A)	SWRM		1
4	Arm	SPCC		1
5	Shaft (B)	SWRM		1
6	Stopper			1
7	Stopper Shaft			1
8	Keeper	SPCC		1