


## 5A Load Switching provided for the whole G3M product line

- Thin design for high-density PCB applications.
- DC input-AC output for a 3-A load or a 5-A load.
- The 5A type is UL, CSA, EN (EN60950) approved.
- UL and CSA compliance for 3-A Relays  
(-UTU models have TÜV compliance as well).
- UL and CSA compliance for 5-A Relays  
(-VD models have VDE compliance as well).

RoHS Compliant

Refer to "Solid State Relays Common Precautions".



### Model Number Legend

G3M-□□□□□-□-□  
1 2 3 4 5 6

#### 1. Rated Load Power Supply Voltage

2: Maximum operating voltage  
lower than 264 V

#### 2. Rated Load Current

03: 3 A  
05: 5 A

#### 3. Terminal Type

P: PCB terminals

#### 4. Zero Cross Function

Blank: Equipped with zero cross function  
L : Not equipped with zero cross function

#### 5. Certification

Blank: UL and CSA for 3-A models  
No certification for 5-A models  
UTU : UL, CSA and TÜV for 3-A models  
VD : UL, CSA and TÜV for 5-A models  
UTU-1 : UL, CSA and TÜV for 3-A models  
with reinforced insulation  
VD-1 : UL, CSA and TÜV for 5-A models  
with reinforced insulation

#### 6. Input Terminal Pitch

Blank: 7.62 mm  
4 : 5.08 mm

### List of Models

| Isolation  | Input terminal pitch | Zero cross function | Indicator | Rated output load     | Rated input voltage | Model       |        | Minimum packing unit |
|------------|----------------------|---------------------|-----------|-----------------------|---------------------|-------------|--------|----------------------|
| Phototriac | 7.62 mm              | Yes                 | No        | 3 A at 100 to 240 VAC | 5 VDC               | G3M-203P    | 5 VDC  | 100 pcs              |
|            |                      |                     |           |                       | 12 VDC              | G3M-203P    | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-203P    | 24 VDC |                      |
|            |                      |                     |           | 5 A at 100 to 240 VAC | 5 VDC               | G3M-205P    | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-205P    | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-205P    | 24 VDC |                      |
|            |                      | No                  |           | 3 A at 100 to 240 VAC | 5 VDC               | G3M-203PL   | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-203PL   | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-203PL   | 24 VDC |                      |
|            |                      |                     |           | 5 A at 100 to 240 VAC | 5 VDC               | G3M-205PL   | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-205PL   | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-205PL   | 24 VDC |                      |
|            | 5.08 mm              | Yes                 |           | 3 A at 100 to 240 VAC | 5 VDC               | G3M-203P-4  | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-203P-4  | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-203P-4  | 24 VDC |                      |
|            |                      |                     |           | 5 A at 100 to 240 VAC | 5 VDC               | G3M-205P-4  | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-205P-4  | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-205P-4  | 24 VDC |                      |
|            |                      | No                  |           | 3 A at 100 to 240 VAC | 5 VDC               | G3M-203PL-4 | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-203PL-4 | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-203PL-4 | 24 VDC |                      |
|            |                      |                     |           | 5 A at 100 to 240 VAC | 5 VDC               | G3M-205PL-4 | 5 VDC  |                      |
|            |                      |                     |           |                       | 12 VDC              | G3M-205PL-4 | 12 VDC |                      |
|            |                      |                     |           |                       | 24 VDC              | G3M-205PL-4 | 24 VDC |                      |

■Ratings

Input (Each model has 5-VDC, 12-VDC, and 24-VDC input versions.)

| Rated voltage | Operating voltage | Impedance   | Must operate voltage level | Must release voltage level |
|---------------|-------------------|-------------|----------------------------|----------------------------|
| 5 VDC         | 4 to 6 VDC        | 300 Ω ±20%  | 4 VDC max.                 | 1 VDC min.                 |
| 12 VDC        | 9.6 to 14.4 VDC   | 800 Ω ±20%  | 9.6 VDC max.               |                            |
| 24 VDC        | 19.2 to 28.8 VDC  | 1.6 kΩ ±20% | 19.2 VDC max.              |                            |

Output

| Item<br>Model | Rated voltage  | Applicable load    |              |                       |
|---------------|----------------|--------------------|--------------|-----------------------|
|               |                | Load voltage range | Load current | Inrush current        |
| G3M-203P(L)   | 100 to 240 VAC | 75 to 264 VAC      | 0.1 to 3 A * | 45 A (60 Hz, 1 cycle) |
| G3M-205P(L)   |                |                    | 0.1 to 5 A * | 60 A (60Hz, 1 cycle)  |


\* The load current varies depending on the ambient temperature.  
Refer to Load Current vs. Ambient Temperature under Engineering Data.

■Characteristics

| Item                          | Model | G3M-203P(L)                                                                  | G3M-205P(L)  |
|-------------------------------|-------|------------------------------------------------------------------------------|--------------|
| Operate time                  |       | G3M-□□□PL: 1 ms max.<br>G3M-□□□P: 1/2 of load power source cycle + 1 ms max. |              |
| Release time                  |       | 1/2 of load power source cycle + 1 ms max.                                   |              |
| Output ON voltage drop        |       | 1.6 V (RMS) max.                                                             |              |
| Leakage current               |       | 1.5 mA max. (at 200 VAC)                                                     |              |
| Insulation resistance         |       | 1,000 MΩ min. (at 500 VDC)                                                   |              |
| Dielectric strength           |       | 2,500 VAC, 50/60 Hz for 1 min between input and output                       |              |
| Vibration resistance          |       | 10 to 55 to 10 Hz, 0.75-mm single amplitude (1.5-mm double amplitude)        |              |
| Shock resistance              |       | 1,000 m/s²                                                                   |              |
| Ambient operating temperature |       | -30°C to 80°C (with no icing or condensation)                                |              |
| Ambient operating humidity    |       | 45% to 85%RH                                                                 |              |
| Storage temperature           |       | -30°C to 100°C (with no icing or condensation)                               |              |
| Weight                        |       | Approx. 15 g                                                                 | Approx. 25 g |



## Engineering Data

### Load Current vs. Ambient Temperature




### Load Current vs. Ambient Temperature (Close Mounting) G3M-205 Series (5-A Load)

<X direction>





### One Cycle Surge Current: Non-repetitive

Non-repetitive (Reduce the current under the dotted line of the impulse withstand current for repetitive operation)





<Y direction>



### Operating Environment Precautions

The rated value for the ambient operating temperature of the SSR is determined under conditions when there is no heat build-up. (Left graph) Note that it is necessary to reduce the load current as the ambient temperature of the SSR may increase due to operating conditions. (Figure below is an example of the G3M-205P(L) model) When using the SSR, design the system to allow heat dissipation sufficient to stay below the Load Current vs. Ambient Temperature characteristic curve.

<Z direction>




- Thirty Relays are soldered to the PCB at each given spacing.
- Continuous power.

## ■ Dimensions


(Unit: mm)

**G3M-203P(L)**  
**G3M-203P(L)-4**




\*Input terminal pitch for models ending in "-4" is 5.08 mm.


**PCB Dimensions (BOTTOM VIEW)**  
**G3M-203P(L)**




**G3M-203P(L)-4**



### Terminal Arrangement (BOTTOM VIEW)




**G3M-205P(L)**  
**G3M-205P(L)-4**




\*Input terminal pitch for models ending in "-4" is 5.08 mm.


### PCB Dimensions (BOTTOM VIEW) G3M-205P(L)



**G3M-205P(L)-4**



### Terminal Arrangement (BOTTOM VIEW)



## ■Precautions

- Please refer to “Solid State Relays Common Precautions” for correct use.

• Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.  
• Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

**Note: Do not use this document to operate the Unit.**

---

**OMRON Corporation**  
Electronic and Mechanical Components Company

**Contact:** [www.omron.com/ecb](http://www.omron.com/ecb)

**Cat. No. K073-E1-07**  
1014(0207)(O)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Omron:

[G3M-203P-4-DC24](#) [G3M-202P-US-DC12](#) [G3M-203P-DC12](#) [G3M-203P-DC24](#) [G3M-202P-US-4-DC12](#) [G3M-202P-US-DC24](#) [G3M-203P-DC5](#) [G3M-202P-US-4-DC5](#) [G3M-205PL-DC24](#) [G3M-203PL-DC24](#) [G3M-205PL-DC12](#) [G3M-205PL-DC5](#) [G3M-202P-US-DC5](#) [G3M-102PL-US DC12](#) [G3M-102PL-US DC24](#) [G3M-102PL-US-4 DC12](#) [G3M-102PL-US-4 DC24](#) [G3M-102PL-US-4 DC5](#) [G3M-202PL-US DC12](#) [G3M-202PL-US DC24](#) [G3M-202PL-US-4 DC12](#) [G3M-202PL-US-4 DC24](#) [G3M-202PL-US-4 DC5](#) [G3M-202P-US-4 DC24](#) [G3M-203P-4 DC12](#) [G3M-203P-4 DC5](#) [G3M-203PL DC12](#) [G3M-203PL DC5](#) [G3M-203PL-4 DC24](#) [G3M-203PL-4 DC5](#) [G3M-205P DC12](#) [G3M-205P DC24](#) [G3M-205P-4 DC12](#) [G3M-205P-4 DC24](#) [G3M-205P-4 DC5](#) [G3M-205PL-4 DC12](#) [G3M-205PL-4 DC24](#) [G3M-205PL-4 DC5](#) [G3M-202PL DC12](#) [G3M-202PL-UTU DC5](#) [G3M-202P-UTU DC5](#) [G3M-203P-UTU-1-4 DC12](#) [G3M-203P-UTU-1-4 DC5](#) [G3M-205P-DC5](#) [G3M-202PL-UTU-1-Z DC24](#) [G3M-203PL-UTU-1 DC24](#) [G3M-203P-UTU-1 DC5](#) [G3M-202PL-UTU-2-Z-DC24](#) [G3M-203P-UTU-1 DC12](#) [G3M-203P-UTU-1 DC24](#) [G3M-205P-VD-1 DC24V](#) [G3M-203PL-4 DC12](#)